




(2,54 mm) .100"

SL, SDL SERIES

LOW PROFILE MACHINED SOCKET STRIPS

FEATURES

- Achieve low profile without sacrificing insertion depth!
- Choice of four precision screw machined lead styles.
- Exceptionally low profile, down to (2,11 mm) .083" off of board.
- Mates with BBL or BDL for board stacking spaces down to (3,89 mm) .153"

SPECIFICATIONS

For complete specifications see www.samtec.com?SL or www.samtec.com?SDL

Insulator Material:

Black Glass Filled Polyester

Contact/Shell Materials:

BeCu/Brass

Plating:

Au or Sn over 50µ" (1,27 µm) Ni

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ

Insertion Force:

(Single contact only)

Standard =

9 oz (2,50 N) avg.,

16 oz (4,45 N) max

((0,43 mm) .017" DIA probe)

Low Insertion Force =

2.5 oz (0,70 N) avg.,

5.5 oz (1,53 N) max

((0,43 mm) .017" DIA probe)

Withdrawal Force:

(Single contact only)

Standard =

2.5 oz (0,70 N) avg.,

1.5 oz (0,42 N) min

((0,43 mm) .017" DIA probe)

Low Insertion Force =

2.0 oz (0,56 N) avg.,

0.5 oz (0,14 N) min

((0,43 mm) .017" DIA probe)

RoHS Compliant: Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Some lengths, styles and options are non-standard, non-returnable.

Mates with:

TS, TD, HTS, BBS, BBD, BBL, BDL, BHS

TYPE STRIP

1

NO. PINS PER ROW

PLATING OPTION


LEAD STYLE

SL


= Single Row Low Profile Socket Strip

SDL

= Double Row Low Profile Socket Strip



01 thru 32



01 thru 36

-G

= 30µ" (0,76 µm)
Gold contact,
10µ" (0,25µm)
Gold shell

-T


= 30µ" (0,76 µm)
Gold contact,
Tin shell

-TT

= Tin contact and shell
(LIF not available)


Low Insertion Force (LIF) Available

-10
Low Profile
(Hollow Leg)




Contact Length = (2,11 mm) .083"
Lead DIA Accepted = (0,38 mm) .015" to (0,51 mm) .020"
Insertion Depth = (2,67 mm) .105" to (4,32 mm) .170"
Style 10 Component Part No. = SC-3P1

-11
Low Profile
(Standard Mount)
For LIF specify -31




Contact Length = (1,58 mm) .062"
Lead DIA Accepted = (0,41 mm) .016" to (0,53 mm) .021"
Insertion Depth = (2,03 mm) .080" to (2,67 mm) .105"
Style 11 Component Part No. = SC-4P1
Style 31 Component Part No. = EZ-4P1

-12
Micro-Socket
(Hollow Leg)



Contact Length = (1,58 mm) .062"
Lead DIA Accepted = (0,41 mm) .016" to (0,51 mm) .020"
Insertion Depth = (1,65 mm) .065" to (3,81 mm) .150"
Style 12 Component Part No. = SC-5P1

-19
Micro-Socket
(Hollow Leg)
For LIF specify -39



Contact Length = (1,58 mm) .062"
Lead DIA Accepted = (0,41 mm) .016" to (0,51 mm) .020"
Insertion Depth = (1,65 mm) .065" to (3,56 mm) .140"
Style 19 Component Part No. = SC-8P1
Style 39 Component Part No. = EZ-8P1

Standard Socket
(Reference only.
Not available
with SL & SDL)