

# General Identification Materials

www.BradyID.com



3" Core General ID Materials:

## B-498 Repositionable Vinyl Cloth Material

Color: White Finish: Semi-Gloss

Repositionable vinyl cloth material for wire, cable, and component marking. Adhesive and cloth backing offers excellent holding power, while easily being repositioned and removed.

Performance Attributes:




Figure 1




Figure 2




Figure 3

| Diagram                                                                                                                                                                                                                                          | Catalog #          | Material    | Color | Label Width A<br>Inch (mm) | Label Height B<br>Inch (mm) | Horiz. Repeat C<br>Inch (mm) | Vert. Repeat D<br>Inch (mm) | Web Width E<br>Inch (mm) | Labels<br>Per Row | Labels<br>Per Pkg | Rec.<br>Ribbon |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|-------------|-------|----------------------------|-----------------------------|------------------------------|-----------------------------|--------------------------|-------------------|-------------------|----------------|
| Fig. 3                                                                                                                                                                                                                                           | THT-94-498-2       | Vinyl Cloth | White | 0.240 (6.1)                | 165 ft (50.8 m)             | -                            | -                           | 1.000 (25.4)             | 1                 | 1 Roll Cont.      | R6206          |
| Fig. 1                                                                                                                                                                                                                                           | THT-90-498-5       | Vinyl Cloth | White | 0.250 (6.4)                | 1.437 (36.5)                | 0.350 (8.9)                  | 1.562 (39.7)                | 2.200 (55.9)             | 6                 | 5,000             | R6200          |
| Fig. 3                                                                                                                                                                                                                                           | THT-93-498-2       | Vinyl Cloth | White | 0.312 (7.9)                | 165 ft (50.8 m)             | -                            | -                           | 1.000 (25.4)             | 1                 | 1 Roll Cont.      | R6206          |
| Fig. 3                                                                                                                                                                                                                                           | THT-92-498-2       | Vinyl Cloth | White | 0.375 (9.5)                | 165 ft (50.8 m)             | -                            | -                           | 1.000 (25.4)             | 1                 | 1 Roll Cont.      | R6206          |
| Fig. 1                                                                                                                                                                                                                                           | THT-68-498-10      | Vinyl Cloth | White | 0.500 (12.7)               | 0.750 (19.1)                | 0.600 (15.2)                 | 0.850 (21.6)                | 2.500 (63.5)             | 4                 | 10,000            | R6202          |
| Fig. 1                                                                                                                                                                                                                                           | THT-87-498-5       | Vinyl Cloth | White | 0.500 (12.7)               | 1.437 (36.5)                | 0.600 (15.2)                 | 1.562 (39.7)                | 3.700 (94.0)             | 6                 | 5,000             | R6207          |
| Fig. 1                                                                                                                                                                                                                                           | THT-14-498-10      | Vinyl Cloth | White | 0.650 (16.5)               | 0.200 (5.1)                 | 0.700 (17.8)                 | 0.300 (7.6)                 | 2.950 (74.9)             | 4                 | 10,000            | R6202          |
| Fig. 1                                                                                                                                                                                                                                           | THT-1-498-10       | Vinyl Cloth | White | 0.750 (19.1)               | 0.250 (6.4)                 | 0.800 (20.3)                 | 0.350 (8.9)                 | 3.350 (85.1)             | 4                 | 10,000            | R6207          |
| Fig. 1                                                                                                                                                                                                                                           | THT-91-498-5       | Vinyl Cloth | White | 0.750 (19.1)               | 0.937 (23.8)                | 0.875 (22.2)                 | 1.062 (27.0)                | 3.500 (88.9)             | 4                 | 5,000             | R6207          |
| Fig. 1                                                                                                                                                                                                                                           | THT-95-498-5       | Vinyl Cloth | White | 0.800 (20.3)               | 1.437 (36.5)                | 0.900 (22.9)                 | 1.562 (39.7)                | 2.800 (71.1)             | 3                 | 5,000             | R6202          |
| Fig. 1                                                                                                                                                                                                                                           | THT-165-498-5      | Vinyl Cloth | White | 0.800 (20.3)               | 1.437 (36.5)                | 0.900 (22.9)                 | 1.562 (39.7)                | 3.700 (94.0)             | 4                 | 5,000             | R6207          |
| Fig. 1                                                                                                                                                                                                                                           | THT-5-498-10       | Vinyl Cloth | White | 1.000 (25.4)               | 0.500 (12.7)                | 1.075 (27.3)                 | 0.600 (15.2)                | 3.350 (85.1)             | 3                 | 10,000            | R6207          |
| Fig. 2                                                                                                                                                                                                                                           | THT-59-498-10      | Vinyl Cloth | White | 1.000 (25.4)               | 0.500 (12.7)                | -                            | 0.600 (15.2)                | 1.200 (30.5)             | 1                 | 10,000            | R6206          |
| Fig. 1                                                                                                                                                                                                                                           | THT-88-498-5       | Vinyl Cloth | White | 1.000 (25.4)               | 0.750 (19.1)                | 1.100 (27.9)                 | 0.875 (22.2)                | 2.300 (58.4)             | 2                 | 5,000             | R6200          |
| Fig. 1                                                                                                                                                                                                                                           | THT-89-498-5       | Vinyl Cloth | White | 1.000 (25.4)               | 1.440 (36.5)                | 1.100 (27.9)                 | 1.562 (39.7)                | 3.400 (86.4)             | 3                 | 5,000             | R6207          |
| Fig. 2                                                                                                                                                                                                                                           | THT-199-498-3      | Vinyl Cloth | White | 1.050 (26.7)               | 0.250 (6.4)                 | -                            | 0.350 (8.9)                 | 1.250 (31.8)             | 1                 | 3,000             | R6206          |
| Fig. 2                                                                                                                                                                                                                                           | THT-17-498-3       | Vinyl Cloth | White | 2.000 (50.8)               | 1.000 (25.4)                | -                            | 1.125 (28.6)                | 2.200 (55.9)             | 1                 | 3,000             | R6200          |
| <b>NOTICE BBP®11 PRINTER ONLY:</b> The following part numbers ending with "-SC" are 1" Small Core Rolls specially designed for use in the BBP11 Printer and do not require the BBP11 media adaptor accessory. View page 82 for more information. |                    |             |       |                            |                             |                              |                             |                          |                   |                   |                |
| Fig. 1                                                                                                                                                                                                                                           | THT-90-498-2.5-SC  | Vinyl Cloth | White | 0.250 (6.4)                | 1.437 (36.5)                | 0.350 (8.9)                  | 1.562 (39.7)                | 2.200 (55.9)             | 6                 | 2,500             | R6213          |
| Fig. 3                                                                                                                                                                                                                                           | THT-92-498-SC      | Vinyl Cloth | White | 0.375 (9.5)                | 165 ft (50.8 m)             | -                            | -                           | 1.000 (25.4)             | 1                 | 1 Roll Cont.      | R6213          |
| Fig. 1                                                                                                                                                                                                                                           | THT-68-498-5-SC    | Vinyl Cloth | White | 0.500 (12.7)               | 0.750 (19.1)                | 0.600 (15.2)                 | 0.850 (21.6)                | 2.500 (63.5)             | 4                 | 5,000             | R6213          |
| Fig. 1                                                                                                                                                                                                                                           | THT-14-498-5-SC    | Vinyl Cloth | White | 0.650 (16.5)               | 0.200 (5.1)                 | 0.700 (17.8)                 | 0.300 (7.6)                 | 2.950 (74.9)             | 4                 | 5,000             | R6213          |
| Fig. 1                                                                                                                                                                                                                                           | THT-1-498-5-SC     | Vinyl Cloth | White | 0.750 (19.1)               | 0.250 (6.4)                 | 0.800 (20.3)                 | 0.350 (8.9)                 | 3.350 (85.1)             | 4                 | 5,000             | R6213          |
| Fig. 1                                                                                                                                                                                                                                           | THT-91-498-2.5-SC  | Vinyl Cloth | White | 0.750 (19.1)               | 0.937 (23.8)                | 0.875 (22.2)                 | 1.062 (27.0)                | 3.500 (88.9)             | 4                 | 2,500             | R6213          |
| Fig. 1                                                                                                                                                                                                                                           | THT-165-498-2.5-SC | Vinyl Cloth | White | 0.800 (20.3)               | 1.437 (36.5)                | 0.900 (22.9)                 | 1.562 (39.7)                | 3.700 (94.0)             | 4                 | 2,500             | R6213          |
| Fig. 1                                                                                                                                                                                                                                           | THT-95-498-2.5-SC  | Vinyl Cloth | White | 0.800 (20.3)               | 1.437 (36.5)                | 0.900 (22.9)                 | 1.562 (39.7)                | 2.800 (71.1)             | 3                 | 2,500             | R6213          |
| Fig. 1                                                                                                                                                                                                                                           | THT-88-498-2.5-SC  | Vinyl Cloth | White | 1.000 (25.4)               | 0.750 (19.1)                | 1.100 (27.9)                 | 0.875 (22.2)                | 2.300 (58.4)             | 2                 | 2,500             | R6213          |
| Fig. 2                                                                                                                                                                                                                                           | THT-199-498-3-SC   | Vinyl Cloth | White | 1.050 (26.7)               | 0.250 (6.4)                 | -                            | 0.350 (8.9)                 | 1.250 (31.8)             | 1                 | 3,000             | R6213          |
| Fig. 2                                                                                                                                                                                                                                           | THT-17-498-1.5-SC  | Vinyl Cloth | White | 2.000 (50.8)               | 1.000 (25.4)                | -                            | 1.125 (28.6)                | 2.200 (55.9)             | 1                 | 1,500             | R6213          |



### Did You Know? - Technical Data Sheets

Looking for more information regarding a certain Brady material?

Brady offers online access to Technical Data Sheets for all Brady materials. View by a specific B-Number or search by relevant keywords.

Visit [www.BradyID.com/techdata](http://www.BradyID.com/techdata) for more information.

