

**General ordering data**

Order No.	0294360000
Part designation	AKZ 4
Version	Feed-through terminal, 4 mm ² , Screw connection, Polyamide, beige, TS 15
EAN	4008190054625
Qty.	100 pc(s).

Product notes

Note, ordering data	AKZ 4 order no. 0294360000 and 0294380000 made of PA with flammability class acc. to UL 94/V-2
---------------------	--

PT OKIECEx/ATEX rating data

EU-type examination certificate	SIRA02ATEX3001U
Download English	SIRA02ATEX3001U_e.pdf
IECEx Certificate of Conformity	IECEXSIR05.0038U
Download	IECEXSIR05.0038U_e.pdf
ATEX voltage	275 V
ATEX current	28 A
ATEX conductor cross-section	4 mm ²
IECEx voltage	275 V
IECEx current	28 A
IECEx conductor cross-section	4 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	beige
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 15
Insulating material	Polyamide
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1

Additional technical data

No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 100 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V2
Version	Feed-through terminal

CSA rating data

Voltage (CSA)	300 V
CSA current	10 A
Min. cross-section (CSA)	AWG 24
Max. cross-section (CSA)	AWG 12

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	4 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	2
Stripping length	8 mm
Clamping screw	M 3
Blade size	0.6 x 3.5 mm
Tightening torque range	0.6...0.8 Nm
Torque level with DMS electric screwdriver	2
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm ²
Solid, max.	6 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	2.5 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	2.5 mm ²
Twin wire-end ferrule, min.	0.5 mm ²
Twin wire end ferrule, max.	1.5 mm ²
AWG conductor size, min.	AWG 24
AWG conductor size, max.	AWG 12
AWG conductor size, min.	0.21 mm ²
AWG conductor size, max.	3.31 mm ²

Conductors for clamping (rated connection)**Dimensions**

Width	6.1 mm
Height of lowest version	30.5 mm
Length	27 mm
Weight	5.93 g
TS 15 offset	13.5 mm

Disconnect terminals

Torque level with DMS electric screwdriver	2
--	---

Rating data

Rated cross-section	4 mm ²
Rated voltage	400 V
Rated impulse voltage	6 kV
Rated current	32 A
Standards	IEC 60947-7-1
Current with max. conductor	41 A
Pollution severity	3

UL rating data

Voltage (UL)	300 V
Current (UL)	27 A
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 12

Approvals

Approvals institutes

**Classifications**

ETIM 2.0	EC001283
ETIM 3.0	EC001283
eClass 4.1	27-14-11-20
eClass 5.0	27-14-11-20
eClass 5.1	27-14-11-20

Similar products

Order No.	Part designation	Version
0340460000	AKZ 1.5	Feed-through terminal, 1.5 mm ² , Screw connection, Polyamide, beige, TS 15
0340480000	AKZ 1.5 BL	Feed-through terminal, 1.5 mm ² , Screw connection, Polyamide, blue, TS 15
0697160000	AKZ 2.5	Feed-through terminal, 2.5 mm ² , Screw connection, PA 66, beige, TS 15
0697180000	AKZ 2.5 BL	Feed-through terminal, 2.5 mm ² , Screw connection, PA 66, blue, TS 15
0294380000	AKZ 4 BL	Feed-through terminal, 4 mm ² , Screw connection, Polyamide, blue, TS 15