


Model 4778 Cable Assembly Micrograbber® Breakouts To Bantam Plug



MATERIALS:

Connector: 1st End - Micrograbber® Breakouts

Contact – Beryllium Copper, Alloy 165

Spring – Stainless Steel, 302

Finish: Contact – Gold plated per MIL-G-45204, Type II, Class 00.

Insulation: Glass filled nylon. Color matches color of wire.

Marking: “POMONA ELECTRONICS” “MICROGRABBER®”

Wire: 20 AWG, stranding 41 x 36 tc., PVC insulated, 2.21 (.087) O.D.

Color: One red and one black, red lead connected to tip, black lead connected to ring.

Molded Breakout: PVC molded to breakout leads and cable. Color: Gray

Cable: 2 Conductor shielded stranded copper, 26 AWG, PVC insulated, 4.57 (.180) O.D. Color: Gray

Marking: “POMONA ELECTRONICS 4778-60”

Connector: 2nd End – Brass Bantam Plug (Miniature Phone Plug)

Insulation: PVC. Color: Black

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 150 VRMS

ORDERING INFORMATION: Model 4778-60

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA