

[Home](#) - [Distributor Area](#) - [Distributors](#) - [Support](#) - [Jobs](#) - [Contact](#)Choose your language:  English (US) 

Search Product:

[\[ Advanced \]](#)[SECURITY PRODUCTS](#) > [COLOR CAMERAS](#) > [COLOR CAMERAS WITH HOUSING](#) > [COLOR CAMERAS WITH HOUSING, WITH AUDIO](#) >

## MINI HIGH RESOLUTION VIDEO, PICTURE AND AUDIO CAPTURE COLOR CAMERA

Order Code: CAMCOLVC2N



### Features

- [Adapters & power supplies](#)
- [Batteries & chargers](#)
- [Cables & accessories](#)
- [Connectors](#)
- [Consumer products & pc acc.](#)
- [Electronic components](#)
- [High-q tools & dmm's](#)
- [Lamps & led's](#)
- [Led products & lamps](#)
- [Light products](#)
- [Loudspeakers & pa systems](#)
- [Perel tools](#)
- [Security products](#)
- [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

### Specifications

- pick-up element: colour CMOS sensor
- lens angle: 58° (diagonal)
- storage capacity: max. 8GB micro SD card (not incl.)
- video recording:
  - recording format: AVI (audio and video)
  - video resolution: 640 x 480 pixels
  - frame rate (fps): 29
  - recording capacity: ±40MB/min
- audio recording:
  - recording format: WAV
  - audio sample rate: 8kHz
  - recording capacity: ±500kB/min
- image recording:
  - recording format: JPEG
  - image resolution: 1280 x 960 pixels
- power supply: built-in Li-battery (recharge via USB)

- battery capacity: 1.5h
- charging time: 2h
- current consumption: max. 140mA
- dimensions: 2 7/8" x 25/32" x 7/16"
- weight: 0.74 oz
- operating temperature: 32°F ~ 122°F

## Files

---

- [EN](#) - [FR](#) - [NL](#) - [ES](#) - [DE](#) - [IT](#) - [PL](#)

## Stock Info

---

- Inner carton:
- Outer Carton: 100
- EAN Barcode: 5410329422905
- UPC Barcode:
- Packaging:

(C) 2005 Velleman Components N.V.  
[ [Disclaimer](#) ]