






Dimensions: mm (In.)



Circuit Diagram



PCB Layout



Electrical Specifications:

- Rating: Non-Switching-100mA/50VDC
Switching-25mA/24VDC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 100MΩ min.
- Dielectric Strength: 500VAC for 1 min.

Mechanical Specifications:

- Operating Temperature: -20° C~+70° C
- Storage Temperature: -40° C~+85° C
- Tolerance: ±0.20mm

Note:

- RoHS compliant and process compatible with 260° solder

Slide Switch (SMT)
103-5034-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-5034-EV](#)