

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	86				T	REV / 0G10-0059-99	26APR99	ME/TM

D

C

B

A


D

C


B

A

328141



1 CIRCULAR MIL AREA RANGE: 20,800-33,100 CM
2 TIN PL 0.00381[.000150] MIN THK PER ASTM B 545



				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51[.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-152	DR 03/09/90 DK SCHRUM		AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK 19JAN95 MS FEHER				
	APPD 19JAN95 WJ VOCKROTH				
FINISH 2	APPD 19JAN95 TL SHUTTER		NAME TERMINAL, AMPPOWER™, WIRE SIZE: 6 AWG		
	PRODUCT SPEC 108-30200				
	APPLICATION SPEC -				
WEIGHT .016 LB		SIZE C	CAGE CODE 00779	DRAWING NO 328141	
		SCALE 4:1		SHEET 1 OF 1	