

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300400006](#)
Status: **Active**
Overview: [minichange_products](#)
Description: Ultra-Lock® Single-Ended Cordset, Female - Pigtail, Straight, 4 Poles, Length 0.50m (1.63'), Stainless Steel Shell, PVC Wire Leads

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	130040
Connector End A	Ultra-Lock® (M12)
Connector End B	Pigtail
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	minichange_products
Product Name	Mini-Change®
Type	Single Ended

Physical

Cable Diameter	N/A
Cable Length	0.50m (1.64')
Color - Cable Jacket	Yellow
Coupling Style	Push to Lock
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper
Material - Coupling Nut	Stainless Steel Type 316
Material - Plating Mating	Gold
Orientation	Straight
Poles	4
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	18
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	4A
Voltage - Maximum	250V

Material Info

Old Part Number	WR4000A42M0058
-----------------	----------------

Reference - Drawing Numbers

Sales Drawing	SD-130040-004
---------------	---------------

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130040Series](#)