

**THOUSANDS** OF APPLICATIONS.  
**HUNDREDS** OF LABELS.  
**ONE** LABEL PRINTER.



**BMP® 71** LABEL PRINTER



# THE ONE WAY TO

## BMP®71 LABEL PRINTER

The best features and functionalities of Brady's portable label printers are now combined into one easy-to-use, top-of-the-line portable thermal transfer printer – Brady's NEW BMP®71 printer. Whether you need ¼" self-laminating wire marker labels or 2" wide vinyl pipe marker labels, you only need ONE label maker - the BMP®71 printer can do it all!

### SAVE TIME WITH FOOLPROOF LABEL DESIGN AND HIGH SPEED PRINT

The BMP71 printer is designed to help you get your job done quickly and efficiently – and that means making labels fast. At 1.5" per second, the BMP71 printer has the fastest print speed on the portable printer market.

But that's not all. With built-in design wizards, material-recognition technology and storage space for over 100,000 label files, this printer can cut your label design time in half.

#### Label Design Wizards Available For:

- Electrical
- Voice/Data Comm
- Safety/General ID



### CUT MATERIAL WASTE - PREVIEW LABELS BEFORE YOU PRINT!

With a large, full color graphical screen, the BMP71 printer shows you exactly what your label will look like as you're creating it – so there's no guesswork. You can stop wasting label material on "test labels" and start saving time and money by creating a label once – knowing it's correct before you even hit "Print."

#### The display includes:

- Label material and ribbon part number
- Label color and size (including the amount of remaining material)
- Font size, bold and other type functions
- Application templates
- Multi-area print areas
- Remaining battery charge



# FASTER, EASIER LABEL PRINTING



## ENHANCE YOUR LABELS WITH ADVANCED GRAPHICS AND SYMBOLS

With hundreds of symbols and graphics, the BMP71 printer can transform your labels from basic text messages to highly effective communication vehicles.

For lean enterprises, Brady's MarkWare™ software provides additional graphics and templates for signs, labels, pipe markers and tags - perfect for 5S, TPM and lean visuals.

## EASY WAY TO CREATE LABELS ON YOUR PC

Brady's LabelMark™ software lets you easily create labels for asset id, component marking, voice / data comm labeling, wire markers and more. LabelMark software is completely integrated with Microsoft Office, AutoCAD applications and more.

**Coming soon** ---- Create labels on your PC, download them to the BMP71 printer and print with the new LabelMark v.5.1 software. Edit your files on the BMP®71 Label Printer and transfer them back into LabelMark software.


### Other Features Include:

- |                      |                  |                    |                               |
|----------------------|------------------|--------------------|-------------------------------|
| ■ 100's Of Symbols   | ■ Frame          | ■ Expand/Condense  | ■ Multiple Areas On One Label |
| ■ Reverse Print      | ■ Mirror Print   | ■ Time/Date Stamps | ■ Barcodes                    |
| ■ Multiple Font Size | ■ Auto Font Size | ■ Underline        | ■ Sequences                   |
| ■ Subscripts         | ■ Vertical       | ■ Italics/Bold     |                               |



### WATCH A DEMO VIDEO AT:

[www.BradyID.com/bmp71](http://www.BradyID.com/bmp71)  
[www.BradyCanada.ca/bmp71](http://www.BradyCanada.ca/bmp71)



# ONE SOURCE FOR LABEL MATERIALS

The BMP®71 Label Printer can print on over 400 label parts - so whatever label size or color you need, we've got you covered. Add all of the materials from the TLS 2200® Thermal Transfer Printer and the HandiMark® Portable Label Maker, and your label options are endless!

## General Industrial, Lean & Safety

Indoor/outdoor pliable vinyl conforms to smooth or rough surfaces such as pipes, walls, doors, panels, shelving, bins, and equipment. Aggressive permanent adhesive; labels offer excellent resistance to oils, detergents, dirt, grime, and many solvents.




Figure 8



### Indoor/Outdoor Grade Vinyl Tape

| Diagram | Part Number      | Labels/Roll    | Material | Color      | Label Dimensions |         |        |           | Recommended Ribbon | Price   |
|---------|------------------|----------------|----------|------------|------------------|---------|--------|-----------|--------------------|---------|
|         |                  |                |          |            | A Inch           | (mm)    | B Inch | (mm)      |                    |         |
| Fig. 8  | M71C-500-595-BK  | 1 Roll (cont.) | B-595    | Black      | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$43.88 |
| Fig. 8  | M71C-500-595-BL  | 1 Roll (cont.) | B-595    | Blue       | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$43.88 |
| Fig. 8  | M71C-500-595-BR  | 1 Roll (cont.) | B-595    | Brown      | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-CL  | 1 Roll (cont.) | B-595    | Clear      | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-GD  | 1 Roll (cont.) | B-595    | Gold       | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-GN  | 1 Roll (cont.) | B-595    | Green      | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$43.88 |
| Fig. 8  | M71C-500-595-GY  | 1 Roll (cont.) | B-595    | Grey       | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-LB  | 1 Roll (cont.) | B-595    | Light Blue | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-OC  | 1 Roll (cont.) | B-595    | Ochre      | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-OR  | 1 Roll (cont.) | B-595    | Orange     | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-PK  | 1 Roll (cont.) | B-595    | Pink       | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-PL  | 1 Roll (cont.) | B-595    | Purple     | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-RD  | 1 Roll (cont.) | B-595    | Red        | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$43.88 |
| Fig. 8  | M71C-500-595-SB  | 1 Roll (cont.) | B-595    | Sky Blue   | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-TN  | 1 Roll (cont.) | B-595    | Tan        | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-WT  | 1 Roll (cont.) | B-595    | White      | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-500-595-YL  | 1 Roll (cont.) | B-595    | Yellow     | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$43.88 |
| Fig. 8  | M71C-1000-595-BK | 1 Roll (cont.) | B-595    | Black      | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$61.21 |
| Fig. 8  | M71C-1000-595-BL | 1 Roll (cont.) | B-595    | Blue       | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$61.21 |
| Fig. 8  | M71C-1000-595-BR | 1 Roll (cont.) | B-595    | Brown      | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-CL | 1 Roll (cont.) | B-595    | Clear      | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-GD | 1 Roll (cont.) | B-595    | Gold       | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-GN | 1 Roll (cont.) | B-595    | Green      | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$61.21 |
| Fig. 8  | M71C-1000-595-GY | 1 Roll (cont.) | B-595    | Grey       | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-LB | 1 Roll (cont.) | B-595    | Light Blue | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-OC | 1 Roll (cont.) | B-595    | Ochre      | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-OR | 1 Roll (cont.) | B-595    | Orange     | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-PK | 1 Roll (cont.) | B-595    | Pink       | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-PL | 1 Roll (cont.) | B-595    | Purple     | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-RD | 1 Roll (cont.) | B-595    | Red        | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$61.21 |
| Fig. 8  | M71C-1000-595-SB | 1 Roll (cont.) | B-595    | Sky Blue   | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-TN | 1 Roll (cont.) | B-595    | Tan        | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-WT | 1 Roll (cont.) | B-595    | White      | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-1000-595-YL | 1 Roll (cont.) | B-595    | Yellow     | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$61.21 |
| Fig. 8  | M71C-2000-595-BK | 1 Roll (cont.) | B-595    | Black      | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$91.85 |
| Fig. 8  | M71C-2000-595-BL | 1 Roll (cont.) | B-595    | Blue       | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$91.85 |
| Fig. 8  | M71C-2000-595-BR | 1 Roll (cont.) | B-595    | Brown      | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-CL | 1 Roll (cont.) | B-595    | Clear      | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-GD | 1 Roll (cont.) | B-595    | Gold       | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-GN | 1 Roll (cont.) | B-595    | Green      | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$91.85 |
| Fig. 8  | M71C-2000-595-GY | 1 Roll (cont.) | B-595    | Grey       | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-LB | 1 Roll (cont.) | B-595    | Light Blue | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-OC | 1 Roll (cont.) | B-595    | Ochre      | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-OR | 1 Roll (cont.) | B-595    | Orange     | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-PK | 1 Roll (cont.) | B-595    | Pink       | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-PL | 1 Roll (cont.) | B-595    | Purple     | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-RD | 1 Roll (cont.) | B-595    | Red        | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R4400-WT       | \$91.85 |
| Fig. 8  | M71C-2000-595-SB | 1 Roll (cont.) | B-595    | Sky Blue   | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-TN | 1 Roll (cont.) | B-595    | Tan        | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-WT | 1 Roll (cont.) | B-595    | White      | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |
| Fig. 8  | M71C-2000-595-YL | 1 Roll (cont.) | B-595    | Yellow     | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$91.85 |

\* See all ribbon colors on page 14.

## General Industrial, Lean & Safety (Continued)

### Pre-Printed Die Cut Labels




Figure 4




Figure 8




Figure 27




Figure 28




Figure 30

| Diagram | Part Number     | Labels/Roll | Material | Color | Label Dimensions |          |        |         | Recommended Ribbon | Price   |
|---------|-----------------|-------------|----------|-------|------------------|----------|--------|---------|--------------------|---------|
|         |                 |             |          |       | A Inch           | (mm)     | B Inch | (mm)    |                    |         |
| Fig. 28 | M71-30-423-TEST | 250         | B-423    | White | 1.50             | (38.10)  | 0.75   | (19.05) | M71-R6000          | \$35.79 |
| Fig. 27 | M71-30-428-CALI | 250         | B-428    | White | 1.50             | (38.10)  | 0.75   | (19.05) | M71-R4300          | \$57.06 |
| Fig. 30 | M71-35-428-PROP | 250         | B-428    | White | 1.63             | (41.40)  | 0.75   | (19.05) | M71-R4300          | \$57.06 |
| Fig. 4  | M71-38-483-CAUT | 100         | B-483    | White | 4.00             | (101.60) | 1.90   | (48.26) | M71-R6000          | \$53.67 |
| Fig. 4  | M71-38-483-DANG | 100         | B-483    | White | 4.00             | (101.60) | 1.90   | (48.26) | M71-R6000          | \$53.67 |
| Fig. 4  | M71-38-483-NOTI | 100         | B-483    | White | 4.00             | (101.60) | 1.90   | (48.26) | M71-R6000          | \$53.67 |
| Fig. 4  | M71-38-483-WARN | 100         | B-483    | White | 4.00             | (101.60) | 1.90   | (48.26) | M71-R6000          | \$53.67 |

### Specialty Continuous Tape

| Diagram | Part Number   | Labels/Roll    | Material | Color  | Label Dimensions |         |        |           | Recommended Ribbon | Price   |
|---------|---------------|----------------|----------|--------|------------------|---------|--------|-----------|--------------------|---------|
|         |               |                |          |        | A Inch           | (mm)    | B Inch | (mm)      |                    |         |
| Fig. 8  | M71C-500-428  | 1 Roll (cont.) | B-428    | Silver | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R4300          | \$59.50 |
| Fig. 8  | M71C-1000-529 | 1 Roll (cont.) | B-529    | White  | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$47.89 |
| Fig. 8  | M71C-2000-529 | 1 Roll (cont.) | B-529    | White  | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$66.54 |

## Control Panel/Raised Panel

Customized legend plates with less hassle and time than engraved plates. Brady Raised Panel Labels are RoHS compliant and UL approved. Aggressive adhesive and solvent resistant.




Figure 4




Figure 25



### Pre-Printed Die Cut Labels

| Diagram | Part Number      | Labels/Roll | Material | Color  | Label Dimensions |          |        |         | Recommended Ribbon | Price    |
|---------|------------------|-------------|----------|--------|------------------|----------|--------|---------|--------------------|----------|
|         |                  |             |          |        | A Inch           | (mm)     | B Inch | (mm)    |                    |          |
| Fig. 4  | M71EP-171-593    | 200         | B-593    | White  | 1.06             | (26.92)  | 0.49   | (12.45) | M71-R6000          | \$99.95  |
| Fig. 4  | M71EP-171-593-BK | 200         | B-593    | Black  | 1.06             | (26.92)  | 0.49   | (12.45) | M71-R4400-WT       | \$99.95  |
| Fig. 4  | M71EP-171-593-GN | 200         | B-593    | Green  | 1.06             | (26.92)  | 0.49   | (12.45) | M71-R4400-WT       | \$99.95  |
| Fig. 4  | M71EP-171-593-RD | 200         | B-593    | Red    | 1.06             | (26.92)  | 0.49   | (12.45) | M71-R4400-WT       | \$99.95  |
| Fig. 4  | M71EP-171-593-SL | 200         | B-593    | Silver | 1.06             | (26.92)  | 0.49   | (12.45) | M71-R6000          | \$99.95  |
| Fig. 4  | M71EP-171-593-YL | 200         | B-593    | Yellow | 1.06             | (26.92)  | 0.49   | (12.45) | M71-R6000          | \$99.95  |
| Fig. 25 | M71EP-167-593    | 100         | B-593    | White  | 1.20             | (30.48)  | 1.50   | (38.10) | M71-R6000          | \$89.95  |
| Fig. 25 | M71EP-167-593-BK | 100         | B-593    | Black  | 1.20             | (30.48)  | 1.50   | (38.10) | M71-R4400-WT       | \$89.95  |
| Fig. 25 | M71EP-167-593-GN | 100         | B-593    | Green  | 1.20             | (30.48)  | 1.50   | (38.10) | M71-R4400-WT       | \$89.95  |
| Fig. 25 | M71EP-167-593-RD | 100         | B-593    | Red    | 1.20             | (30.48)  | 1.50   | (38.10) | M71-R4400-WT       | \$89.95  |
| Fig. 25 | M71EP-167-593-YL | 100         | B-593    | Yellow | 1.20             | (30.48)  | 1.50   | (38.10) | M71-R6000          | \$89.95  |
| Fig. 25 | M71EP-168-593    | 100         | B-593    | White  | 1.20             | (30.48)  | 1.90   | (48.26) | M71-R6000          | \$99.95  |
| Fig. 25 | M71EP-168-593-BK | 100         | B-593    | Black  | 1.20             | (30.48)  | 1.90   | (48.26) | M71-R4400-WT       | \$99.95  |
| Fig. 25 | M71EP-168-593-GN | 100         | B-593    | Green  | 1.20             | (30.48)  | 1.90   | (48.26) | M71-R4400-WT       | \$99.95  |
| Fig. 25 | M71EP-168-593-RD | 100         | B-593    | Red    | 1.20             | (30.48)  | 1.90   | (48.26) | M71-R4400-WT       | \$99.95  |
| Fig. 25 | M71EP-168-593-YL | 100         | B-593    | Yellow | 1.20             | (30.48)  | 1.90   | (48.26) | M71-R6000          | \$99.95  |
| Fig. 25 | M71EP-169-593    | 100         | B-593    | White  | 1.80             | (45.72)  | 1.80   | (45.72) | M71-R6000          | \$105.95 |
| Fig. 25 | M71EP-169-593-BK | 100         | B-593    | Black  | 1.80             | (45.72)  | 1.80   | (45.72) | M71-R4400-WT       | \$105.95 |
| Fig. 25 | M71EP-169-593-GN | 100         | B-593    | Green  | 1.80             | (45.72)  | 1.80   | (45.72) | M71-R4400-WT       | \$105.95 |
| Fig. 25 | M71EP-169-593-RD | 100         | B-593    | Red    | 1.80             | (45.72)  | 1.80   | (45.72) | M71-R4400-WT       | \$105.95 |
| Fig. 25 | M71EP-169-593-YL | 100         | B-593    | Yellow | 1.80             | (45.72)  | 1.80   | (45.72) | M71-R6000          | \$105.95 |
| Fig. 4  | M71EP-173-593    | 100         | B-593    | White  | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R6000          | \$75.95  |
| Fig. 4  | M71EP-173-593-BK | 100         | B-593    | Black  | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R4400-WT       | \$75.95  |
| Fig. 4  | M71EP-173-593-GN | 100         | B-593    | Green  | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R4400-WT       | \$75.95  |
| Fig. 4  | M71EP-173-593-RD | 100         | B-593    | Red    | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R4400-WT       | \$75.95  |
| Fig. 4  | M71EP-173-593-SL | 100         | B-593    | Silver | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R6000          | \$75.95  |
| Fig. 4  | M71EP-173-593-YL | 100         | B-593    | Yellow | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R6000          | \$75.95  |
| Fig. 4  | M71EP-176-593    | 50          | B-593    | White  | 3.00             | (76.20)  | 1.00   | (25.40) | M71-R6000          | \$59.95  |
| Fig. 4  | M71EP-176-593-BK | 50          | B-593    | Black  | 3.00             | (76.20)  | 1.00   | (25.40) | M71-R4400-WT       | \$59.95  |
| Fig. 4  | M71EP-176-593-GN | 50          | B-593    | Green  | 3.00             | (76.20)  | 1.00   | (25.40) | M71-R4400-WT       | \$59.95  |
| Fig. 4  | M71EP-176-593-RD | 50          | B-593    | Red    | 3.00             | (76.20)  | 1.00   | (25.40) | M71-R4400-WT       | \$59.95  |
| Fig. 4  | M71EP-176-593-YL | 50          | B-593    | Yellow | 3.00             | (76.20)  | 1.00   | (25.40) | M71-R6000          | \$59.95  |
| Fig. 4  | M71EP-174-593    | 50          | B-593    | White  | 4.00             | (101.60) | 1.00   | (25.40) | M71-R6000          | \$75.95  |
| Fig. 4  | M71EP-174-593-BK | 50          | B-593    | Black  | 4.00             | (101.60) | 1.00   | (25.40) | M71-R4400-WT       | \$75.95  |
| Fig. 4  | M71EP-174-593-GN | 50          | B-593    | Green  | 4.00             | (101.60) | 1.00   | (25.40) | M71-R4400-WT       | \$75.95  |
| Fig. 4  | M71EP-174-593-RD | 50          | B-593    | Red    | 4.00             | (101.60) | 1.00   | (25.40) | M71-R4400-WT       | \$75.95  |
| Fig. 4  | M71EP-174-593-SL | 50          | B-593    | Silver | 4.00             | (101.60) | 1.00   | (25.40) | M71-R6000          | \$75.95  |
| Fig. 4  | M71EP-174-593-YL | 50          | B-593    | Yellow | 4.00             | (101.60) | 1.00   | (25.40) | M71-R6000          | \$75.95  |

\* See all ribbon colors on page 14.

## General Labels/Rating Plates

Choose from several materials with aggressive adhesives for use in commercial/industrial applications.




Figure 4




Figure 8




Figure 14



### Die Cut Labels

| Diagram | Part Number | Labels/Roll | Material | Color  | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)    | Recommended Ribbon | Price   |
|---------|-------------|-------------|----------|--------|--------|--------------------------|--------|---------|--------------------|---------|
| Fig. 4  | M71-68-430  | 750         | B-430    | Clear  | 0.24   | (6.00)                   | 0.15   | (3.81)  | M71-R6000          | \$30.18 |
| Fig. 4  | M71-71-430  | 750         | B-430    | Clear  | 0.35   | (8.89)                   | 0.20   | (5.08)  | M71-R6000          | \$30.18 |
| Fig. 14 | M71-80-488  | 250         | B-488    | White  | 0.75   | (19.05)                  | 0.90   | (22.86) | M71-R4300          | \$25.30 |
| Fig. 4  | M71-97-488  | 250         | B-488    | White  | 0.90   | (22.86)                  | 0.90   | (22.86) | M71-R4300          | \$27.00 |
| Fig. 4  | M71-16-430  | 500         | B-430    | Clear  | 1.00   | (25.40)                  | 0.38   | (9.53)  | M71-R6000          | \$43.13 |
| Fig. 4  | M71-17-430  | 500         | B-430    | Clear  | 1.00   | (25.40)                  | 0.50   | (12.70) | M71-R6000          | \$43.13 |
| Fig. 4  | M71-16-483  | 500         | B-483    | White  | 1.00   | (25.40)                  | 0.38   | (9.53)  | M71-R6000          | \$47.77 |
| Fig. 4  | M71-17-483  | 500         | B-483    | White  | 1.00   | (25.40)                  | 0.50   | (12.70) | M71-R6000          | \$48.75 |
| Fig. 4  | M71-19-483  | 250         | B-483    | White  | 1.00   | (25.40)                  | 1.00   | (25.40) | M71-R6000          | \$34.33 |
| Fig. 4  | M71-17-486  | 500         | B-486    | Silver | 1.00   | (25.40)                  | 0.50   | (12.70) | M71-R4300          | \$55.95 |
| Fig. 4  | M71-45-430  | 500         | B-430    | Clear  | 1.05   | (38.10)                  | 0.38   | (9.53)  | M71-R6000          | \$45.08 |
| Fig. 4  | M71-65-483  | 250         | B-483    | White  | 1.38   | (34.93)                  | 1.00   | (25.40) | M71-R6000          | \$30.42 |
| Fig. 4  | M71-29-459  | 500         | B-459    | White  | 1.50   | (38.10)                  | 0.50   | (12.70) | M71-R6000          | \$43.85 |
| Fig. 4  | M71-30-459  | 250         | B-459    | White  | 1.50   | (38.10)                  | 0.75   | (19.05) | M71-R6000          | \$38.36 |
| Fig. 4  | M71-29-483  | 500         | B-483    | White  | 1.50   | (38.10)                  | 0.50   | (12.70) | M71-R6000          | \$54.12 |
| Fig. 4  | M71-30-483  | 250         | B-483    | White  | 1.50   | (38.10)                  | 0.75   | (19.05) | M71-R6000          | \$46.53 |
| Fig. 4  | M71-31-483  | 250         | B-483    | White  | 1.50   | (38.10)                  | 1.00   | (25.40) | M71-R6000          | \$38.85 |
| Fig. 4  | M71-29-486  | 500         | B-486    | Silver | 1.50   | (38.10)                  | 0.50   | (12.70) | M71-R4300          | \$64.38 |
| Fig. 4  | M71-30-486  | 250         | B-486    | Silver | 1.50   | (38.10)                  | 0.75   | (19.05) | M71-R4300          | \$52.77 |
| Fig. 4  | M71-29-489  | 500         | B-489    | White  | 1.50   | (38.10)                  | 0.50   | (12.70) | M71-R4300          | \$53.26 |
| Fig. 4  | M71-32-489  | 250         | B-489    | White  | 1.50   | (38.10)                  | 1.50   | (38.10) | M71-R4300          | \$54.37 |
| Fig. 4  | M71-81-488  | 750         | B-488    | White  | 1.90   | (48.26)                  | 0.25   | (6.35)  | M71-R4300          | \$61.45 |
| Fig. 4  | M71-20-459  | 100         | B-459    | White  | 2.00   | (50.80)                  | 1.00   | (25.40) | M71-R6000          | \$23.45 |
| Fig. 4  | M71-61-483  | 100         | B-483    | White  | 2.00   | (50.80)                  | 0.50   | (12.70) | M71-R6000          | \$17.46 |
| Fig. 4  | M71-20-483  | 100         | B-483    | White  | 2.00   | (50.80)                  | 1.00   | (25.40) | M71-R6000          | \$26.52 |
| Fig. 4  | M71-20-486  | 100         | B-486    | Silver | 2.00   | (50.80)                  | 1.00   | (25.40) | M71-R4300          | \$34.33 |
| Fig. 4  | M71-37-483  | 100         | B-483    | White  | 3.00   | (76.20)                  | 1.90   | (48.26) | M71-R6000          | \$38.85 |
| Fig. 4  | M71-37-486  | 100         | B-486    | Silver | 3.00   | (76.20)                  | 1.90   | (48.26) | M71-R4300          | \$49.49 |
| Fig. 4  | M71-23-483  | 100         | B-483    | White  | 4.00   | (101.60)                 | 1.00   | (25.40) | M71-R6000          | \$40.19 |
| Fig. 4  | M71-38-483  | 100         | B-483    | White  | 4.00   | (101.60)                 | 1.90   | (48.26) | M71-R6000          | \$46.67 |
| Fig. 4  | M71-38-489  | 100         | B-489    | White  | 4.00   | (101.60)                 | 1.90   | (48.26) | M71-R4300          | \$46.67 |

### Specialty Continuous Tape

| Diagram | Part Number   | Labels/Roll    | Material | Color | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)      | Recommended Ribbon | Price    |
|---------|---------------|----------------|----------|-------|--------|--------------------------|--------|-----------|--------------------|----------|
| Fig. 8  | M71C-375-430  | 1 Roll (cont.) | B-430    | Clear | 0.38   | (9.53)                   | 50 ft. | (15.24 m) | M71-R6000          | \$50.46  |
| Fig. 8  | M71C-500-430  | 1 Roll (cont.) | B-430    | Clear | 0.50   | (12.70)                  | 50 ft. | (15.24 m) | M71-R6000          | \$50.46  |
| Fig. 8  | M71C-500-483  | 1 Roll (cont.) | B-483    | White | 0.50   | (12.70)                  | 50 ft. | (15.24 m) | M71-R6000          | \$56.94  |
| Fig. 8  | M71C-1000-430 | 1 Roll (cont.) | B-430    | Clear | 1.00   | (25.40)                  | 50 ft. | (15.24 m) | M71-R6000          | \$69.64  |
| Fig. 8  | M71C-1000-483 | 1 Roll (cont.) | B-483    | White | 1.00   | (25.40)                  | 50 ft. | (15.24 m) | M71-R6000          | \$78.80  |
| Fig. 8  | M71C-1900-430 | 1 Roll (cont.) | B-430    | Clear | 1.90   | (48.26)                  | 50 ft. | (15.24 m) | M71-R6000          | \$104.22 |
| Fig. 8  | M71C-1900-483 | 1 Roll (cont.) | B-483    | White | 1.90   | (48.26)                  | 50 ft. | (15.24 m) | M71-R6000          | \$117.40 |

\* See all ribbon colors on page 14.




**REQUEST A SAMPLE PACK AT:**  
[www.BradyID.com/bmp71](http://www.BradyID.com/bmp71)  
[www.BradyCanada.ca/bmp71](http://www.BradyCanada.ca/bmp71)



# Circuit Board & Component ID

Various sizes and label types for marking relays, solenoids, switches, drive motors, and other components.



## Specialty Continuous Tape

| Diagram | Part Number  | Labels/Roll    | Material | Color | Label Dimensions |         |        |           | Recommended Ribbon | Price   |
|---------|--------------|----------------|----------|-------|------------------|---------|--------|-----------|--------------------|---------|
|         |              |                |          |       | A Inch           | (mm)    | B Inch | (mm)      |                    |         |
| Fig. 8  | M71C-500-423 | 1 Roll (cont.) | B-423    | White | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$45.82 |

## Die Cut Labels

| Diagram | Part Number   | Labels/Roll | Material | Color  | Label Dimensions |          |        |         | Recommended Ribbon | Price    |
|---------|---------------|-------------|----------|--------|------------------|----------|--------|---------|--------------------|----------|
|         |               |             |          |        | A Inch           | (mm)     | B Inch | (mm)    |                    |          |
| Fig. 4  | M71-1-423     | 750         | B-423    | White  | 0.25             | (6.35)   | 0.25   | (6.35)  | M71-R6000          | \$25.30  |
| Fig. 4  | M71-3-423     | 500         | B-423    | White  | 0.38             | (9.53)   | 0.38   | (9.53)  | M71-R6000          | \$26.39  |
| Fig. 4  | M71-3-457     | 500         | B-457    | White  | 0.38             | (9.53)   | 0.38   | (9.53)  | M71-R6000          | \$92.48  |
| Fig. 4  | M71-4-423     | 500         | B-423    | White  | 0.40             | (10.16)  | 0.40   | (10.16) | M71-R6000          | \$27.62  |
| Fig. 4  | M71-5-423     | 750         | B-423    | White  | 0.50             | (12.70)  | 0.20   | (5.08)  | M71-R6000          | \$35.79  |
| Fig. 4  | M71-6-423     | 750         | B-423    | White  | 0.50             | (12.70)  | 0.28   | (6.99)  | M71-R6000          | \$37.64  |
| Fig. 4  | BM71-7-423*   | 5000        | B-423    | White  | 0.50             | (12.70)  | 0.50   | (12.70) | M71-R6000          | \$277.72 |
| Fig. 4  | M71-7-423     | 500         | B-423    | White  | 0.50             | (12.70)  | 0.50   | (12.70) | M71-R6000          | \$33.11  |
| Fig. 4  | M71-6-473     | 750         | B-473    | White  | 0.50             | (12.70)  | 0.28   | (6.99)  | M71-R6000          | \$47.88  |
| Fig. 4  | M71-9-423     | 750         | B-423    | White  | 0.65             | (16.51)  | 0.20   | (5.08)  | M71-R6000          | \$39.71  |
| Fig. 4  | M71-9-426     | 750         | B-426    | Amber  | 0.65             | (16.51)  | 0.20   | (5.08)  | M71-R4300          | \$135.86 |
| Fig. 4  | M71-9-473     | 750         | B-473    | White  | 0.65             | (16.51)  | 0.20   | (5.08)  | M71-R6000          | \$49.73  |
| Fig. 4  | M71-10-457    | 750         | B-457    | White  | 0.75             | (19.05)  | 0.25   | (6.35)  | M71-R6000          | \$140.13 |
| Fig. 4  | M71-10-473    | 750         | B-473    | White  | 0.75             | (19.05)  | 0.25   | (6.35)  | M71-R6000          | \$51.19  |
| Fig. 4  | M71-10-423    | 750         | B-423    | White  | 0.75             | (19.05)  | 0.25   | (6.35)  | M71-R6000          | \$40.93  |
| Fig. 4  | M71-13-423    | 750         | B-423    | White  | 0.90             | (22.86)  | 0.25   | (6.35)  | M71-R6000          | \$43.62  |
| Fig. 4  | M71-13-426    | 750         | B-426    | Amber  | 0.90             | (22.86)  | 0.25   | (6.35)  | M71-R4300          | \$135.86 |
| Fig. 4  | M71-14-423    | 750         | B-423    | White  | 1.00             | (25.40)  | 0.19   | (4.75)  | M71-R6000          | \$46.29  |
| Fig. 4  | M71-15-423    | 750         | B-423    | White  | 1.00             | (25.40)  | 0.28   | (6.99)  | M71-R6000          | \$47.64  |
| Fig. 4  | BM71-16-423*  | 5000        | B-423    | White  | 1.00             | (25.40)  | 0.38   | (9.53)  | M71-R6000          | \$275.00 |
| Fig. 4  | M71-16-423    | 500         | B-423    | White  | 1.00             | (25.40)  | 0.38   | (9.53)  | M71-R6000          | \$39.21  |
| Fig. 4  | BM71-17-423*  | 5000        | B-423    | White  | 1.00             | (25.40)  | 0.50   | (12.70) | M71-R6000          | \$266.93 |
| Fig. 4  | M71-17-423    | 500         | B-423    | White  | 1.00             | (25.40)  | 0.50   | (12.70) | M71-R6000          | \$39.21  |
| Fig. 4  | BM71-19-423*  | 2500        | B-423    | White  | 1.00             | (25.40)  | 1.00   | (25.40) | M71-R6000          | \$193.89 |
| Fig. 4  | M71-19-423    | 250         | B-423    | White  | 1.00             | (25.40)  | 1.00   | (25.40) | M71-R6000          | \$27.73  |
| Fig. 4  | M71-16-426    | 500         | B-426    | Amber  | 1.00             | (25.40)  | 0.38   | (9.53)  | M71-R4300          | \$151.97 |
| Fig. 4  | M71-17-426    | 500         | B-426    | Amber  | 1.00             | (25.40)  | 0.50   | (12.70) | M71-R4300          | \$155.89 |
| Fig. 4  | M71-15-428    | 750         | B-428    | Silver | 1.00             | (25.40)  | 0.28   | (6.99)  | M71-R4300          | \$62.55  |
| Fig. 4  | BM71-17-428*  | 5000        | B-428    | Silver | 1.00             | (25.40)  | 0.50   | (12.70) | M71-R4300          | \$357.59 |
| Fig. 4  | M71-17-428    | 500         | B-428    | Silver | 1.00             | (25.40)  | 0.50   | (12.70) | M71-R4300          | \$51.07  |
| Fig. 4  | M71-16-457    | 500         | B-457    | White  | 1.00             | (25.40)  | 0.38   | (9.53)  | M71-R6000          | \$151.97 |
| Fig. 4  | M71-16-473    | 500         | B-473    | White  | 1.00             | (25.40)  | 0.38   | (9.53)  | M71-R6000          | \$49.12  |
| Fig. 4  | M71-17-473    | 500         | B-473    | White  | 1.00             | (25.40)  | 0.50   | (12.70) | M71-R6000          | \$49.12  |
| Fig. 4  | M71-24-423-BK | 500         | B-423    | Black  | 1.13             | (28.70)  | 0.50   | (12.70) | M71-R6000          | \$38.12  |
| Fig. 4  | M71-25-423    | 750         | B-423    | White  | 1.25             | (31.75)  | 0.25   | (6.35)  | M71-R6000          | \$50.22  |
| Fig. 4  | M71-27-423    | 750         | B-423    | White  | 1.50             | (38.10)  | 0.13   | (3.18)  | M71-R6000          | \$51.31  |
| Fig. 4  | M71-28-423    | 750         | B-423    | White  | 1.50             | (38.10)  | 0.25   | (6.35)  | M71-R6000          | \$57.17  |
| Fig. 4  | BM71-29-423*  | 5000        | B-423    | White  | 1.50             | (38.10)  | 0.50   | (12.70) | M71-R6000          | \$306.90 |
| Fig. 4  | M71-29-423    | 500         | B-423    | White  | 1.50             | (38.10)  | 0.50   | (12.70) | M71-R6000          | \$43.85  |
| Fig. 4  | M71-31-423    | 250         | B-423    | White  | 1.50             | (38.10)  | 1.00   | (25.40) | M71-R6000          | \$31.52  |
| Fig. 4  | M71-32-423    | 250         | B-423    | White  | 1.50             | (38.10)  | 1.50   | (38.10) | M71-R6000          | \$44.84  |
| Fig. 4  | M71-28-426    | 750         | B-426    | Amber  | 1.50             | (38.10)  | 0.25   | (6.35)  | M71-R4300          | \$178.50 |
| Fig. 4  | M71-29-428    | 500         | B-428    | Silver | 1.50             | (38.10)  | 0.50   | (12.70) | M71-R4300          | \$58.76  |
| Fig. 4  | M71-28-473    | 750         | B-473    | White  | 1.50             | (38.10)  | 0.25   | (6.35)  | M71-R6000          | \$71.35  |
| Fig. 4  | M71-2-423     | 100         | B-423    | White  | 2.00             | (50.80)  | 0.25   | (6.35)  | M71-R6000          | \$16.97  |
| Fig. 4  | BM71-20-423*  | 1000        | B-423    | White  | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R6000          | \$154.80 |
| Fig. 4  | M71-20-423    | 100         | B-423    | White  | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R6000          | \$22.10  |
| Fig. 4  | BM71-20-424*  | 1000        | B-424    | White  | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R4300          | \$118.26 |
| Fig. 4  | M71-20-424    | 100         | B-424    | White  | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R4300          | \$16.87  |
| Fig. 4  | BM71-20-428*  | 1000        | B-428    | Silver | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R4300          | \$218.80 |
| Fig. 4  | M71-20-428    | 100         | B-428    | Silver | 2.00             | (50.80)  | 1.00   | (25.40) | M71-R4300          | \$31.28  |
| Fig. 4  | M71-26-423    | 100         | B-423    | White  | 2.75             | (69.85)  | 1.25   | (31.75) | M71-R6000          | \$32.12  |
| Fig. 4  | M71-26-428    | 100         | B-428    | White  | 2.75             | (69.85)  | 1.25   | (31.75) | M71-R4300          | \$45.08  |
| Fig. 4  | M71-22-423    | 100         | B-423    | White  | 3.00             | (76.20)  | 1.00   | (25.40) | M71-R6000          | \$26.64  |
| Fig. 4  | M71-37-423    | 100         | B-423    | White  | 3.00             | (76.20)  | 1.90   | (48.26) | M71-R6000          | \$32.12  |
| Fig. 4  | M71-22-428    | 100         | B-428    | Silver | 3.00             | (76.20)  | 1.00   | (25.40) | M71-R4300          | \$37.51  |
| Fig. 4  | M71-23-423    | 100         | B-423    | White  | 4.00             | (101.60) | 1.00   | (25.40) | M71-R6000          | \$32.12  |
| Fig. 4  | M71-38-423    | 100         | B-423    | White  | 4.00             | (101.60) | 1.90   | (48.26) | M71-R6000          | \$38.36  |
| Fig. 4  | M71-38-428    | 100         | B-428    | White  | 4.00             | (101.60) | 1.90   | (48.26) | M71-R4300          | \$49.97  |

\* "B" indicates bulk roll.

\* See all ribbon colors on page 14.

## Wire And Cable Markers

Durable vinyl cloth wrap around wire and cable markers. Firm adhesive can be removed cleanly and reapplied.




Figure 4




Figure 5




Figure 6




Figure 7




Figure 8




Figure 12

### Wrap Around Wire ID Labels

| Diagram | Part Number    | Labels/Roll    | Material | Color | Approx. Wire Gauge | A Inch | (mm)    | B Inch  | (mm)      | C Inch | (mm) | Recommened Ribbon | Price    |
|---------|----------------|----------------|----------|-------|--------------------|--------|---------|---------|-----------|--------|------|-------------------|----------|
| Fig. 6  | M71-21-499     | 100            | B-499    | White | Cables             | 1.00   | (25.40) | 2.50    | (63.50)   | –      | –    | M71-R4300         | \$36.17  |
| Fig. 6  | M71-21-498     | 100            | B-498    | White | Cables             | 1.00   | (25.40) | 2.50    | (63.50)   | –      | –    | M71-R6200         | \$30.67  |
| Fig. 6  | M71-33-498     | 100            | B-498    | White | Cables             | 1.50   | (38.10) | 4.00    | (101.60)  | –      | –    | M71-R6200         | \$49.49  |
| Fig. 6  | M71-10-498     | 750            | B-498    | White | 16-10              | 0.25   | (6.35)  | 0.75    | (19.05)   | –      | –    | M71-R6200         | \$47.88  |
| Fig. 12 | M71-7-499      | 500            | B-499    | White | 16-10              | 0.50   | (12.70) | 0.50    | (12.70)   | –      | –    | M71-R4300         | \$46.91  |
| Fig. 12 | M71-7-498      | 500            | B-498    | White | 16-10              | 0.50   | (12.70) | 0.50    | (12.70)   | –      | –    | M71-R6200         | \$45.94  |
| Fig. 6  | BM71-11-499*   | 5000           | B-499    | White | 16-10              | 0.50   | (12.70) | 0.75    | (19.05)   | –      | –    | M71-R4300         | \$299.94 |
| Fig. 6  | M71-11-499     | 500            | B-499    | White | 16-10              | 0.50   | (12.70) | 0.75    | (19.05)   | –      | –    | M71-R4300         | \$42.76  |
| Fig. 6  | BM71-11-498*   | 5000           | B-498    | White | 16-10              | 0.50   | (12.70) | 0.75    | (19.05)   | –      | –    | M71-R6200         | \$292.73 |
| Fig. 6  | M71-11-498     | 500            | B-498    | White | 16-10              | 0.50   | (12.70) | 0.75    | (19.05)   | –      | –    | M71-R6200         | \$41.79  |
| Fig. 6  | M71-16-499     | 500            | B-499    | White | 12-10              | 0.38   | (9.53)  | 1.00    | (25.40)   | –      | –    | M71-R4300         | \$51.31  |
| Fig. 6  | M71-16-498     | 500            | B-498    | White | 12-10              | 0.38   | (9.53)  | 1.00    | (25.40)   | –      | –    | M71-R6200         | \$50.22  |
| Fig. 6  | M71-18-499     | 250            | B-499    | White | 12-10              | 0.75   | (19.05) | 1.00    | (25.40)   | –      | –    | M71-R4300         | \$35.31  |
| Fig. 6  | BM71-18-498*   | 2500           | B-498    | White | 12-10              | 0.75   | (19.05) | 1.00    | (25.40)   | –      | –    | M71-R6200         | \$234.94 |
| Fig. 6  | M71-18-498     | 250            | B-498    | White | 12-10              | 0.75   | (19.05) | 1.00    | (25.40)   | –      | –    | M71-R6200         | \$34.57  |
| Fig. 12 | M71-17-498     | 500            | B-498    | White | 12-10              | 1.00   | (25.40) | 0.50    | (12.70)   | –      | –    | M71-R6200         | \$52.77  |
| Fig. 12 | M71-19-499     | 250            | B-499    | White | 12-10              | 1.00   | (25.40) | 1.00    | (25.40)   | –      | –    | M71-R4300         | \$38.36  |
| Fig. 12 | BM71-19-498*   | 2500           | B-498    | White | 12-10              | 1.00   | (25.40) | 1.00    | (25.40)   | –      | –    | M71-R6200         | \$254.84 |
| Fig. 12 | M71-19-498     | 250            | B-498    | White | 12-10              | 1.00   | (25.40) | 1.00    | (25.40)   | –      | –    | M71-R6200         | \$37.51  |
| Fig. 4  | M71-78-499     | 250            | B-499    | White | 12-10              | 1.90   | (48.26) | 1.00    | (25.40)   | –      | –    | M71-R4300         | \$61.45  |
| Fig. 6  | M71-28-499     | 750            | B-499    | White | 10-4               | 0.25   | (6.35)  | 1.50    | (38.10)   | –      | –    | M71-R4300         | \$49.97  |
| Fig. 6  | M71-29-499     | 500            | B-499    | White | 10-4               | 0.50   | (12.70) | 1.50    | (38.10)   | –      | –    | M71-R4300         | \$47.64  |
| Fig. 6  | BM71-29-498*   | 5000           | B-498    | White | 10-4               | 0.50   | (12.70) | 1.50    | (38.10)   | –      | –    | M71-R6200         | \$317.04 |
| Fig. 6  | M71-29-498     | 500            | B-498    | White | 10-4               | 0.50   | (12.70) | 1.50    | (38.10)   | –      | –    | M71-R6200         | \$46.67  |
| Fig. 6  | M71-30-499     | 250            | B-499    | White | 10-4               | 0.75   | (19.05) | 1.50    | (38.10)   | –      | –    | M71-R4300         | \$42.16  |
| Fig. 6  | M71-30-498     | 250            | B-498    | White | 10-4               | 0.75   | (19.05) | 1.50    | (38.10)   | –      | –    | M71-R6200         | \$41.06  |
| Fig. 6  | M71-31-499     | 250            | B-499    | White | 10-4               | 1.00   | (25.40) | 1.50    | (38.10)   | –      | –    | M71-R4300         | \$48.87  |
| Fig. 6  | M71-31-498     | 250            | B-498    | White | 10-4               | 1.00   | (25.40) | 1.50    | (38.10)   | –      | –    | M71-R6200         | \$47.64  |
| Fig. 12 | M71-32-498     | 250            | B-498    | White | 10-4               | 1.50   | (38.10) | 1.50    | (38.10)   | –      | –    | M71-R6200         | \$59.00  |
| Fig. 5  | M71C-240-498   | 1 Roll (cont.) | B-498    | White | –                  | 0.24   | (6.09)  | 30 ft.  | (9.10 m)  | –      | –    | M71-R6200         | \$39.58  |
| Fig. 8  | BM71C-240-498* | 1 Roll (cont.) | B-498    | White | –                  | 0.24   | (5.80)  | 275 ft. | (83.82 m) | –      | –    | M71-R6200         | \$254.44 |
| Fig. 5  | M71C-318-498   | 1 Roll (cont.) | B-498    | White | –                  | 0.32   | (8.07)  | 30 ft.  | (9.10 m)  | –      | –    | M71-R6200         | \$40.68  |
| Fig. 5  | BM71C-318-498* | 1 Roll (cont.) | B-498    | White | –                  | 0.32   | (8.07)  | 275 ft. | (83.82 m) | –      | –    | M71-R6200         | \$260.95 |
| Fig. 5  | M71C-375-498   | 1 Roll (cont.) | B-498    | White | –                  | 0.38   | (9.53)  | 30 ft.  | (9.10 m)  | –      | –    | M71-R6200         | \$41.30  |
| Fig. 5  | BM71C-375-498* | 1 Roll (cont.) | B-498    | White | –                  | 0.38   | (9.53)  | 275 ft. | (83.82 m) | –      | –    | M71-R6200         | \$265.07 |
| Fig. 8  | M71C-500-499   | 1 Roll (cont.) | B-499    | White | –                  | 0.50   | (12.70) | 30 ft.  | (9.10 m)  | –      | –    | M71-R4300         | \$29.62  |
| Fig. 8  | M71C-500-498   | 1 Roll (cont.) | B-498    | White | –                  | 0.50   | (12.70) | 30 ft.  | (9.10 m)  | –      | –    | M71-R6200         | \$29.62  |
| Fig. 4  | M71-84-499     | 500            | B-499    | White | –                  | 0.90   | (22.86) | 0.50    | (12.70)   | –      | –    | M71-R4300         | \$44.10  |
| Fig. 4  | M71-17-489     | 500            | B-489    | White | –                  | 1.00   | (25.40) | 0.50    | (12.70)   | –      | –    | M71-R4300         | \$47.77  |
| Fig. 8  | M71C-1000-499  | 1 Roll (cont.) | B-499    | White | –                  | 1.00   | (25.40) | 30 ft.  | (9.10 m)  | –      | –    | M71-R4300         | \$41.31  |
| Fig. 8  | M71C-1000-498  | 1 Roll (cont.) | B-498    | White | –                  | 1.00   | (25.40) | 30 ft.  | (9.10 m)  | –      | –    | M71-R6200         | \$41.31  |
| Fig. 4  | M71-29-437     | 500            | B-437    | White | –                  | 1.50   | (38.10) | 0.50    | (12.70)   | –      | –    | M71-R4300         | \$67.16  |
| Fig. 4  | M71-81-499     | 750            | B-499    | White | –                  | 1.90   | (48.26) | 0.25    | (6.35)    | –      | –    | M71-R4300         | \$58.52  |
| Fig. 8  | M71C-1900-499  | 1 Roll (cont.) | B-499    | White | –                  | 1.90   | (48.30) | 30 ft.  | (9.10 m)  | –      | –    | M71-R4300         | \$62.00  |
| Fig. 8  | M71C-1900-498  | 1 Roll (cont.) | B-498    | White | –                  | 1.90   | (48.30) | 30 ft.  | (9.10 m)  | –      | –    | M71-R6200         | \$62.00  |

### Fiber Optic Flags

| Diagram | Part Number | Labels/Roll | Material | Color | A Inch | (mm)    | B Inch | (mm)    | Recommened Ribbon | Price   |
|---------|-------------|-------------|----------|-------|--------|---------|--------|---------|-------------------|---------|
| Fig. 23 | M71FP-1-425 | 250         | B-425    | White | 1.18   | (30.00) | 0.79   | (20.00) | M71-R4300         | \$22.60 |
| Fig. 24 | M71FT-1-425 | 250         | B-425    | White | 1.18   | (30.00) | 0.79   | (20.00) | M71-R4300         | \$22.60 |
| Fig. 23 | M71FP-2-425 | 100         | B-425    | White | 1.75   | (44.45) | 1.00   | (25.40) | M71-R4300         | \$22.60 |




Figure 23




Figure 24

\* "B" indicates bulk roll.  
 \*\* Flame retardant material.  
 \* See all ribbon colors on page 14.

## Self Laminating Wire Markers

Protected printing area offers superior chemical and abrasion resistance. Features a non-printed clear area that wraps around and overlaminates the printed text.




Figure 4




Figure 7




Figure 19



### Self-Laminating Labels

| Diagram | Part Number   | Labels/<br>Roll | Material | Color  | Approx.<br>Wire Gauge | A Inch (mm) |         | B Inch (mm) |          | C Inch (mm) |         | Reccommended<br>Ribbon | Price    |
|---------|---------------|-----------------|----------|--------|-----------------------|-------------|---------|-------------|----------|-------------|---------|------------------------|----------|
| Fig. 7  | BM71-21-427*  | 1000            | B-427    | White  | Cables                | 1.00        | (25.40) | 2.50        | (63.50)  | 0.75        | (19.05) | M71-R4300              | \$178.85 |
| Fig. 7  | M71-21-427    | 100             | B-427    | White  | Cables                | 1.00        | (25.40) | 2.50        | (63.50)  | 0.75        | (19.05) | M71-R4300              | \$25.54  |
| Fig. 7  | M71-21-427-YL | 100             | B-427    | Yellow | Cables                | 1.00        | (25.40) | 2.50        | (63.50)  | 0.75        | (19.05) | M71-R4300              | \$32.01  |
| Fig. 19 | BM71-64-427*  | 1000            | B-427    | White  | Cables                | 1.00        | (25.40) | 3.38        | (85.73)  | 1.13        | (28.58) | M71-R4300              | \$109.51 |
| Fig. 19 | M71-64-427    | 100             | B-427    | White  | Cables                | 1.00        | (25.40) | 3.38        | (85.73)  | 1.13        | (28.58) | M71-R4300              | \$15.64  |
| Fig. 7  | BM71-23-427*  | 1000            | B-427    | White  | Cables                | 1.00        | (25.40) | 4.00        | (101.60) | 1.00        | (25.40) | M71-R4300              | \$213.56 |
| Fig. 7  | M71-23-427    | 100             | B-427    | White  | Cables                | 1.00        | (25.40) | 4.00        | (101.60) | 1.00        | (25.40) | M71-R4300              | \$30.42  |
| Fig. 7  | BM71-109-427* | 500             | B-427    | White  | Cables                | 1.50        | (38.10) | 4.00        | (101.60) | 1.50        | (38.10) | M71-R4300              | \$144.03 |
| Fig. 7  | BM71-33-427*  | 500             | B-427    | White  | Cables                | 1.50        | (38.10) | 4.00        | (101.60) | 1.00        | (25.40) | M71-R4300              | \$144.03 |
| Fig. 7  | M71-109-427   | 100             | B-427    | White  | Cables                | 1.50        | (38.10) | 4.00        | (101.60) | 1.50        | (38.10) | M71-R4300              | \$41.17  |
| Fig. 7  | M71-33-427    | 100             | B-427    | White  | Cables                | 1.50        | (38.10) | 4.00        | (101.60) | 1.00        | (25.40) | M71-R4300              | \$41.17  |
| Fig. 7  | M71-33-427-YL | 100             | B-427    | Yellow | Cables                | 1.50        | (38.10) | 4.00        | (101.60) | 1.00        | (25.40) | M71-R4300              | \$51.56  |
| Fig. 7  | BM71-34-427*  | 500             | B-427    | White  | Cables                | 1.50        | (38.10) | 6.00        | (152.40) | 1.50        | (38.10) | M71-R4300              | \$238.48 |
| Fig. 7  | M71-34-427    | 50              | B-427    | White  | Cables                | 1.50        | (38.10) | 6.00        | (152.40) | 1.50        | (38.10) | M71-R4300              | \$34.09  |
| Fig. 7  | M71-66-427    | 100             | B-427    | White  | Cables                | 1.94        | (49.23) | 3.15        | (80.00)  | 1.00        | (25.40) | M71-R4300              | \$41.17  |
| Fig. 7  | M71-10-427    | 750             | B-427    | White  | 16-10                 | 0.25        | (6.35)  | 0.75        | (19.05)  | 0.38        | (9.53)  | M71-R4300              | \$32.62  |
| Fig. 7  | BM71-11-427*  | 5000            | B-427    | White  | 16-10                 | 0.50        | (12.70) | 0.75        | (19.05)  | 0.38        | (9.53)  | M71-R4300              | \$242.88 |
| Fig. 7  | M71-11-427    | 500             | B-427    | White  | 16-10                 | 0.50        | (12.70) | 0.75        | (19.05)  | 0.38        | (9.53)  | M71-R4300              | \$34.69  |
| Fig. 7  | M71-96-427    | 250             | B-427    | White  | 16-10                 | 1.00        | (25.40) | 0.75        | (19.05)  | 0.38        | (9.53)  | M71-R4300              | \$23.69  |
| Fig. 7  | BM71-17-427*  | 5000            | B-427    | White  | 12-10                 | 0.50        | (12.70) | 1.00        | (25.40)  | 0.38        | (9.53)  | M71-R4300              | \$259.75 |
| Fig. 7  | M71-17-427    | 500             | B-427    | White  | 12-10                 | 0.50        | (12.70) | 1.00        | (25.40)  | 0.38        | (9.53)  | M71-R4300              | \$37.14  |
| Fig. 7  | BM71-19-427*  | 2500            | B-427    | White  | 12-10                 | 1.00        | (25.40) | 1.00        | (25.40)  | 0.38        | (9.53)  | M71-R4300              | \$233.11 |
| Fig. 7  | M71-19-427    | 250             | B-427    | White  | 12-10                 | 1.00        | (25.40) | 1.00        | (25.40)  | 0.38        | (9.53)  | M71-R4300              | \$33.36  |
| Fig. 7  | M71-19-427-YL | 250             | B-427    | Yellow | 12-10                 | 1.00        | (25.40) | 1.00        | (25.40)  | 0.38        | (9.53)  | M71-R4300              | \$36.77  |
| Fig. 7  | M71-104-427   | 250             | B-427    | White  | 12-10                 | 1.50        | (38.10) | 1.00        | (25.40)  | 0.38        | (9.53)  | M71-R4300              | \$42.76  |
| Fig. 7  | M71-28-427    | 750             | B-427    | White  | 10-4                  | 0.25        | (6.35)  | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$41.54  |
| Fig. 7  | BM71-29-427*  | 5000            | B-427    | White  | 10-4                  | 0.50        | (12.70) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$317.64 |
| Fig. 7  | M71-29-427    | 500             | B-427    | White  | 10-4                  | 0.50        | (12.70) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$45.45  |
| Fig. 7  | BM71-18-427*  | 2500            | B-427    | White  | 10-4                  | 0.75        | (19.05) | 1.00        | (25.40)  | 0.38        | (9.53)  | M71-R4300              | \$212.70 |
| Fig. 7  | M71-18-427    | 250             | B-427    | White  | 10-4                  | 0.75        | (19.05) | 1.00        | (25.40)  | 0.38        | (9.53)  | M71-R4300              | \$30.31  |
| Fig. 7  | BM71-30-427*  | 2500            | B-427    | White  | 10-4                  | 0.75        | (19.05) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$236.65 |
| Fig. 7  | M71-30-427    | 250             | B-427    | White  | 10-4                  | 0.75        | (19.05) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$33.85  |
| Fig. 7  | M71-30-427-BL | 250             | B-427    | Blue   | 10-4                  | 0.75        | (19.05) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$42.28  |
| Fig. 7  | M71-30-427-PL | 250             | B-427    | Purple | 10-4                  | 0.75        | (19.05) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$42.28  |
| Fig. 7  | M71-30-427-RD | 250             | B-427    | Red    | 10-4                  | 0.75        | (19.05) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$42.28  |
| Fig. 7  | M71-103-427   | 250             | B-427    | White  | 10-4                  | 1.00        | (25.40) | 1.25        | (31.75)  | 0.50        | (12.70) | M71-R4300              | \$39.34  |
| Fig. 7  | BM71-31-427*  | 2500            | B-427    | White  | 10-4                  | 1.00        | (25.40) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$299.94 |
| Fig. 7  | M71-31-427    | 250             | B-427    | White  | 10-4                  | 1.00        | (25.40) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$42.76  |
| Fig. 7  | M71-31-427-GN | 250             | B-427    | Green  | 10-4                  | 1.00        | (25.40) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$54.50  |
| Fig. 7  | M71-31-427-RD | 250             | B-427    | Red    | 10-4                  | 1.00        | (25.40) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$54.50  |
| Fig. 7  | M71-31-427-YL | 250             | B-427    | Yellow | 10-4                  | 1.00        | (25.40) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$54.50  |
| Fig. 4  | M71-30-427-AW | 250             | B-427    | White  | 10-4                  | 1.50        | (38.10) | 0.75        | (19.05)  | —           | —       | M71-R4300              | \$33.85  |
| Fig. 7  | BM71-32-427*  | 1000            | B-427    | White  | 10-4                  | 1.50        | (38.10) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$123.39 |
| Fig. 7  | M71-32-427    | 250             | B-427    | White  | 10-4                  | 1.50        | (38.10) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$44.22  |
| Fig. 7  | M71-32-427-YL | 250             | B-427    | Yellow | 10-4                  | 1.50        | (38.10) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$54.86  |
| Fig. 7  | M71-88-427    | 250             | B-427    | White  | 10-4                  | 1.75        | (44.45) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$57.79  |
| Fig. 7  | BM71-107-427* | 1000            | B-427    | White  | 10-4                  | 2.00        | (50.80) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$359.19 |
| Fig. 7  | M71-107-427   | 100             | B-427    | White  | 10-4                  | 2.00        | (50.80) | 1.50        | (38.10)  | 0.50        | (12.70) | M71-R4300              | \$52.91  |

\* "B" indicates bulk roll.

\* See all ribbon colors on page 14.

# PermaSleeves™ Wire Markers

These full circle heat-shrink sleeves are the ultimate in marker durability, permanence and aesthetic appearance. Fast shrink rate saves time and costs during installation.



Figure 8




Figure 20



## PermaSleeve Markers (Shrink Ratio 3-to-1)

| Diagram | Part Number         | Labels/Roll    | Material | Color  | Approx. Wire Gauge | Label Dimensions |         |        |           | Recommended Ribbon | Price      |
|---------|---------------------|----------------|----------|--------|--------------------|------------------|---------|--------|-----------|--------------------|------------|
|         |                     |                |          |        |                    | A Inch           | (mm)    | B Inch | (mm)      |                    |            |
| Fig. 8  | BM71C-94-342*       | 1 Roll (cont.) | B-342    | White  | 28-18              | 0.18             | (4.62)  | 50 ft. | (15.24 m) | M71-R4300          | \$186.00   |
| Fig. 20 | M71-94-1-342        | 100            | B-342    | White  | 28-18              | 1.02             | (25.78) | 0.18   | (4.62)    | M71-R4300          | \$42.64    |
| Fig. 20 | M71-94-1-342YL      | 100            | B-342    | Yellow | 28-18              | 1.02             | (25.78) | 0.18   | (4.62)    | M71-R4300          | \$43.00    |
| Fig. 20 | BM71-94-175-342*    | 2500           | B-342    | White  | 28-18              | 1.77             | (44.83) | 0.18   | (4.62)    | M71-R4300          | \$1,011.93 |
| Fig. 20 | BM71-94-175-342YL*  | 2500           | B-342    | Yellow | 28-18              | 1.77             | (44.83) | 0.18   | (4.62)    | M71-R4300          | \$1,011.93 |
| Fig. 20 | M71-94-175-342      | 100            | B-342    | White  | 28-18              | 1.77             | (44.83) | 0.18   | (4.62)    | M71-R4300          | \$57.90    |
| Fig. 20 | M71-94-175-342YL    | 100            | B-342    | Yellow | 28-18              | 1.77             | (44.83) | 0.18   | (4.62)    | M71-R4300          | \$57.90    |
| Fig. 8  | BM71C-125-342*      | 1 Roll (cont.) | B-342    | White  | 22-16              | 0.24             | (5.96)  | 50 ft. | (15.24 m) | M71-R4300          | \$198.00   |
| Fig. 20 | BM71-125-1-342*     | 1000           | B-342    | White  | 22-16              | 1.02             | (25.78) | 0.24   | (5.96)    | M71-R4300          | \$315.81   |
| Fig. 20 | M71-125-1-342       | 100            | B-342    | White  | 22-16              | 1.02             | (25.78) | 0.24   | (5.96)    | M71-R4300          | \$45.20    |
| Fig. 20 | M71-125-1-342YL     | 100            | B-342    | Yellow | 22-16              | 1.02             | (25.78) | 0.24   | (5.96)    | M71-R4300          | \$45.20    |
| Fig. 20 | BM71-125-175-342*   | 1000           | B-342    | White  | 22-16              | 1.77             | (44.83) | 0.24   | (5.96)    | M71-R4300          | \$424.30   |
| Fig. 20 | BM71-125-175-342YL* | 1000           | B-342    | Yellow | 22-16              | 1.77             | (44.83) | 0.24   | (5.96)    | M71-R4300          | \$424.30   |
| Fig. 20 | M71-125-175-342     | 100            | B-342    | White  | 22-16              | 1.77             | (44.83) | 0.24   | (5.96)    | M71-R4300          | \$60.71    |
| Fig. 20 | M71-125-175-342YL   | 100            | B-342    | Yellow | 22-16              | 1.77             | (44.83) | 0.24   | (5.96)    | M71-R4300          | \$60.71    |
| Fig. 8  | BM71C-187-342*      | 1 Roll (cont.) | B-342    | White  | 18-12              | 0.34             | (8.50)  | 50 ft. | (15.24 m) | M71-R4300          | \$210.00   |
| Fig. 20 | BM71-187-1-342*     | 100            | B-342    | White  | 18-12              | 1.02             | (25.78) | 0.34   | (8.50)    | M71-R4300          | \$352.33   |
| Fig. 20 | BM71-187-1-342YL*   | 1000           | B-342    | Yellow | 18-12              | 1.02             | (25.78) | 0.34   | (8.50)    | M71-R4300          | \$352.33   |
| Fig. 20 | M71-187-1-342       | 100            | B-342    | White  | 18-12              | 1.02             | (25.78) | 0.34   | (8.50)    | M71-R4300          | \$50.33    |
| Fig. 20 | M71-187-1-342YL     | 100            | B-342    | Yellow | 18-12              | 1.02             | (25.78) | 0.34   | (8.50)    | M71-R4300          | \$50.33    |
| Fig. 20 | BM71-187-175-342*   | 1000           | B-342    | White  | 18-12              | 1.77             | (44.83) | 0.34   | (8.50)    | M71-R4300          | \$458.63   |
| Fig. 20 | BM71-187-175-342YL* | 1000           | B-342    | Yellow | 18-12              | 1.77             | (44.83) | 0.34   | (8.50)    | M71-R4300          | \$458.63   |
| Fig. 20 | M71-187-175-342     | 100            | B-342    | White  | 18-12              | 1.77             | (44.83) | 0.34   | (8.50)    | M71-R4300          | \$67.43    |
| Fig. 20 | M71-187-175-342YL   | 100            | B-342    | Yellow | 18-12              | 1.77             | (44.83) | 0.34   | (8.50)    | M71-R4300          | \$67.43    |
| Fig. 8  | BM71C-250-342*      | 1 Roll (cont.) | B-342    | White  | 16-10              | 0.44             | (11.15) | 50 ft. | (15.24 m) | M71-R4300          | \$270.00   |
| Fig. 20 | BM71-250-1-342*     | 1000           | B-342    | White  | 16-10              | 1.02             | (25.78) | 0.44   | (11.15)   | M71-R4300          | \$426.26   |
| Fig. 20 | M71-250-1-342       | 100            | B-342    | White  | 16-10              | 1.02             | (25.78) | 0.44   | (11.15)   | M71-R4300          | \$60.97    |
| Fig. 20 | M71-250-1-342YL     | 100            | B-342    | Yellow | 16-10              | 1.02             | (25.78) | 0.44   | (11.15)   | M71-R4300          | \$60.97    |
| Fig. 20 | BM71-250-175-342*   | 1000           | B-342    | White  | 16-10              | 1.77             | (44.83) | 0.44   | (11.15)   | M71-R4300          | \$573.84   |
| Fig. 20 | BM71-250-175-342YL* | 1000           | B-342    | Yellow | 16-10              | 1.77             | (44.83) | 0.44   | (11.15)   | M71-R4300          | \$573.84   |
| Fig. 20 | M71-250-175-342     | 100            | B-342    | White  | 16-10              | 1.77             | (44.83) | 0.44   | (11.15)   | M71-R4300          | \$82.10    |
| Fig. 20 | M71-250-175-342YL   | 100            | B-342    | Yellow | 16-10              | 1.77             | (44.83) | 0.44   | (11.15)   | M71-R4300          | \$81.84    |
| Fig. 8  | BM71C-375-342*      | 1 Roll (cont.) | B-342    | White  | 12-6               | 0.65             | (16.38) | 50 ft. | (15.24 m) | M71-R4300          | \$396.00   |
| Fig. 20 | BM71-375-1-342*     | 1000           | B-342    | White  | 12-6               | 1.02             | (25.78) | 0.65   | (16.38)   | M71-R4300          | \$629.05   |
| Fig. 20 | M71-375-1-342       | 100            | B-342    | White  | 12-6               | 1.02             | (25.78) | 0.65   | (16.38)   | M71-R4300          | \$89.81    |
| Fig. 20 | M71-375-1-342YL     | 100            | B-342    | Yellow | 12-6               | 1.02             | (25.78) | 0.65   | (16.38)   | M71-R4300          | \$89.81    |
| Fig. 20 | BM71-375-175-342*   | 1000           | B-342    | White  | 12-6               | 1.77             | (44.83) | 0.65   | (16.38)   | M71-R4300          | \$845.30   |
| Fig. 20 | M71-375-175-342     | 100            | B-342    | White  | 12-6               | 1.77             | (44.83) | 0.65   | (16.38)   | M71-R4300          | \$120.82   |
| Fig. 20 | M71-375-175-342YL   | 100            | B-342    | Yellow | 12-6               | 1.77             | (44.83) | 0.65   | (16.38)   | M71-R4300          | \$120.82   |
| Fig. 8  | BM71C-500-342*      | 1 Roll (cont.) | B-342    | White  | 8-1                | 0.85             | (21.61) | 50 ft. | (15.24 m) | M71-R4300          | \$456.00   |
| Fig. 20 | BM71-500-1-342*     | 1000           | B-342    | White  | 8-1                | 1.02             | (25.78) | 0.85   | (21.61)   | M71-R4300          | \$726.79   |
| Fig. 20 | BM71-500-1-342YL*   | 1000           | B-342    | Yellow | 8-1                | 1.02             | (25.78) | 0.85   | (21.61)   | M71-R4300          | \$726.79   |
| Fig. 20 | M71-500-1-342       | 100            | B-342    | White  | 8-1                | 1.02             | (25.78) | 0.85   | (21.61)   | M71-R4300          | \$103.84   |
| Fig. 20 | M71-500-1-342YL     | 100            | B-342    | Yellow | 8-1                | 1.02             | (25.78) | 0.85   | (21.61)   | M71-R4300          | \$103.84   |
| Fig. 20 | BM71-500-175-342*   | 1000           | B-342    | White  | 8-1                | 1.77             | (44.83) | 0.85   | (21.61)   | M71-R4300          | \$977.73   |
| Fig. 20 | BM71-500-175-342YL* | 1000           | B-342    | Yellow | 8-1                | 1.77             | (44.83) | 0.85   | (21.61)   | M71-R4300          | \$977.73   |
| Fig. 20 | M71-500-175-342     | 100            | B-342    | White  | 8-1                | 1.77             | (44.83) | 0.85   | (21.61)   | M71-R4300          | \$139.63   |
| Fig. 20 | M71-500-175-342YL   | 100            | B-342    | Yellow | 8-1                | 1.77             | (44.83) | 0.85   | (21.61)   | M71-R4300          | \$139.63   |
| Fig. 20 | M71-1000-1-342      | 50             | B-342    | White  | 1-500              | 1.02             | (25.78) | 1.66   | (42.16)   | M71-R4300          | \$71.72    |
| Fig. 20 | M71-1000-1-342YL    | 50             | B-342    | Yellow | 1-500              | 1.02             | (25.78) | 1.66   | (42.16)   | M71-R4300          | \$71.72    |
| Fig. 8  | BM71C-1000-342*     | 1 Roll (cont.) | B-342    | White  | 1-500              | 1.66             | (42.16) | 50 ft. | (15.24 m) | M71-R4300          | \$630.00   |
| Fig. 20 | BM71-1000-175-342*  | 500            | B-342    | White  | 1-500              | 1.77             | (44.83) | 1.66   | (42.16)   | M71-R4300          | \$679.75   |
| Fig. 20 | M71-1000-175-342    | 50             | B-342    | White  | 1-500              | 1.77             | (44.83) | 1.66   | (42.16)   | M71-R4300          | \$97.14    |
| Fig. 20 | M71-1000-175-342YL  | 50             | B-342    | Yellow | 1-500              | 1.77             | (44.83) | 1.66   | (42.16)   | M71-R4300          | \$97.14    |

\* "B" indicates bulk roll.

\* See all ribbon colors on page 14.

## PermaSleeves™ Wire Markers (Continued)




Figure 26



### Tags

| Diagram | Part Number      | Labels/Roll | Material | Color | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)    | Recommended Ribbon | Price    |
|---------|------------------|-------------|----------|-------|--------|--------------------------|--------|---------|--------------------|----------|
| Fig. 26 | M71-111-145FR-GY | 100         | B-145FR  | Grey  | 1.21   | (30.63)                  | 0.76   | (19.25) | M71-R6000          | \$33.60  |
| Fig. 26 | BM71-111-145-GY* | 1000        | B-145    | Grey  | 1.21   | (30.63)                  | 0.76   | (19.25) | M71-R6000          | \$213.81 |
| Fig. 26 | M71-111-145-GY   | 100         | B-145    | Grey  | 1.21   | (30.63)                  | 0.76   | (19.25) | M71-R6000          | \$30.53  |
| Fig. 26 | M71-110-145FR-GY | 100         | B-145FR  | Grey  | 1.75   | (44.45)                  | 1.00   | (25.40) | M71-R6000          | \$33.60  |
| Fig. 26 | BM71-110-145-GY* | 1000        | B-145    | Grey  | 1.75   | (44.45)                  | 1.00   | (25.40) | M71-R6000          | \$213.81 |
| Fig. 26 | M71-110-145-GY   | 100         | B-145    | Grey  | 1.75   | (44.45)                  | 1.00   | (25.40) | M71-R6000          | \$30.53  |

## Voice/Data Comm

Durable materials with permanent adhesive in a variety of sizes for marking racks, bays, frames, slots, and other voice/data equipment.




Figure 3




Figure 4




Figure 5



Figure 8




Figure 31



### Die Cut Labels

| Diagram | Part Number  | Labels/Roll | Material | Color | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)    | Recommended Ribbon | Price    |
|---------|--------------|-------------|----------|-------|--------|--------------------------|--------|---------|--------------------|----------|
| Fig. 4  | M71-45-422   | 500         | B-422    | White | 1.05   | (38.10)                  | 0.38   | (9.53)  | M71-R6000          | \$48.75  |
| Fig. 4  | M71-30-422   | 250         | B-422    | White | 1.50   | (38.10)                  | 0.75   | (19.05) | M71-R6000          | \$45.69  |
| Fig. 4  | BM71-20-422* | 1000        | B-422    | White | 2.00   | (50.80)                  | 1.00   | (25.40) | M71-R6000          | \$178.85 |
| Fig. 4  | M71-37-422   | 100         | B-422    | White | 3.00   | (76.20)                  | 1.90   | (48.26) | M71-R6000          | \$38.12  |

### Specialty Continuous Tape

| Diagram | Part Number   | Labels/Roll    | Material | Color | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)      | Recommended Ribbon | Price    |
|---------|---------------|----------------|----------|-------|--------|--------------------------|--------|-----------|--------------------|----------|
| Fig. 8  | M71C-375-422  | 1 Roll (cont.) | B-422    | White | 0.38   | (9.53)                   | 50 ft. | (15.24 m) | M71-R6000          | \$54.37  |
| Fig. 5  | M71C-475-422  | 1 Roll (cont.) | B-422    | White | 0.48   | (12.10)                  | 50 ft. | (15.24 m) | M71-R6000          | \$62.53  |
| Fig. 8  | M71C-500-422  | 1 Roll (cont.) | B-422    | White | 0.50   | (12.70)                  | 50 ft. | (15.24 m) | M71-R6000          | \$54.37  |
| Fig. 8  | M71C-625-422  | 1 Roll (cont.) | B-422    | White | 0.63   | (15.88)                  | 50 ft. | (15.24 m) | M71-R6000          | \$75.74  |
| Fig. 8  | M71C-1000-422 | 1 Roll (cont.) | B-422    | White | 1.00   | (25.40)                  | 50 ft. | (15.24 m) | M71-R6000          | \$75.15  |
| Fig. 8  | M71C-1900-422 | 1 Roll (cont.) | B-422    | White | 1.90   | (48.26)                  | 50 ft. | (15.24 m) | M71-R6000          | \$112.65 |

### Tags

| Diagram | Part Number  | Labels/Roll    | Material | Color | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)      | Recommended Ribbon | Price    |
|---------|--------------|----------------|----------|-------|--------|--------------------------|--------|-----------|--------------------|----------|
| Fig. 3  | M71C-230-412 | 1 Roll (cont.) | B-412    | White | 0.23   | (5.84)                   | 50 ft. | (15.24 m) | M71-R6200          | \$45.32  |
| Fig. 3  | M71C-375-412 | 1 Roll (cont.) | B-412    | White | 0.38   | (9.53)                   | 50 ft. | (15.24 m) | M71-R6200          | \$47.77  |
| Fig. 5  | M71C-475-412 | 1 Roll (cont.) | B-412    | White | 0.48   | (12.10)                  | 50 ft. | (15.24 m) | M71-R6200          | \$50.33  |
| Fig. 3  | M71C-500-412 | 1 Roll (cont.) | B-412    | White | 0.50   | (12.70)                  | 50 ft. | (15.24 m) | M71-R6200          | \$50.33  |
| Fig. 5  | M71C-625-412 | 1 Roll (cont.) | B-412    | White | 0.63   | (15.90)                  | 50 ft. | (15.24 m) | M71-R6200          | \$60.96  |
| Fig. 3  | M71C-785-412 | 1 Roll (cont.) | B-412    | White | 0.79   | (19.94)                  | 50 ft. | (15.24 m) | M71-R6200          | \$69.64  |
| Fig. 31 | BM71-40-412* | 5000           | B-412    | White | 1.94   | (49.23)                  | 0.38   | (9.53)    | M71-R6200          | \$265.72 |
| Fig. 31 | M71-40-412   | 750            | B-412    | White | 1.94   | (49.23)                  | 0.38   | (9.53)    | M71-R6200          | \$57.06  |

## Printable Tags

Polyethylene material that is tear and chemical/solvent resistance.




Figure 21




Figure 32



### Tags



| Diagram | Part Number  | Labels/Roll | Material | Color | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)    | Recommended Ribbon | Price    |
|---------|--------------|-------------|----------|-------|--------|--------------------------|--------|---------|--------------------|----------|
| Fig. 21 | M71-36-109   | 250         | B-109    | White | 1.13   | (28.57)                  | 1.75   | (44.45) | M71-R4300          | \$45.94  |
| Fig. 32 | BM71-12-109* | 1000        | B-109    | White | 3.00   | (76.20)                  | 0.75   | (19.05) | M71-R4300          | \$240.19 |
| Fig. 32 | M71-12-109   | 100         | B-109    | White | 3.00   | (76.20)                  | 0.75   | (19.05) | M71-R4300          | \$34.33  |

\* "B" indicates bulk roll.

\* See all ribbon colors on page 14.

## Tamper Indicating

Tamper resistant tape destructs into tiny fragments when being removed. Making any attempts to remove the label very difficult and time consuming.



### Tamper Resistant Labels


| Diagram | Part Number | Labels/Roll | Material | Color  | Label Dimensions |         |        |         | Recommended Ribbon | Price   |
|---------|-------------|-------------|----------|--------|------------------|---------|--------|---------|--------------------|---------|
|         |             |             |          |        | A Inch           | (mm)    | B Inch | (mm)    |                    |         |
| Fig. 4  | M71-17-352  | 500         | B-352    | Silver | 1.00             | (25.40) | 0.50   | (12.70) | M71-R6000          | \$50.09 |
| Fig. 4  | M71-17-351  | 500         | B-351    | White  | 1.00             | (25.40) | 0.50   | (12.70) | M71-R6200          | \$49.73 |
| Fig. 4  | M71-31-352  | 250         | B-352    | Silver | 1.50             | (38.10) | 1.00   | (25.40) | M71-R6000          | \$39.95 |
| Fig. 4  | M71-31-351  | 250         | B-351    | White  | 1.50             | (38.10) | 1.00   | (25.40) | M71-R6200          | \$39.95 |
| Fig. 4  | M71-20-352  | 100         | B-352    | Silver | 2.00             | (50.80) | 1.00   | (25.40) | M71-R6000          | \$30.53 |
| Fig. 4  | M71-20-351  | 100         | B-351    | White  | 2.00             | (50.80) | 1.00   | (25.40) | M71-R6200          | \$30.53 |
| Fig. 4  | M71-37-352  | 100         | B-352    | Silver | 3.00             | (76.20) | 1.90   | (48.26) | M71-R6000          | \$44.10 |
| Fig. 4  | M71-37-351  | 100         | B-351    | White  | 3.00             | (76.20) | 1.90   | (48.26) | M71-R6200          | \$44.22 |

### Specialty Continuous Tape

| Diagram | Part Number   | Labels/Roll    | Material | Color | Label Dimensions |         |        |           | Recommended Ribbon | Price    |
|---------|---------------|----------------|----------|-------|------------------|---------|--------|-----------|--------------------|----------|
|         |               |                |          |       | A Inch           | (mm)    | B Inch | (mm)      |                    |          |
| Fig. 8  | M71C-500-530  | 1 Roll (cont.) | B-530    | White | 0.50             | (12.70) | 50 ft. | (15.24 m) | M71-R6000          | \$53.21  |
| Fig. 8  | M71C-1000-530 | 1 Roll (cont.) | B-530    | White | 1.00             | (25.40) | 50 ft. | (15.24 m) | M71-R6000          | \$70.53  |
| Fig. 8  | M71C-2000-530 | 1 Roll (cont.) | B-530    | White | 2.00             | (50.80) | 50 ft. | (15.24 m) | M71-R6000          | \$105.17 |

## Static Dissipative

Low profile polyimide material that has a static dissipative liner. Primarily used for printed circuit boards and electronic component labeling.






### Die Cut Labels

| Diagram | Part Number | Labels/Roll | Material | Color | Label Dimensions |         |        |         | Recommended Ribbon | Price    |
|---------|-------------|-------------|----------|-------|------------------|---------|--------|---------|--------------------|----------|
|         |             |             |          |       | A Inch           | (mm)    | B Inch | (mm)    |                    |          |
| Fig. 4  | M71-4-478   | 500         | B-478    | White | 0.40             | (10.16) | 0.40   | (10.16) | M71-R6000          | \$72.44  |
| Fig. 4  | M71-9-478   | 750         | B-478    | White | 0.65             | (16.51) | 0.20   | (5.08)  | M71-R6000          | \$108.72 |
| Fig. 4  | M71-14-477  | 750         | B-477    | White | 1.00             | (25.40) | 0.19   | (4.75)  | M71-R6000          | \$140.13 |
| Fig. 4  | M71-25-478  | 750         | B-478    | White | 1.25             | (31.75) | 0.25   | (6.35)  | M71-R6000          | \$137.08 |
| Fig. 4  | M71-2-477   | 100         | B-477    | White | 2.00             | (50.80) | 0.25   | (6.35)  | M71-R6000          | \$39.71  |

## Laboratory Identification

Self Laminating labels are great for vials, tubes, straws and more. Good for high and low temperature applications.



### Self Laminating Labels

| Diagram | Part Number  | Labels/Roll | Material | Color | Label Dimensions |              |        |         | Recommended Ribbon | Price    |
|---------|--------------|-------------|----------|-------|------------------|--------------|--------|---------|--------------------|----------|
|         |              |             |          |       | A Inch           | (mm)         | B Inch | (mm)    |                    |          |
| Fig. 1  | M71-82-499   | 500         | B-499    | White | 0.37 dia.        | (9.53 dia.)  | —      | —       | M71-R4300          | \$31.52  |
| Fig. 1  | M71-83-499   | 500         | B-499    | White | 0.50 dia.        | (12.70 dia.) | —      | —       | M71-R4300          | \$31.52  |
| Fig. 15 | M71-98-499   | 500         | B-499    | White | 1.00             | (25.40)      | 0.38   | (9.53)  | M71-R4300          | \$62.19  |
| Fig. 18 | BM71-75-461* | 1000        | B-461    | White | 1.00             | (25.40)      | 2.63   | (66.68) | M71-R4300          | \$233.97 |

## Temporary/Removable

These indoor labels are designed with special adhesive that makes it easy to remove and re-apply.



Figure 8



### Specialty Continuous Tape

| Diagram | Part Number      | Labels/Roll    | Material | Color  | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)      | Recommened Ribbon | Price   |
|---------|------------------|----------------|----------|--------|--------|--------------------------|--------|-----------|-------------------|---------|
| Fig. 8  | M71C-500-581-WT  | 1 Roll (cont.) | B-581    | White  | 0.50   | (12.70)                  | 50 ft. | (15.24 m) | M71-R6000         | \$46.56 |
| Fig. 8  | M71C-500-581-YL  | 1 Roll (cont.) | B-581    | Yellow | 0.50   | (12.70)                  | 50 ft. | (15.24 m) | M71-R6000         | \$46.56 |
| Fig. 8  | M71C-1000-581-WT | 1 Roll (cont.) | B-581    | White  | 1.00   | (25.40)                  | 50 ft. | (15.24 m) | M71-R6000         | \$65.21 |
| Fig. 8  | M71C-1000-581-YL | 1 Roll (cont.) | B-581    | Yellow | 1.00   | (25.40)                  | 50 ft. | (15.24 m) | M71-R6000         | \$65.21 |
| Fig. 8  | M71C-2000-581-WT | 1 Roll (cont.) | B-581    | White  | 2.00   | (50.80)                  | 50 ft. | (15.24 m) | M71-R6000         | \$98.50 |
| Fig. 8  | M71C-2000-581-YL | 1 Roll (cont.) | B-581    | Yellow | 2.00   | (50.80)                  | 50 ft. | (15.24 m) | M71-R6000         | \$98.50 |

## Low Light Applications

B-582 Bradyglo phosphorescent material is light absorbing and will glow for 10 hours. B-584 reflective material helps to illuminate the labels when light is shined on the surface.

These two materials are great for egress and other critical pieces of information.




Figure 8



### Specialty Continuous Tape

| Diagram | Part Number        | Labels/Roll    | Material | Color          | A Inch | Label Dimensions<br>(mm) | B Inch | (mm)      | Recommened Ribbon | Price    |
|---------|--------------------|----------------|----------|----------------|--------|--------------------------|--------|-----------|-------------------|----------|
| Fig. 8  | BM71C-1000-584-OR* | 1 Roll (cont.) | B-584    | Orange         | 1.00   | (25.40)                  | 75 ft. | (22.86 m) | M71-R6000         | \$122.00 |
| Fig. 8  | BM71C-1000-584-WT* | 1 Roll (cont.) | B-584    | White          | 1.00   | (25.40)                  | 75 ft. | (22.86 m) | M71-R6000         | \$122.00 |
| Fig. 8  | BM71C-1000-584-YL* | 1 Roll (cont.) | B-584    | Yellow         | 1.00   | (25.40)                  | 75 ft. | (22.86 m) | M71-R6000         | \$122.00 |
| Fig. 8  | BM71C-1000-582*    | 1 Roll (cont.) | B-582    | Phosphorescent | 1.00   | (25.40)                  | 75 ft. | (22.86 m) | M71-R6000         | \$122.00 |
| Fig. 8  | BM71C-2000-584-OR* | 1 Roll (cont.) | B-584    | Orange         | 2.00   | (50.80)                  | 75 ft. | (22.86 m) | M71-R6000         | \$195.42 |
| Fig. 8  | BM71C-2000-584-WT* | 1 Roll (cont.) | B-584    | White          | 2.00   | (50.80)                  | 75 ft. | (22.86 m) | M71-R6000         | \$195.42 |
| Fig. 8  | BM71C-2000-584-YL* | 1 Roll (cont.) | B-584    | Yellow         | 2.00   | (50.80)                  | 75 ft. | (22.86 m) | M71-R6000         | \$195.42 |
| Fig. 8  | BM71C-2000-582*    | 1 Roll (cont.) | B-582    | Phosphorescent | 2.00   | (50.80)                  | 75 ft. | (22.86 m) | M71-R6000         | \$195.42 |

\* "B" indicates bulk roll.

\* See all ribbon colors on page 14.

## ToughStripe® Print-On-Demand Floor Labels

- Create custom-printed floor labels using your BMP®71 Label Printer!
- Same durability and performance as ToughStripe® floor marking tape
- Easy 3-step process: print label, position on floor, apply overlamine




Figure 8



| Description | Catalog Number       |                      |
|-------------|----------------------|----------------------|
|             | 1" x 100' (\$122.40) | 2" x 100' (\$183.70) |
| White       | M71-1000-483-WT-KT   | M71-2000-483-WT-KT   |
| Black       | M71-1000-483-BK-KT   | M71-2000-483-BK-KT   |
| Yellow      | M71-1000-483-YL-KT   | M71-2000-483-YL-KT   |
| Red         | M71-1000-483-RD-KT   | M71-2000-483-RD-KT   |
| Blue        | M71-1000-483-BL-KT   | M71-2000-483-BL-KT   |
| Green       | M71-1000-483-GN-KT   | M71-2000-483-GN-KT   |
| Orange      | M71-1000-483-OR-KT   | M71-2000-483-OR-KT   |





## BMP®71 Ribbons

| Part Number  | Description  | Size           | Price   | Part Number  | Description    | Size           | Price   |
|--------------|--------------|----------------|---------|--------------|----------------|----------------|---------|
| M71-R4300    | Black Ribbon | 150' (45.72 m) | \$53.66 | M71-R6800-WT | White Ribbon   | 150' (45.72 m) | \$69.85 |
| M71-R6000    | Black Ribbon | 150' (45.72 m) | \$53.66 | M71-R6900-RD | Red Ribbon     | 150' (45.72 m) | \$63.42 |
| M71-R6200    | Black Ribbon | 150' (45.72 m) | \$53.66 | M71-R6900-BL | Blue Ribbon    | 150' (45.72 m) | \$63.42 |
| M71-R6400    | Black Ribbon | 150' (45.72 m) | \$59.02 | M71-R6900-GR | Green Ribbon   | 150' (45.72 m) | \$63.42 |
| M71-R6600    | Black Ribbon | 150' (45.72 m) | \$69.85 | M71-R6900-MA | Magenta Ribbon | 150' (45.72 m) | \$63.42 |
| M71-R4400-WT | White Ribbon | 150' (45.72 m) | \$63.42 | M71-R6900-YL | Yellow Ribbon  | 150' (45.72 m) | \$51.16 |

| B-Number | Material                              | M71-R4300<br>(Black) | M71-R6000<br>(Black) | M71-R6200<br>(Black) | M71-R6400<br>(Black) | M71-R6600<br>(Black) | M71-R4400-WT<br>(White) | M71-R6800-WT<br>(White) | M71-R6900<br>(Colors) |
|----------|---------------------------------------|----------------------|----------------------|----------------------|----------------------|----------------------|-------------------------|-------------------------|-----------------------|
| B-109    | Tag                                   | ●                    | —                    | ▲                    | —                    | —                    | —                       | —                       | —                     |
| B-145    | Tag                                   | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | —                     |
| B-145FR  | Tag                                   | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-321*   | Polyolefin                            | —                    | —                    | ●                    | —                    | —                    | —                       | —                       | —                     |
| B-341    | Polyolefin                            | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-342    | Polyolefin                            | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-345*   | High Temp Sleeve                      | —                    | —                    | —                    | —                    | ●                    | —                       | ▲                       | —                     |
| B-351    | Vinyl                                 | —                    | —                    | ●                    | —                    | —                    | —                       | —                       | —                     |
| B-352    | Vinyl                                 | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-353*   | Paper                                 | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-390*   | Polypropylene                         | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-412    | Polypropylene                         | ▲                    | —                    | ●                    | —                    | —                    | —                       | —                       | —                     |
| B-422    | Polyester                             | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-423    | Polyester                             | —                    | ● UL                 | ▲                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-424    | Paper                                 | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-425    | Polyimide                             | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-426    | Polyimide                             | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-427    | Vinyl                                 | ● UL                 | —                    | ▲                    | —                    | —                    | —                       | —                       | —                     |
| B-428    | Polyester                             | ● UL                 | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-430    | Polyester                             | —                    | ● UL                 | ▲                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-432*   | Polyester                             | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-433*   | Polyester                             | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-435*   | Polyester                             | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-439*   | Vinyl                                 | —                    | ●                    | ▲                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-457    | Polyimide                             | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-459    | Polyester                             | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-461    | Polyester                             | ●                    | —                    | ▲                    | —                    | —                    | —                       | —                       | —                     |
| B-473    | Polyester                             | —                    | ● UL                 | ▲                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-477    | Polyimide                             | —                    | ● UL                 | ▲                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-478    | Polyimide                             | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-479*   | Polyimide                             | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-481*   | Polyester                             | —                    | —                    | —                    | ●                    | —                    | —                       | —                       | —                     |
| B-483    | Polyester                             | —                    | ● UL                 | ▲                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-486    | Polyester                             | ● UL                 | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-488    | Polyester                             | ● UL                 | —                    | ▲                    | —                    | —                    | —                       | —                       | —                     |
| B-489    | Polyester                             | ● UL                 | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-490*   | Polyester                             | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-495*   | Polyethylene Napthalate               | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-498    | Vinyl Cloth                           | ▲                    | —                    | ●                    | —                    | —                    | —                       | —                       | —                     |
| B-499    | Nylon Cloth                           | ● UL                 | —                    | ▲                    | —                    | —                    | —                       | —                       | —                     |
| B-529    | Polypropylene                         | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-530    | Tamper Resistant                      | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-595    | Vinyl                                 | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-581    | Vinyl                                 | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-582    | Phosphorescent                        | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-584    | Reflective                            | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-593    | Polyester                             | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-7531*  | Metalized Polyester                   | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-7536*  | Polyester                             | —                    | —                    | ●                    | —                    | —                    | —                       | —                       | —                     |
| B-7546*  | Tamper-Evident Polyester              | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-7551*  | Polyester                             | —                    | —                    | ●                    | —                    | —                    | —                       | —                       | —                     |
| B-7566*  | Tamper-Evident Polyester              | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-7576*  | Tamper-Evident Metalized Polyester    | —                    | ● UL                 | —                    | —                    | —                    | —                       | —                       | —                     |
| B-7593*  | Polyethelene                          | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-7596*  | Vinyl                                 | —                    | —                    | ●                    | —                    | —                    | —                       | —                       | —                     |
| B-7597*  | Polyethelene                          | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-7599*  | Polyethelene Tag                      | ●                    | —                    | —                    | —                    | —                    | —                       | —                       | —                     |
| B-7643*  | Thermosplastic Polyether Polyurethane | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-7696*  | Vinyl Tag                             | —                    | ●                    | —                    | —                    | —                    | ▲                       | —                       | ▲                     |
| B-8425*  | Polypropylene                         | —                    | ● UL                 | —                    | —                    | —                    | ▲                       | —                       | ▲                     |

\*TLS@2200 materials that can be used in the BMP®71 Label Printer.

|    |                                                               |
|----|---------------------------------------------------------------|
| ●  | Recommended ribbon for use with respective material.          |
| ▲  | Acceptable ribbon for use with respective material.           |
| UL | These materials are UL recognized with its respective ribbon. |



# BMP®71 PRINTER APPLICATIONS

## Visual Workplace



M71C-1000-580-WT M71-R6900BL

## Multi-Line Labels



M71C-2000-580-RD M71-R6900WT

## Vinyl Pipe Markers Up To 2” Wide



M71C-1000-580-BL  
M71-R6900WT



## Glow-In-The-Dark



M71C-1000-582 M71-R6900GN

## Floor Labeling Solutions




M71C-2000-580-YL M71-R6000



# SEE THE POSSIBILITIES WITH THE E

Work Station Labels



M71-40-412 M71-R6200

Die Cut Labels




M71-7-423 M71-R6000

Equipment Labels



M71-30-428-CALI M71-R4300

Patch Panel Labels




M71C-375-422 M71-R6000

Power and Ground Cable Tags



M71-111-145FR-GY M71-R6000

Flags/Fiber Optic Labels



M71FP-2-425 M71-R4300


M71FD-2-425 M71-R4300

Wire Bundle Labels




M71-12-109 M71-R4300

PermaSleeve™ Heat-Shrink Sleeves



BM71-187-1-342 M71-R4300

Self-Laminating Labels



M71-31-427-YL M71-R4300

# 3MP®71 LABEL PRINTER

## Arc Flash Labels




M71-38-483-WARN M71-R6000

## Labels Withstand High Temperatures



M71-38-483-DANG M71-R6000

## Framed Labels



M71-24-423-BK M71-R6000

## Control Panel Labels



M71EP-167-593-RD M71-R6000

## Pre-Printed Labels




M71-25-478 M71-R6000

## Create Tags With Bar Codes



M71-20-423 M71-R6000

## Tamper Indicating Tape



M71-17-352 M71-R6000

\* Most labels are actual size.

THE ALL-IN-ONE LABELER FOR YOUR WHOLE CREW

| Catalog Number | Description                                                     | Catalog Number | Description                                           |
|----------------|-----------------------------------------------------------------|----------------|-------------------------------------------------------|
| BMP71*         | BMP®71 Label Printer                                            | BMP71-SC-QC    | BMP®71 Label Printer with Soft Case and Quick Charger |
| BMP71-LM       | BMP®71 Label Printer with LabelMark Software                    | M71-AC-BC      | BMP®71 AC/Battery Adaptor                             |
| BMP71-MW       | BMP®71 Label Printer with Markware Lean Software                | M71-ADAPT      | TLS/Handimark Media Adaptor                           |
| BMP71-360-KIT  | BMP®71 Label Printer with Brady 360 Replacement Printer Program | M71-BATT       | BMP®71 Battery Pack                                   |
| BMP71-QC       | BMP®71 Label Printer with Quick Charger                         | M71-CABLE      | BMP®71 USB Cable                                      |
| BMP71-SC       | BMP®71 Label Printer with Soft Case                             | M71-CLEAN      | BMP®71 Cleaning Kit                                   |
|                |                                                                 | M71-HC         | BMP®71 Hardcase                                       |
|                |                                                                 | M71-QC         | BMP®71 Quick Charger                                  |
|                |                                                                 | M71-SC         | BMP®71 Softcase                                       |
|                |                                                                 | BMP71-360      | Brady 360 Replacement Printer Program                 |



**BMP®71** LABEL PRINTER  
\*Label printer ships with Hardcase, Charger/ AC Adapter, 1 Roll of M71-31-423 White Die Cut Labels, 1 R6000 Black Ribbon Cartridge, Roll Adapter, USB Cable, Quickstart Guide, a CD including the Printer Driver, Users Guide and Tutorial.

WATCH A DEMO VIDEO OR REQUEST A FREE SAMPLE PACK AT:  
[www.BradyID.com/bmp71](http://www.BradyID.com/bmp71)  
[www.BradyCanada.ca/bmp71](http://www.BradyCanada.ca/bmp71)



Brady 360™ Replacement Printer Program

The Brady 360™ Printer Replacement Plan supplements the Limited Warranty already provided to you with the purchase of your Brady printer. With this plan, Brady Corporation, in its reasonable discretion, will send a replacement printer in the event that your covered printer requires service during the term of its Limited Warranty. Brady will replace your defective printer with a new printer that has the same or similar functionality and is of the same or greater value.

Limit two new replacement printers per covered printer in each warranty period. The plan must be purchased at the time of printer purchase to be valid.

\*\* Limit of two printers in the first 12 months of initial purchase.

Terms of Brady Corporation's BMP®71 warranty can be found at:  
[www.BradyID.com/bmp71](http://www.BradyID.com/bmp71)  
[www.BradyCanada.ca/bmp71](http://www.BradyCanada.ca/bmp71)

USA  
1-888-272-3946  
[www.BradyID.com](http://www.BradyID.com)  
  
Canada  
1-800-263-6179  
[www.BradyCanada.ca](http://www.BradyCanada.ca)  
  
Mexico  
1-800-262-7777  
[www.BradyLatinAmerica.com](http://www.BradyLatinAmerica.com)

