


HALOGEN (H3 55W) Details

Back



Part #	H3 55W				
Description	H3 12V 55W PK22S				
Bulb Shape	T3 1/4	Filament	C-6	Base Style	PK22s
Glass Diameter	0.45 in/ 11.43 mm	Lumens	1450	Base Material	Metal
Design Wattage	68	MSCP [†]	115	RoHS Compliant	Yes
Design Voltage	13.2	MOL [‡]	1.65 in/ 41.91 mm	Rated Avg Life Hrs	400
Design Amps	4.58	LCL ^{††}	0.70 in/ 17.78 mm	Headlight Socket	

[†] **MSCP (Mean Spherical Candlepower):**
 Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

[‡] **MOL (Maximum Overall Length):**
 The overall length of a lamp, from the top of the shell to the bottom of the base.

^{††} **LCL (Light Center Length):**
 The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.