

**Enclosure
KLIPPON K61****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon has stood for competence and quality in enclosures and customer-specific, connection-ready applications. Customer satisfaction is our number one priority. That is why we have updated and modernized our line of aluminium housings. These are improved products for all application requirements.

General ordering data

Order No.	0573600000
Part designation	KLIPPON K61
Version	Enclosures, 160 mm, 91 mm, 260 mm, Aluminium AlSi12
GTIN (EAN)	4008190126919
Qty.	1 pc(s).

Enclosure KLIPPON K61

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions (1)

Weight	2,060 g	Length	91 mm
Width	260 mm	Height	160 mm
Fixing dimension, width	240 mm		

General information

Fixing dimension, width	240 mm	Material	Aluminium AISi12
Surface	untreated	Cover fixing	M4 torx stainless steel screws with slot
Enclosure fixing	Holes 4 mm	Integral fixing	threaded holes M6
Material	Aluminium AISi12	Resistance to shocks	10.00 J
Sealing material	Neoprene	Surface	untreated

Cable glands top/bottom

M 12	27	M 16	23
M 40	3	M20	13
M25	8	M32	4
Side of enclosure	left right		

cable glands, left

M 12 (3)	8	M 20 (3)	3
----------	---	----------	---

cable glands, right

M 12 (2)	8	M 16 (2)	6
M 20 (2)	3	M 25 (2)	2
M 32 (2)	1	M 40 (2)	1
Side of enclosure	left right		

horizontal assembly

WDU 10 / ZDU 10	1x19	WDU 16 / ZDU 16	1x16
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x38	WDU 4 / ZDU 4	1x32
WDU 6 / ZDU 6	1x24		

Approvals

Approvals institutes	CULUS; GERMLLOYD; GOSTME25; MARITREG
----------------------	---

Classifications

eClass 5.1	27-14-91-07	eClass 6.0	27-14-91-07
------------	-------------	------------	-------------