

M23-Round-Plug Connector, Single-Ended Cordsets


RSUF | RKU | RKUE



12- and 19-Poles


M23 cordsets, single ended, male straight connector, 12- and 19-poles with threaded joint, external threads and molded cable.

RSUF



M23 cordsets, single ended, female straight connector, 12- and 19-poles with threaded joint, internal threads and molded cable.


RKU/RKUE



Pin Assignments


M23 - Male / Female

12 poles



- 1 = white
- 2 = green
- 3 = yellow
- 4 = grey
- 5 = grey/pink
- 6 = red/blue
- 7 = white/green
- 8 = brown/green
- 9 = blue
- 10 = blue
- 11 = brown
- 12 = yellow/green

19 poles



- 1 = violet
- 2 = red
- 3 = grey
- 4 = red/blue
- 5 = green
- 6 = blue
- 7 = grey/pink
- 8 = white/green
- 9 = white/yellow
- 10 = white/grey
- 11 = black
- 12 = yellow/green
- 13 = yellow/brown
- 14 = brown/green
- 15 = white
- 16 = yellow
- 17 = pink
- 18 = grey/brown
- 19 = brown

RSUF | RKU | RKUE

Environmental

Mechanical

Electrical

Cable Specifications

Part Number		Pins	Outer Jacket	Standard Cable Lengths	Characteristics
RSUF 12-256/...M	RKU 12-256/...M	12	PUR, halogen-free	5 M / 10 M / 15 M / 20 M	  
RSUF 19-242/...M	RKU 19-242/...M	19	PUR, halogen-free	5 M / 10 M / 15 M / 20 M	  
	RKUE 19-242/...M		PUR, halogen-free	5 M / 10 M / 15 M / 20 M	  