



These same products are available in larger, bulk packaging at substantial savings. Add 1 to the Allied Stock No. to get the same part in bulk.

Butt-Type Splices

Nylon Insulated — Fig. A

Stock No.	Mfr.'s Type	Wire Range	Length	Width	Pkg. Qty.	PER PKG.	
						1-4	5-9
534-0660	2RA18	22-18	1.19	0.18	100	54.51	44.60
534-0665	2RB14	16-14	1.19	0.21	100	54.51	44.60
534-0670	2RC10	12-10	1.26	0.28	50	39.93	32.66
534-0675	2RD8	8	1.69	—	25	43.47	35.58
534-0680	2RE6	6	1.85	—	20	40.65	33.26
534-0685	2RF4	4	1.85	—	15	36.26	29.67

Vinyl Insulated — Fig. B

534-0690	2RA18X	22-18	1.13	0.25	100	42.36	34.66
534-0695	2RB14X	16-14	1.13	0.26	100	41.96	34.32
534-0700	2RC10X	12-10	1.31	0.31	50	31.12	25.45

Non-Insulated — Fig. C

534-0705	2A-18	22-18	0.62	0.12	100	29.07	23.79
534-0710	2B-14	16-14	0.62	0.16	100	30.36	24.86
534-0715	2C-10	12-10	0.72	0.22	50	21.37	17.48
534-0720	2D-8	9-8-7	1.03	0.28	25	25.94	21.22
534-0725	2E-6	6-5	1.12	0.37	20	27.48	22.50
534-0730	2F-4	4-3	1.25	0.44	15	32.53	26.63
534-0735	2G21	2-1	1.72	0.55	5	14.06	11.40

Locking Fork Terminals

Vinyl Insulated — Fig. D

These have a specially designed tongue that lets them go on like a fork and stay on like a ring.

Stock No.	Mfr.'s Type	Wire Range	Bolt Hole	Length	Width	Pkg. Qty.	PER PKG.	
							1-4	5-9
534-0740	18RA-6FL	22-18	6	0.97	0.25	100	43.77	35.80
534-0745	18RA-8FL	22-18	8	0.97	0.29	100	43.77	35.79
534-0750	18RA-10FL	22-18	10	0.97	0.29	100	43.80	35.84
534-0755	14RB-6FL	16-14	6	0.97	0.25	100	45.63	37.34
534-0760	14RB-8FL	16-14	8	0.97	0.29	100	45.63	37.35
534-0765	14RB-10FL	16-14	10	0.97	0.29	100	45.63	37.33
534-0770	10RC-6FL	12-10	6	1.09	0.31	50	28.28	23.14
534-0775	10RC-8FL	12-10	8	1.09	0.37	50	36.44	29.83
534-0780	10RC-10FL	12-10	10	1.09	0.37	50	29.64	24.25
534-0782	10RC-14FL	12-10	1/4"	1.09	0.49	50	37.40	30.60

Nylon Insulated — Fig. D

534-0785	RA18-6FL	22-18	6	0.86	0.25	100	62.15	50.86
534-0790	RA18-8FL	22-18	8	0.86	0.29	100	57.48	47.02
534-0795	RA18-10FL	22-18	10	0.86	0.29	100	46.63	39.95
534-0800	RB14-6FL	16-14	6	0.87	0.25	100	44.83	38.43
534-0805	RB14-8FL	16-14	8	0.87	0.29	100	44.39	38.05
534-0810	RB14-10FL	16-14	10	0.87	0.29	100	44.83	38.44
534-0815	RC10-6FL	12-10	6	0.97	0.31	50	32.78	27.31
534-0820	RC10-8FL	12-10	8	1.00	0.37	50	28.30	24.26
534-0825	RC10-10FL	12-10	10	1.00	0.37	50	28.31	24.26
534-0830	RC10-14FL	12-10	1/4"	1.12	0.50	50	29.72	25.48

Insulated Male Tabs

Mate with female disconnects on this page. **Material:** Brass. **Finish:** Tin-plated.

Vinyl Self-Insulated Male Tabs

Stock No.	Mfr.'s Type	Fig.	Wire Range	Tab Size (In.)	Pkg. Qty.	PER PKG.	
						1-4	5-9
534-0575	18RA-250T	E	22-18	0.250 × 0.032	100	45.00	38.07
534-0580	18RAD-187	F	22-18	0.187 × 0.032	100	50.76	42.95
534-0585	18RAD-188	F	22-18	0.187 × 0.020	100	50.76	42.95
534-0590	14RB-250T	E	16-14	0.250 × 0.032	100	46.47	39.33
534-0595	14RBD-187	F	16-14	0.187 × 0.032	100	46.86	39.65
534-0600	14RBD-188	F	16-14	0.187 × 0.020	100	43.55	36.86
534-0605	10RC-250T	E	12-10	0.250 × 0.032	50	26.08	22.06

Nylon Fully Insulated Male Tabs

Stock No.	Mfr.'s Type	Fig.	Wire Range	Tab Size (In.)	Pkg. Qty.	PER PKG.	
						1-4	5-9
534-0610	18RA-251T	F	22-18	0.250 × 0.032	50	28.48	23.29
534-0615	14RB-251T	F	16-14	0.250 × 0.032	50	29.38	24.03
534-0620	10RC-251T	F	12-10	0.250 × 0.032	25	18.31	15.00

Non-Insulated Male Tabs

Stock No.	Mfr.'s Type	Fig.	Wire Range	Tab Size (In.)	Pkg. Qty.	PER PKG.	
						1-4	5-9
534-0625	A18-251T	G	22-18	0.250 × 0.032	100	36.33	29.72
534-0640	B14-251T	G	16-14	0.250 × 0.032	100	36.78	30.09
534-0655	C10-251T	G	12-10	0.250 × 0.032	50	19.47	15.93

Nylon Insulated Female Disconnects

Stock No.	Mfr.'s Type	Fig.	Wire Range	Tab Size (In.)	Pkg. Qty.	PER PKG.	
						1-4	5-9
534-0400	RA18-250F	H	22-18	0.250 × 0.032	100	52.39	43.66
534-0405	RAD18-183	H	22-18	0.187 × 0.032	100	51.01	43.15
534-0410	RAD18-182	H	22-18	0.187 × 0.020	100	50.99	43.14
534-0415	RA18-111F	H	22-18	0.110 × 0.020	100	52.47	44.41
534-0420	RA18-110F	H	22-18	0.110 × 0.032	100	50.47	42.71
534-0425	18RA-2577	J	22-18	0.250 × 0.032	100	48.57	41.09
534-0430	18RAD-18377	J	22-18	0.187 × 0.032	100	48.90	41.37
534-0435	18RAD-18277	J	22-18	0.187 × 0.020	100	53.79	44.82
534-0440	RB14-250F	H	16-14	0.250 × 0.032	100	49.61	41.97
534-0445	RBD14-183	H	16-14	0.187 × 0.032	100	55.88	47.28
534-0450	RBD14-182	H	16-14	0.187 × 0.020	100	58.08	49.14
534-0455	RB14-111F	H	16-14	0.110 × 0.020	100	52.47	44.41
534-0460	RB14-110F	H	16-14	0.110 × 0.032	100	50.48	42.71
534-0465	14RB-2577	J	16-14	0.250 × 0.032	100	48.09	40.69
534-0470	14RBD-18377	J	16-14	0.187 × 0.032	100	48.44	40.99
534-0475	14RBD-18277	J	16-14	0.187 × 0.020	100	48.44	40.99
534-0480	RC10-250F	H	12-10	0.250 × 0.032	50	32.48	27.49
534-0485	10RC-2577	J	12-10	0.250 × 0.032	50	29.55	25.01

Vinyl Insulated Female Disconnects

Stock No.	Mfr.'s Type	Fig.	Wire Range	Tab Size (In.)	Pkg. Qty.	PER PKG.	
						1-4	5-9
534-0490	18RA-250F	H	22-18	0.250 × 0.032	100	46.60	39.44
534-0495	18RAD-183	H	22-18	0.187 × 0.032	100	45.85	38.78
534-0500	18RAD-182	H	22-18	0.187 × 0.020	100	45.84	38.78
534-0505	14RB-250F	H	16-14	0.250 × 0.032	100	46.60	39.43
534-0510	14RBD-183	H	16-14	0.187 × 0.032	100	40.87	34.59
534-0515	14RBD-182	H	16-14	0.187 × 0.020	100	42.49	35.95
534-0520	10RC-250F	H	12-10	0.250 × 0.032	50	29.04	24.57

Non-Insulated Female Disconnects

Stock No.	Mfr.'s Type	Fig.	Wire Range	Tab Size (In.)	Pkg. Qty.	PER PKG.	
						1-4	5-9
534-0525	A18-250	K	22-18	0.250 × 0.032	100	28.06	23.75
534-0530	A18-250A	L	22-18	0.250 × 0.032	50	16.31	13.78
534-0535	AD18-183	K	22-18	0.187 × 0.032	100	31.02	26.25
534-0540	AD18-182	K	22-18	0.187 × 0.020	100	32.52	27.52
534-0545	B14-250	K	16-14	0.250 × 0.032	100	26.97	22.83
534-0550	B14-250A	L	16-14	0.250 × 0.032	50	16.84	14.08
534-0555	BD14-183	K	16-14	0.187 × 0.032	100	31.02	26.25
534-0560	BD14-182	K	16-14	0.187 × 0.020	100	31.03	26.25
534-0565	C10-250F	K	12-10	0.250 × 0.032	50	26.84	22.71
534-0570	C10-250A	L	12-10	0.250 × 0.032	50	28.40	24.03