

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0465621044

Status:

Active

Overview:

EXTreme Ten60Power High-Current Connector

Description:

2.00mm, 5.50mm Pitch EXTreme Ten60Power Vertical Receptacle Assembly with Top Guide Receiver, 25 Signal Circuits, 2 Power Circuits

Documents:

Drawing (PDF)

Product Specification PS-46436-100-001 (PDF)

Application Specification AS-46436-100-001 (PDF)

Packaging Specification PK-46562-002-000 (PDF)

Packaging Specification PK-46562-1044 (PDF)

Test Summary 464361000-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

Application tooling part link

Application Tooling Part Link

62100-7900

General

Product Family

Series

Application

Comments

Overview

Product Name

UPC

PCB Receptacles

46562

Board-to-Board, Power

See PS-46436-100 for details

EXTreme Ten60Power High-Current Connector

EXTreme Ten60Power

884982559851

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

27

27

Black

200

94V-0

No

Yes

None

No

Copper

Gold

Tin

High Temperature Thermoplastic

9.912/g

1

Vertical

No

None

1.58mm

Tray

2.54mm, 5.50mm

0.127µm

2.540µm


Yes

Yes

No

No

-40° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

46562 Series

Mates With

464371044 EXTreme Ten60Power Right Angle Plug Assembly

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Removal Tool for Ten60 Power Receptacle Terminals

621007900

Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	2.5A, 55.0A
Grounding to PCB	No
Voltage - Maximum	600V AC / 250V DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-46436-100-001
Packaging Specification	PK-46562-002-000, PK-46562-1044
Product Specification	PS-46436-100-001
Sales Drawing	SD-46562-1044-001
Test Summary	464361000-TS-000

This document was generated on 08/18/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION