

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.




E

D


C

B

A



OPTIONAL INSULATING BARRIER



DIMENSIONS IN INCHES (MILLIMETERS)
DO NOT SCALE DRAWING


Dwg. No.

GRS-4021B-XXXX

MOUNTING PANEL THICKNESS

Standard—.050" (1.27mm) to .150" (3.81mm).

Optional Mounting Claws for Custom Panel thickness are available.



TAB AND POLARIZATION OPTIONS

TERMINAL OPTIONS:

.187" (4.75mm) x .032" (.81mm) Solderless
.110" (2.79mm) x .032" (.81mm) Solderless
.187" (4.75mm) x .020" (.51mm) Solderless
.110" (2.79mm) wide with .048" (1.22mm) x .237" (6.02mm) Slot for Soldering

B-FORMAT 2002

REVISIONS

1 2 3 4 5 6 7 8 9 10



CW INDUSTRIES
Southampton, Pa. 18966

Title:

**ROCKER
SWITCH
ASSEMBLY
D.P./S.T. MOM.**

TOLERANCES UNLESS OTHERWISE SPECIFIED
2 Place Decimal ±.010 METRIC
3 Place Decimal ±.005 1 Place Dec. ±.25mm
Angles ±1' 2 Place Dec. ±.13mm

Made for: CW IND.

Division:

SWITCH

Drawn by: DGW 10-28-2010

Dwg. No.

GRS-4021B-XXXX

Checked by:

Approval:

PDF FILE MADE