


All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:			DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
XXX	A	RELEASED	Ilivya	27-11-08	Suresh	27-11-08	JN	12/12/08



ITEM	DESCRIPTION	MATERIAL	FINISH
4	CABLE	-	-
3	TUBING	**HEAT SHRINK	BLACK
2	SMA FEMALE RELIEF	BRASS	NICKEL
1	SMA MALE CRIMP	BRASS	NICKEL

**DUAL WALL POLYOLEFIN

Manufacturer Part Number	Length	Cable Type	Strain Relief
SPC25307	12	RG-316/U	No
SPC25308	24	RG-316/U	No
90352CPS	63	U/613-GR	dN
SPC25310	48	RG-316/U	No
SPC25311	60	RG-316/U	No
SPC25312	72	RG-316/U	No
SPC25511	12	RG-174A/U	No
SPC25512	24	RG-174A/U	No
SPC25513	36	RG-174A/U	No
SPC25514	48	RG-174A/U	No
SPC25515	60	RG-174A/U	No
SPC25516	72	RG-174A/U	No
SPC25826	12	RG-55B/U	No
SPC25828	24	RG-55B/U	No
SPC25830	36	RG-55B/U	No
SPC25833	60	RG-55B/U	No
SPC25835	72	RG-55B/U	No
SPC25838	24	RG-58C/U	Yes
SPC25840	36	RG-58C/U	Yes
SPC25842	48	RG-58C/U	Yes
SPC25844	60	RG-58C/U	Yes
SPC25846	72	RG-58C/U	Yes
SPC25848	12	RG-142B/U	No
SPC25849	24	RG-142B/U	No

Disclaimer:

All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.



SPC TECHNOLOGY

Drawing Title:

SMA MALE CRIMP TO SMA FEMALE CRIMP

Size:
A

Dwg. No

TA-1012

Electronic File

Ta-1012.dwg

Rev
A

Scale: NTS

U.O.M.: Inches (mm)

Sheet: 1 of 2

Unless otherwise specified, Dimensions are for references purposes only.

Drawn By:

Ilivya

Date:

27-11-08

Checked By:

Suresh

Date:

27-11-08

Approved By:

Jason Nash

Date:

12/12/08

All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:				DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:		Drawn	Date	Checked	Date	Approved	Date
XXX	A	RELEASED		Ilivya	27-11-08	Suresh	27-11-08	JN	12/12/08



Manufacturer Part Number	Length	Cable Type	Strain Relief
SPC25850	36	RG-142B/U	No
SPC25851	48	RG-142B/U	No
SPC25852	60	RG-142B/U	No
SPC25853	72	RG-142B/U	No
SPC25854	12	RG-188A/U	No
SPC25855	24	RG-188A/U	No
SPC25856	36	RG-188A/U	No
SPC25857	48	RG-188A/U	No
SPC25858	60	RG-188A/U	No
SPC25859	72	RG-188A/U	No
SPC25860	12	RG-223/U	No
SPC25861	24	RG-223/U	No
SPC25862	36	RG-223/U	No
SPC25863	48	RG-223/U	No
SPC25864	60	RG-223/U	No
SPC25865	72	RG-223/U	No
SPC25866	12	RG-400/U	No
SPC25867	24	RG-400/U	No
SPC25868	36	RG-400/U	No
SPC25869	48	RG-400/U	No
SPC25870	60	RG-400/U	No
SPC25871	72	RG-400/U	No
SPC28508	12	RG-58A/U	Yes
SPC28510	24	RG-58A/U	Yes
SPC28514	60	RG-58A/U	Yes
SPC28516	72	RG-58A/U	Yes
SPC28518	12	LMR-195	No
SPC28519	24	LMR-195	No
SPC28520	36	LMR-195	No
SPC28521	48	LMR-195	No
SPC28522	60	LMR-195	No
SPC28523	72	LMR-195	No
SPC28524	12	LMR-100	No
SPC28525	24	LMR-100	No
SPC28526	36	LMR-100	No
SPC28527	48	LMR-100	No
SPC28528	60	LMR-100	No
SPC28529	72	LMR-100	No
SPC28530	12	RG-316/U DS	No
SPC28531	24	RG-316/U DS	No
SPC28532	36	RG-316/U DS	No
SPC28533	48	RG-316/U DS	No
SPC28534	60	RG-316/U DS	No
SPC28535	72	RG-316/U DS	No

Disclaimer:

All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.



SPC TECHNOLOGY

Unless otherwise specified, Dimensions are for references purposes only.

Drawn By:	Date:
Ilivya	27-11-08
Checked By:	Date:
Suresh	27-11-08
Approved By:	Date:
Jason Nash	12/12/08

Drawing Title:
SMA MALE CRIMP TO SMA FEMALE CRIMP

Size: A	Dwg. No TA-1012	Electronic File TA-1012.dwg	Rev A
---------	-----------------	-----------------------------	-------

Scale: NTS U.O.M.: Inches (mm) Sheet: 2 of 2