

- ▶ Cable Ties
- ▶ Cable Ties with Fasteners
- ▶ Cable Tie Tools
- ▶ Clamps and Clips
- ▶ Heatshrink Moulded Shapes
- ▶ Mounts
- ▶ Heavy Duty Mounts
- ▶ Wire Connectors
- ▶ Wiring Duct
- ▶ Wiring Protection
- ▶ Labels, Printers and Software
- ▶ Pre-Terminated Networking
- ▶ Copper Network Solutions
- ▶ Fiber Network Solutions
- ▶ Jacks and Wall Plates
- ▶ Racks - Cable Management
- ▶ Surface Raceway Systems

156-00594

Omega Clip Tie, 50lbs, Clip Dia .26"-.3" Max Bun Dia 1.38" PA66UV Tie, HIRHS MNT, BLK 500/pk

Article Number: 156-00594
Part Number: 156-00594
Type: T50ROC2



- ➔Find a Distributor
 - ➔Order Samples
 - ➔Get Technical Drawings
-     |  Share

➔Base Data

Part No.	156-00594
Type	T50ROC2
Color	Black (BK)
Features	Omega Clips secure cables to tubular frame rails. The UV stabilized cable tie is fastened to the tubular frame rail and the solar cable snaps into the clip. The cable can be removed from the clip and reinstalled without additional fasteners.
Identification Plate Position	none

➔Product Dimensions

Min. Tensile Strength	50lbs / 225N
Length (L)	7.9" / 200mm
Attach to Diameter	0.26 " - 0.30 "
Width (W) (imperial)	.18"
Width (W)	4.6mm
Min. Ø Bundle	1.8" / 6.5mm
Max. Ø Bundle	1.8" / 45mm
Attach to Ø	6.5 - 7.5 mm

➔Material and Specifications

Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) / Polyamide 6.6 UV-stabilized (PA66UV)
Cable Tie	Polyamide 6.6 UV-stabilized (PA66UV)
Flammability	UL94 V2
Material Specification	RoHS
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C) / -40 °F to +221 °F (-40 °C to +105 °C)

➔Logistic and Packaging

Packaging Type	bag
----------------	-----

Pkg. Qty.	500
EAN code	4031026404547

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)