

ACE-663A

60W AC Input AT Power Supply



Feature

1. With ITE safety
2. Only 1.41 inch height
3. With power good LED
4. With output adjustable trimmer
5. High Efficiency 83%
6. Operation from -20°C to 70°C by convection
7. The terminal block with cover is optional


Safety



Specification

Input	Voltage :			90 ~ 264VAC Full Range
	Frequency :			47 ~ 63Hz
	Inrush Current :			30A Max for 115VAC 60A Max for 230VAC
Output	Voltage	Min. load	Max. load	Ripple & Noise
	+5V	0A	6A	50mV
	+12V	0A	2A	120mV
	Over-voltage protection :			latch off
	Short Circuit protection :			auto recovery
General Specification	Watt			60W
	PFC			-
	Hold-up time			14 ms Min.
	Efficiency			83% Min.
	MTBF			100,000 hours
	Temperature			Operation:-20 ~ 70°C Storage : -40 ~ 85°C
	Dimension			95 X 100 X 36 (mm) 3.74 X 3.93 X 1.41 (inch)
	Outline Connector			Optional CB-643EB-RS CB-643BP-RS

Dimension



CB-643BP-RS



CB-643EB-RS

Ordering Information

Part No.	Description
ACE-663A-RS	60W AC Input AT Power Supply, RoHS

Optional

Part No.	Description
CB-643EB-RS	DC cable for ACE-663A/643A power to CPU card, W/4PIN 12V CPU / HDD / S-ATA Connector, 30cm
CB-643BP-RS	DC cable for ACE-663A/643A power to Backplane, W/20PIN ATX / HDD / S-ATA connector, 30cm



Headquarters

IEI Technology Corp.

TEL : +886-2-86916798 FAX : +886-2-66160028

sales@ieiworld.com www.ieiworld.com

No. 29, Zhongxing Rd., Sijhih City, Taipei County, 221, Taiwan

America-United States

IEI Technology USA Corp.

TEL : +1-562-690-6677 FAX : +1-562-690-0898

sales@usa.ieiworld.com www.usa.ieiworld.com

515 N. Puente St., Brea, CA 92821

China

Armorlink SH Corp.

TEL : +86-021-54429000 FAX : +86-021-54429100

sales@ieiworld.com.cn www.ieiworld.com.cn

No.515, Shenfu Road, Minhang District, Shanghai, China