

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [88768-5300](#)
Status: **Active**
Overview: [DMS-59®](#)
Description: 1.27mm Pitch DMS-59®-to-Two DVI-I Adapters Cable Assembly, 0.20m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-88768-5300 \(PDF\)](#)

General

Product Family Cable Assemblies
Series [88759](#)
Connector to Connector DMS-59™-to-DVI-I
Overview [DMS-59®](#)
Product Name DMS59®
UPC 756054581629

Physical

Cable Length 0.20m
Circuits (Loaded) 59
Color - Resin Black
Gender Male-Female
Lock to Mating Part Yes
Material - Metal Aluminum, Phosphor Bronze, Steel
Material - Plating Mating Gold, N/A
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 155.600/g
Packaging Type Bag
Pitch - Mating Interface 1.27mm
Plating min - Mating 0.051µm, 0.762µm, 1.905µm
Plating min - Termination 2.540µm, 3.810µm
Single Ended No
Termination Interface: Style N/A, Through Hole
Wire Insulation Diameter N/A
Wire Size AWG 32
Wire/Cable Type Round


Electrical

Current - Maximum per Contact 1A
Impedance 100#
Shielded Yes
Voltage - Maximum 30V AC

Material Info

Reference - Drawing Numbers

Product Specification PS-88768-5300
Sales Drawing SD-88744-097



EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[88759Series](#)