



A



B



C



D

NOTES: UNLESS OTHERWISE SPECIFIED;

- 1 CONNECTOR MATERIALS:
HOUSING: GLASS FILLED THERMOPLASTIC,
UL94-V0 COMPLIANT
KEEPER: GLASS FILLED THERMOPLASTIC,
UL94-V0 COMPLIANT
TERMINAL: PHOSPHOR BRONZE ALLOY
- 2 PACKED IN TUBES.
- 3 FEATURE MAY OR MAY NOT BE PRESENT DEPENDING UPON THE MOLD TOOL USED TO PRODUCE PRODUCT.
- 4 PRODUCT SPECIFICATION: GS-12-177.
- 5 APPLICATION SPECIFICATION: GS-20-015.
UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 6 THE PRODUCTS WHERE THE PART NUMBER ENDS IN 'LF' MEET THE EUROPEAN
- 7 ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- 8 LOCATION PEGS ARE EXISTED ONLY IN ONE MODULE

A

B

C

D



Copyright FCI.

rev	ecn no	dr	date
M	V04-1123	TAB	02/03/05
N	V05-0437	VS	07/14/05
P	V05-1026	JRV	11/7/05
R	DG06-0378	KL	09/01/06
S	DG06-0434	Cenh	10/23/06
T	DG08-0173	TER	7/11/08
U	N10-0382	Cenh	11/13/10

www.fciconnect.com			surface ☒	tolerance std	projection	MM	
			ANGULAR	LINEAR	size	A4	
Dr V. SEBASTIAN			0°	±2°	0.X	± 0.50	Scale 4:1
Eng J. VOLSTROF			0°	±2°	0.XX	± 0.13	
Chr J. VOLSTROF			0°	±2°	0.XXX	± -	ECN N10-0382
Appr J. VOLSTROF			Product family		METRAL	Spec ref	
FCI			title			dwg no	Rev.
			T SERIES R/A RECEPTACLE ASSY, 4 ROW, STB			SE96846	U
			catalog no			CUSTOMER	sheet 1 of 4

1

2

3

4

A

B

C


D

A

B

C

D



www.fciconnect.com			surface 		tolerance std		projection 			
			TOLERANCES UNLESS		OTHERWISE SPECIFIED					
Dr	V. SEBASTIAN	07/14/05	ANGULAR	LINEAR	0.X	± 0.50	size	A4	Scale	
Eng	J. VOLSTROF	07/14/05			0.XX	± 0.13			4:1	
Chr	J. VOLSTROF	07/14/05			0.XXX	± -	ECN		N10-0382	
Appr	J. VOLSTROF	07/14/05	Product family			METRAL	Spec ref			
	title T SERIES R/A RECEPTACLE ASSY, 4 ROW, STB					dwg no	SE96846		Rev U	
					catalog no		CUSTOMER		sheet 2 of 4	

REV F - 2006-04-17

1

2


3PDM: Rev:U

STATUS:Released

4Printed: Dec 01, 2010



Copyright FCI.



	PCB THICKNESS	DIM D	RETENTION FEATURES
HMI F 4_ T A P 400 H__LF	1.60	2.90 ±0.30	PRESS-FIT PEGS
HMI F 4_ T B P 400 H__LF	2.40	3.60 ±0.30	

www.fciconnect.com			surface ☒		tolerance std		projection 		MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	V. SEBASTIAN	07/14/05	ANGULAR		LINEAR	0.X	± 0.50	size	A4	Scale 4:1
Eng	J. VOLSTROF	07/14/05				0.XX	± 0.13			
Chr	J. VOLSTROF	07/14/05	0°	±2°		0.XXX	± -	ECN		N10-0382
Appr	J. VOLSTROF	07/14/05	Product family			METRAL		Spec ref		
		T SERIES R/A RECEPTACLE ASSY, 4 ROW, STB					dwg no		SE96846	Rev.
										U
		catalog no			CUSTOMER			sheet 4 of 4		