


# SR45A 450W SOLDERING IRON




## DATA SHEET

769-3113



### SPECIFICATIONS SR45A (ANGLED) 450WATT SOLDERING IRON

NOMINAL POWER (W)	450
STANDARD VOLTAGE	230
NOMINAL TIP TEMP (°C)	480
FITTED BIT (D.F.)	1 1/4" (32mm)
CABLE LENGTH (m)	2.0
CABLE TYPE	Rubber with British plug
HANDLE MATERIAL	Wood
COUNTRY OF ORIGIN	U.K.
WEIGHT gms. (approx.)	1600
DIMENSIONS (approx.)	A: (bit) 55mm. B: 310mm. C: 95mm. D: 400mm.



### TYPICAL APPLICATIONS:

Heavy duty tasks. Features large bit with rapid heat replacement. Extensively used for heavy maintenance work including electronic motors with high temperature alloys, large metal boxes and for joining busbars.