


NOTES: UNLESS OTHERWISE SPECIFIED


1. CONSTRUCTION:
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
AVAILABLE IN TEN COLORS.
CONTACT BLADE: BERYLLIUM COPPER, GOLD PLATED
PER MIL-G-45204 B TYPE 1
0.00001" [0.000254] THK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.

2. PERFORMANCE
MAXIMUM CURRENT: 1.0 AMPS
MAXIMUM VOLTAGE: 600 W.V.D.C.
MAXIMUM TEMPERATURE: 200°F (93°C)

3. FEATURES:
HOOK FITS COMPONENTS UP TO Ø0.025" [0.64].
PIN PERMITS CONNECTION TO 0.025" [0.64] SQ.
OR Ø0.030" [0.76] SOCKETS.



ACTUAL SIZE



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.		DESCRIPTION	
		± .XX ±	±	APPROVALS	DATE	E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A. PICO HOOK WITH 0.25 [6.35] POST GOLD PLATED	
		± .XXX ±		DRAWN	6/09		
				APPROVED BY			
		MATERIAL SEE NOTE.				SIZE	CODE IDENT NO. DRAWING NO.
		FINISH SEE NOTE.				A	08505 P25COLOR
		NEXT ASSY USED ON				SCALE	2:1
		APPLICATION DO NOT SCALE DRAWING				SHEET	1 OF 1