

You are here: [Products](#) » [Heatsinks f.cool](#) » [Profile heatsinks and fluid coolers](#) » [Standard extruded heatsinks](#) » [SK 02 ...](#) » **SK 02**



- ▼ **Heatsinks f.cool**
- ▼ Profile heatsinks and fluid coolers
 - **Standard extruded heatsinks**
 - Extruded heatsinks for lock-in retaining spring
 - Extruded heatsinks for PCB mounting
 - Extruded heatsinks for DC/DC converter
 - Retaining springs for transistors
 - U-Extruded heatsinks
 - Die-cast heatsinks
 - Fin coolers
 - Fluid coolers
 - Aluminium flat-, quadrangular-, angled-, U- and T-profiles
- ▶ Heatsinks and active heatsinks for processors
- ▶ Board Level heatsinks
- ▶ Cooling aggregates
- ▶ Accessories for electronic components
- ▶ **Cases f.case**
- ▶ **Connectors f.con**

Standard extruded heatsinks


SK 02 ...

SK 02 37,5 SA

115 x 63 mm, with guide away for cover plates or blanks, mounting parts IS 1, IS 2, IS 3

[Data sheet](#)

[add to request](#)



- [Features](#)
- [Technical Drawing](#)
- [Service](#)
- [Accessories / related products](#)

thermal resistance R_{th}	1.9 - 1 K/W
drilling pattern	TO 3 CB
surface	black anodised
height	63 mm
width B	115 mm
length	37.5 mm
plate thickness	4 mm