




A



B



C

Shell size	Number of contacts	A $^{+0.76}_0$	B $^{+0.25}_0$	C ± 0.12	F $^{+0.13}_{-0.03}$	G	K _{maxi}	L $^{+0.22}_0$	Part number
E	09	30.43	16.79	24.99	4.36	5.90 $^{+0.15}_0$	1.50	0.80	86553113TLF
A	15	38.76	25.12	33.32	4.36	5.90 $^{+0.15}_0$	1.50	0.80	86553114TLF
B	25	52.65	38.84	47.04	4.36	5.70 $^{+0.25}_0$	1.50	0.80	86553115TLF
C	37	68.94	55.30	63.50	4.36	5.70 $^{+0.25}_0$	1.50	1.00	86553116TLF

NOTE: RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Plating: Sn pure bright over Copper.
- Packaging spec: see GS-14-920.

European Views

www.fciconnect.com				surface ISO 1302	tolerance std ISO 406 ISO 1101	projection
TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	GOISNARD	28/06/17	ANGULAR		0.X	± 0.1
Eng	PESSON	2006/01/12	LINEAR	0.XX	± 0.1	
Chr	LEGARE	2006/01/12		0.XXX	± 0.1	ECN LS09-0006
Appr	LEGARE	2006/01/12	Product family	D-SUB	Spec ref	-
rev	ecn no	dr	date		size	Scale
A	LS05-0123	LGO	2006/01/12		A3	3
B	LS06-0095	LGO	2006/06/24			
C	LS07-0135	MPE	2007/05/11			
D	LS09/0006	PCR	2009/01/08			
-	-	-	-			
-	-	-	-			
-	-	-	-			
FCI				METAL CAPS D SUB ACCESSORIES		
catalog no				drg no		Rev. D
-				C01-8655-1656		
-				CUSTOMER		sheet 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

89648-002LF