

INTERCONNECTS

SERIES 714...01X • .100" GRID ULTRA LOW PROFILE CARRIERS • SINGLE AND DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3





FIG. 4

- Ultra low profile receptacles sit .018" above the board
- Series 714 use MM #0552-1 and MM #0552-2 pin receptacles. See page 158 for details
- Hi-Rel, 3-finger BeCu #11 contact is rated at 3 amps. See page 251 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Single Row (.039" min. mounting hole)					
	714-XX-1 -31-012000 Specify number of pins 01-64					
FIG. 2	Single Row (.039" min. mounting hole)					
	714-XX-1 -31-018000 Specify number of pins 01-64					
FIG. 3	Double Row (.039" min. mounting hole)					
	714-XX-2 -31-012000 Specify number of pins 04-64					
FIG. 4	Double Row (.039" min. mounting hole)					
	714-XX-2 -31-018000 Specify number of pins 04-64					
RoHS - 2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264						
SPECIFY PLATING CODE XX=		91	93		41	43
Sleeve (Pin)		200 μ"Sn/Pb	200 μ"Sn/Pb		200 μ"Sn	200 μ"Sn
Contact (Clip)		10 μ"Au	30 μ"Au		10 μ"Au	30 μ"Au