





SECTION TERMINAISON CONTACT



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



rev	econ no	dr	date
C	-	JAR	2002/09/10
D	LS05-001	MPE	2005/03/09
E	LS05-0056	MPE	2005/06/27
F	LS06-0097	LGO	2006/07/29
G	109-0268	NG	2009-11-24
-	-	-	-
-	-	-	-

www.fciconnect.com		surface ISO 1302		tolerance std ISO 406 ISO 1101	projection 	mm 
		TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	LELEON	1992-09-14	ANGULAR		size	Scale
Eng	PESSON	1992-09-14	LINEAR	0.X	A3	2
Chr	NIRMAL GEORGE	2009-11-24	0.XX	0.XXX	ECN	109-0268
Appr	SUDHIR VARMA	2009-11-24	Product family	D-SUB	Spec ref -	
MALE CONNECTOR DELTA D ST			Dwg no		Rev.	
straight,solder type for			C01-8646-0098		G	
catalog no			-		CUSTOMER sheet 1 of 1	

	A $\pm$ 0.38	B $\pm$ 0.12	C $\pm$ 0.10	D $\pm$ 0.25	E $\pm$ 0.07	PART NUMBER
SHELL						
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PV00
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PV00
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PV00
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PV00

Plating:	4	-->	flash	AU
Plating:	6	-->	0.76	AL

LEAD FREE PART NUMBER						
SHELL	A $\pm$ 0.38	B $\pm$ 0.12	C $\pm$ 0.10	D $\pm$ 0.25	E $\pm$ 0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PV00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PV00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PV00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PV00LF

Plating: 4 --> flash AU
Plating: 6 --> 0.76» AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com

surface	tolerance std
ISO 1302	ISO 406 ISO 1107

projection	mm
	40
	60
	40

mm

○

Δ



○

w

A

MALE CONNECTOR DELTA D STRAIGHT, solder type for

C01-8646-0098

Rev