



2.5mm x 7mm Rectangular LED CBI® Circuit Board Indicator

Dialight

561-4x01-xxx



PART NO.

561-4101-xxx
561-4201-xxx
561-4301-xxx

COLOR

Red
Green
Yellow

Benefits

- Available with a variety of LEDs
- Housing material meets UL94 V-0
- Rectangular shaped LED
- Black housing enhances contrast
- High reliability - life measured in years
- Vibration and shock resistant
- Standoffs on housing facilitate PC board cleaning

LED Data

- For absolute maximum ratings and other electrical/optical data refer to LED data sheet.

Dimensions in mm [inches]

PART NUMBER ORDERING CODE									
Series	LED Type			Overall Height					
5	6	1	-	4	x	0	1	-	x x x
								055 = 14.0 [0.550]	
								081 = 20.6 [0.810]	

Typical Operating Characteristics (T_A=25°C)

See LED data sheet for additional information

Part Number	Color	Peak Wavelength nm	I _v mcd	V _F Volts	Test Current (mA)	Viewing Angle 2θ _{1/2}	LED Data sheet	Page #
561-4101-xxx	Red	635	5	1.9	20	100°	521-9264	5-17
561-4201-xxx	Green	565	2.5	2.3	20	100°	521-9266	5-17
561-4301-xxx	Yellow	583	5	2.1	20	100°	521-9265	5-17