





REV.	DATE	DESCRIPTION
NC	5/25/00	INITIAL RELEASE
A	12/29/00	UPDATE PLATING TO SILVER
B	09/10/06	REVISE BODY DESIGN , PLATING TO NEXCOTE, UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S.



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8					DRAWN	G.R.S.	09/10/06						
7					CHECKED								
6									PART DESCRIPTION				
5									7/16 PANEL JACK (FOR .250 SEMI-RIGID CABLE)				
4									PART NO.				
3	CONTACT PIN	BER. COPPER	SILVER		1					272101			
2	INSULATOR	TEFLON	NATURAL		1					DWG. NO.			
1	BODY	BRASS	NEXCOTE	1					272101.DWG				
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE				REV. B		SIZE A	SCALE NA	
					C:/272/272101.DWG								