


SPECIFICATION

1. Rated Voltage12V
2. Operating Voltage6~18V
3. Max. Rated Current40mA
4. Coil Resistance $115 \pm 12 \Omega$
5. Coil Impedance.....200 Ω
6. Min. Sound Pressure Level85dB/10cm
7. Resonant Frequency.....2048Hz
8. Case MaterialMPPO
9. Operating Temperature-30~+80℃
10. Store Temperature-40~+85℃
11. Weight7g



				KEPO KEPO ELECTRONIC CO., LTD. http://www.kepo.com.tw	
				Magnetic Buzzer	
				KPM-1612A	
No.	DESCRIPTION	APPROVED	DATE		
TOLERANCES UNLESS NOTED OTHERWISE: X .X ± .XX ± .XXX ± 90° FORMED ±2° ANGLES ±4°		APPROVALS	DATE		
		DRAWN		UNIT	DWG NO.
		CHECKED		mm	KP3.840.685
FIRST ANGLE PROJECTION		APPROVED	05.05.11	SCALE	NOT TO SCALE
				SHEET	VER 1.2