


		REVISIONS				
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVE
			D	REL WAS 5216 - 1105-93	1-6-81	
01	✓		D1	REV PER ECN 4296	4-28-82	MB
02	✓		02	REV ECN 1895	4-11-82	SB
✓	✓		A	REV LOC & DIST AD-4171	11-28-89	BF
✓			B	OBS-2,30 ECN 0915-93	8-93	RAC
✓			C	REV PER 0010-1105-93	4-94	EA/JH
✓	✓		D	REV PER 0010-0670-94	12-94	EB/JH
✓			E	REV PER 0010-1070-95	2-96	EB/TE



COVER PART NO.	COVER PART NO.	HOUSING ASSEMBLY PART NO.	NO. OF POSITIONS	KIT PART NO.
3-102541-4	3-102536-4	3-102398-4	72	3-102704-2-4
3-3	3-3	3-3	70	3-2
3-2	3-2	3-2	68	3-2
3-1	3-1	3-1	66	3-2
3-0	3-0	3-0	64	3-2
2-9	2-9	2-9	62	2-2
2-8	2-8	2-8	60	2-2
2-7	2-7	2-7	58	2-2
2-6	2-6	2-6	56	2-2
2-5	2-5	2-5	54	2-2
2-4	2-4	2-4	52	2-2
2-3	2-3	2-3	50	2-2
2-2	2-2	2-2	48	2-2
2-1	2-1	2-1	46	2-2
2-0	2-0	2-0	44	2-2
1-9	1-9	1-9	42	1-2
1-8	1-8	1-8	40	1-9
1-7	1-7	1-7	38	1-2
1-6	1-6	1-6	36	1-2
1-5	1-5	1-5	34	1-2
1-4	1-4	1-4	32	1-2
1-3	1-3	1-3	30	1-2
1-2	1-2	1-2	28	1-2
1-1	1-1	1-1	26	1-2
1-0	1-0	1-0	24	1-7
-9	-9	-9	22	6
-8	-8	-8	20	8
-7	-7	-7	18	2
-6	-6	-6	16	5
-5	-5	-5	14	2
-4	-4	-4	12	2
-3	-3	-3	10	4
-2	-2	-2	8	2
102541-1	102536-1	102398-1	6	3 102704-

		PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± <u>—</u> ANGLES ± <u>—</u>		CONTRACT NO DR <u>J. Marat</u> <u>11/13/79</u> CRK <u>J. Marat</u> <u>1-7-81</u> APPD <u>111 Yingt</u> <u>1-15-81</u> APPD <u>111 Yingt</u> <u>1-15-81</u>	
MATERIAL <u>—</u>		NAME KIT-CONNECTOR, LOW PROFILE NO POLARIZATION .100 CENTERS. MASS TERMINATION AMPMODU DOUBLE ROW. #22-#26 AWG WIRE SIZE	
FINISH <u>—</u>		SIZE C	CODE IDENT NO 00779
		DRAWING NO 102704	SCALE N.T.S.
		SHEET	