



ISO 529
Tap tolerance: Class 1,2 and 3
Chamfer thread number: 1, 2 and3
Cutting rake: 7°
Flute geometry: Straight flutes
Surface treatment: Bright
Range: 1/6 - 3/4in

380252

Size x pitch	Cutter diameter (mm)	Overall length (mm)	Flute length (mm)	Shank diameter (mm)	A (mm)	Order code	Price each
1/16 x 27	7.94	65	17	8.1	6.0	No Order Code	
1/8 x 27	10.290	70	19	11.1	8.30	138-9496	
1/4 x 18	13.720	75	27	14.3	10.70	138-9497	
3/8 x 18	17.150	80	27	17.8	13.50	148-5358	
1/2 x 14	21.340	100	35	17.5	13.10	148-5359	
3/4 x 14	26.670	105	35	23.0	17.20	148-5360	