



Einzeladern, Schaltdrähte, Schaltlitzen

LifY PVC-Schaltlitze, höchstflexibel

Verwendung

Höchstflexible Schaltlitzen eignen sich hervorragend für bewegliche Verbindungen in der Verdrahtungstechnik, sowie als Messleitungen.

Aufbau

Leiter: feinstdrähtige Cu-Litze, blk.
Isolation: PVC gem. VDE 0207

Technische Eigenschaften

Isolationswiderstand: min. 200 MOhm x km bei +20 °C

	0,14 qmm	0,25 – 2,5 qmm	4,0 – 70,0 qmm
Betriebsspannung:	500 V	900 V	1500 V
Prüfspannung:	1200 V	2500 V	3000 V

Temperaturbereich: ruhend: –30 °C bis +70 °C; bewegt: –5 °C bis +70 °C
Biegeradius: ruhend: min. 8 x A-Ø; bewegt: min. 10 x A-Ø

Aufmachung

0,14 – 1,0 qmm: Spulen à 100 m
ab 1,5 qmm: Ringe à 100 m
(Sonderaufmachungen möglich)

Farben

Ab Lager: blau, braun, gelb, grün, grün-gelb, grau, rot, schwarz, weiß
(weitere Farben sowie 2-farbige Ausführungen sind auf Anfrage lieferbar)



Zusatzinformationen: Bitte berücksichtigen Sie bei Ihren Vergleichen den z.T. unterschiedlichen Leiteraufbau der einzelnen Hersteller.
Add-on information: At your comparisons, please consider the partly different structure of conductors of the various manufacturer.

Bestell-Nr. Order-No.	Abmessung dimension	Leiteraufbau structure of cond.	A-Ø O.D.	Gewicht weight	Cu.-Gewicht co.-weight
	(qmm)	(mm)	(ca. mm)	(kg/km)	(kg/km)
1601014	0,14	72 x 0,05	1,1	3,0	1,4
1601025	0,25	128 x 0,05	1,4	4,0	2,5
1601050	0,50	256 x 0,05	2,0	8,8	5,0
1601075	0,75	384 x 0,05	2,2	12,0	7,5
1601100	1,00	512 x 0,05	2,5	16,0	10,0
1601150	1,50	392 x 0,07	3,4	25,0	15,0
1601250	2,50	651 x 0,07	3,8	37,2	25,0
1601400	4,00	512 x 0,10	4,9	51,0	40,0
1601600	6,00	768 x 0,10	6,0	71,0	60,0
1611000	10,00	1280 x 0,10	7,5	130,0	100,0
1611600	16,00	2048 x 0,10	9,0	187,0	160,0
1612500	25,00	1400 x 0,15	10,5	294,0	250,0
1613500	35,00	1960 x 0,15	12,5	380,0	350,0
1615000	50,00	2600 x 0,15	13,8	521,0	500,0
1617000	70,00	3920 x 0,15	15,5	740,0	700,0

Single cores, Hook-up wires (stranded, solid)

LifY Hook-up wire stranded, extremely flexible, PVC

Application

General wiring technology in the electronics field, as well as measuring line, where high flexibility is demanded.

Construction

Conductor: finest bare stranded copper wire
Insulation: PVC acc. to VDE 0207

Technical characteristics

Insulation resistance: min. 200 MOhm x km at +20 °C

	0,14 qmm	0,25 – 2,5 qmm	4,0 – 70,0 qmm
Operating voltage:	500 V	900 V	1500 V
Testing voltage:	1200 V	2500 V	3000 V

Temperature range: static: –30 °C to +70 °C; dynamic: –5 °C to +70 °C
Bending radius: static: 8 x O.D.; dynamic: 10 x O.D.

Packaging

0,14 – 1,0 qmm: spools at 100 m
up from 1,5 qmm: rings at 100 m
(Special packaging available)

Colours

Available from stock: blue, brown, yellow, green, yellow-green, grey, red, black, white
(further colours as well as 2-coloured versions are available on request)

Umrechnungstabelle AWG – metrisch		conversation table AWG – metric		
AWG-Nr. AWG-No.	Draht Ø (mm) solid wire (mm)	Querschnitt (qmm) cross-section (qmm)	Litzenaufbau AWG structure of stranding AWG	Litzenaufbau DIN structure of stranding DIN
34	0,160	0,020	7 x 0,065	
32	0,202	0,035	7 x 0,080	
30	0,254	0,057	7 x 0,102	14 x 0,07
28	0,321	0,088	7 x 0,127	10 x 0,10
26	0,405	0,140	7 x 0,160	18 x 0,10
24	0,511	0,226	7 x 0,203 (19 x 0,127)	14 x 0,15
22	0,644	0,344	7 x 0,254 (19 x 0,160)	7 x 0,25
20	0,812	0,562	7 x 0,320 (19 x 0,203)	7 x 0,32
18	1,024	0,896	7 x 0,404 (19 x 0,254)	19 x 0,26
16	1,290	1,429	7 x 0,510 (19 x 0,320)	30 x 0,25
14	1,628	2,238	7 x 0,643 (19 x 0,361)	
12	2,050	3,630	7 x 0,813 (19 x 0,455)	

Litzenaufbau gem. VDE 0295		structure of stranding acc. to VDE 0295					
qmm	mehrdrähtig, Klasse 2, Spalte 1	vieldräftig Spalte 2	feinstdräftig Klasse 5, Spalte 3	feinstdräftig Klasse 6, Spalte 4	feinstdräftig Spalte 5	feinstdräftig Spalte 6	feinstdräftig Spalte 7
qmm	class 2, column 1	column 2	class 5, column 3	class 6, column 4	column 5	column 6	column 7
0,14				18 x 0,10	18 x 0,10	36 x 0,07	72 x 0,05
0,25			14 x 0,15	32 x 0,10	32 x 0,10	65 x 0,07	128 x 0,05
0,34		7 x 0,25	19 x 0,15	42 x 0,10	42 x 0,10	88 x 0,07	174 x 0,05
0,38		7 x 0,27	12 x 0,20	21 x 0,15	48 x 0,10	100 x 0,07	194 x 0,05
0,5	7 x 0,30	7 x 0,30	16 x 0,20	28 x 0,15	64 x 0,10	131 x 0,07	256 x 0,05
0,75	7 x 0,37	7 x 0,37	24 x 0,20	42 x 0,15	96 x 0,10	195 x 0,07	384 x 0,05
1,0	7 x 0,43	7 x 0,43	32 x 0,20	56 x 0,15	128 x 0,10	260 x 0,07	512 x 0,05
1,5	7 x 0,52	70 x 0,52	30 x 0,25	84 x 0,15	192 x 0,10	392 x 0,07	768 x 0,05
2,5	7 x 0,67	19 x 0,41	50 x 0,25	140 x 0,15	320 x 0,10	651 x 0,07	1280 x 0,05
4,0	7 x 0,85	19 x 0,52	56 x 0,30	224 x 0,15	512 x 0,10	1040 x 0,07	
6,0	7 x 1,05	19 x 0,64	84 x 0,30	192 x 0,20	768 x 0,10	1560 x 0,07	
10,0	7 x 1,35	49 x 0,51	80 x 0,40	320 x 0,20	1280 x 0,10	2600 x 0,07	
16,0	7 x 1,70	49 x 0,65	128 x 0,40	512 x 0,20	2048 x 0,10		
25,0	7 x 2,13	84 x 0,62	200 x 0,40	800 x 0,20	3200 x 0,10		
35,0	7 x 2,52	133 x 0,58	280 x 0,40	1120 x 0,20			
50,0	19 x 1,83	133 x 0,69	400 x 0,40	705 x 0,30			

Die Anzahl der Drähte Spalte 3–7 ist unverbindlich. Die VDE 0295 legt lediglich den max. D des Einzeldrahtes und den maximalen dem Querschnitt zugeordneten Widerstand fest.
The number of wires in column 3–7 is noncommittal. VDE 0295 lay down that max. diameter of the single wire and the maximum of cross section for the assigned resistance.

Leiterwiderstände gem. VDE 0295 | Conductor restistance in acc. with VDE 0295
Leiterwiderstand bei 20 °C für 1000 m in Ohm | Conductor restistance at 20 °C for 1000 m in Ohm

qmm qmm	Cu-Leiter, verzinkt Tinned copper wire Klasse 1+2 Class 1+2	Klasse 5+6 Class 5+6	Cu-Leiter, blank Bare copper wire Klasse 1+2 Class 1+2	Klasse 5+6 Class 5+6
0,08		250,00		243,00
0,14		142,00		138,00
0,25		82,00		79,00
0,34		59,00		57,00
0,5	36,70	40,10	36,00	39,00
0,75	24,80	26,70	24,50	26,00
1,0	18,20	20,00	18,10	19,50
1,5	12,20	13,70	12,10	13,30
2,5	7,56	8,21	7,41	7,98
4,0	4,70	5,09	4,61	4,95
6,0	3,11	3,39	3,08	3,30
10,0	1,84	1,95	1,83	1,91
16,0	1,16	1,24	1,15	1,21
25,0	0,734	0,795	0,727	0,78
35,0	0,529	0,565	0,524	0,554
50,0	0,391	0,393	0,387	0,386

Leiterwiderstände für Cu-Litzen-Leiter (Auszug aus der VDE 0295). Maßgebend für den Aufbau der Leiter ist der max. Einzeldrahtdurchmesser und der max. Leiterwiderstand.
Conductor reststances for stranded copper wires (extract from VDE 0295). Relevant for the wire construction is the max. diameter of the single wire and the max. conductor restistance.

Farbcode nach DIN 47100/11.79, Adrige Verseilung (ohne Farbwiederholung
Colourcode acc. to DIN 47100/11.79, Twisted cores (without colour repetition)

Ader-Nr. Core-No.	Farbe der Ader Colour of core	Ader-Nr. Core-No.	Farbe der Ader Colour of core
1	ws / wh	32	ge-bl / ye-bu
2	bn / bn	33	gn-rt / gn-rd
3	gn / gn	34	ge-rt / ye-rd
4	ge / ye	35	gn-sw / gn-bk
5	gr / gy	36	ge-sw / ye-bk
6	rs / pk	37	gr-bl / gy-bu
7	bl / bu	38	rs-bl / pk-bu
8	rt / rd	39	gr-rt / gy-rd
9	sw / bk	40	rs-rt / pk-rd
10	vio / vt	41	gr-sw / gy-bk
11	gr-rs / gy-pk	42	rs-sw / pk-bk
12	rt-bl / rd-bu	43	bl-sw / bu-bk
13	ws-gn / wh-gn	44	rt-sw / rd-bk
14	bn-gn / bn-gn	45	ws-bn-sw / wh-bn-bk
15	ws-ge / wh-ye	46	ge-gn-sw / ye-gn-bk
16	ge-bn / ye-bn	47	gr-rs-sw / gy-pk-bk
17	ws-gr / wh-gy	48	bl-rt-sw / bu-rd-bk
18	gr-bn / gy-bn	49	ws-bn-sw / wh-gn-bk
19	ws-rs / wh-pk	50	gn-bn-sw / gn-bn-bk
20	rs-bn / pk-bn	51	ws-ge-sw / wh-ye-bk
21	ws-bl / wh-bu	52	ge-bn-sw / ye-bn-bk
22	bn-bl / bn-bu	53	ws-gr-sw / wh-gy-bk
23	ws-rt / wh-rd	54	gr-bn-sw / gy-bn-bk
24	bn-rt / bn-rd	55	ws-rs-sw / wh-pk-bk
25	ws-sw / wh-bk	56	rs-bn-sw / pk-bn-bk
26	bn-sw / bn-bk	57	ws-bl-sw / wh-bu-bk
27	gr-gn / gy-gn	58	bn-bl-sw / bn-bu-bk
28	ge-gr / ye-gy	59	ws-rt-sw / wh-rd-bk
29	rs-gn / pk-gn	60	bn-rt-sw / bn-rd-bk
30	ge-rs / ye-pk	61	sw-ws / bk-wh
31	gn-bl / gn-bu		

Bei adriger Verseilung mit Farbwiederholung wiederholt sich der Farbcode ab der 45. Ader, beginnend mit weiß. Grundsätzlich ist die erste Farbe die Grundfarbe der Ader. Bei mehrfarbigen Adern setzt sich die Kennzeichnung aus der Grundfarbe und einer bzw. mehreren Ringmarkierungen zusammen. Die Ringmarkierungen sind in kurzen Abständen in Form von abriebfesten Farbringen aufgebracht. Die Zählweise der Adern beginnt von außen nach innen, durch alle Lagen fortlaufend gleichsinnig.

In case of core twisting with colour repetition, the colour code is repeating with white beginning from the 45th core. Generally the first colour is the base colour. Multico-
loured cores are marked with the base-colour and one respectively more ring-markings. The ring-markers are applied in short intervals in an abrasion-proof form. The
method of counting from the cores is beginning from outside to inside through all layers continuously in the same direction.

Farbcode nach DIN 47100/11.79, paarige Verseilung | Colourcode acc. to DIN 47100/11.79, twisted pairs

Paar-Nr. Pair-No.	Farben der Adern Colour of cores		Paar-Nr. Pair-No.	Farben der Adern Colour of cores	
	a-Ader a-Core	b-Ader b-Core		a-Ader a-Core	b-Ader b-Core
1, 23, 45	ws / wh	bn / bn	12, 34, 56	ws-rt / wh-rd	bn-rt / bn-rd
2, 24, 46	gn / gn	ge / ye	13, 35, 57	ws-sw / wh-bk	bn-sw / bn-bk
3, 25, 47	gr / gy	rs / pk	14, 36, 58	gr-gn / gy-gn	ge-gr / ye-gy
4, 26, 48	bl / bu	rt / rd	15, 37, 59	rs-gn / pk-gn	ge-rs / ye-pk
5, 27, 49	sw / bk	vio / vt	16, 38, 60	gn-bl / gn-bu	ge-bl / ye-bu
6, 28, 50	gr-rs / gy-pk	rt-bl / rd-bu	17, 39, 61	gn-rt / gn-rd	ge-rt / ye-rd
7, 29, 51	ws-gn / wh-gn	bn-gn / bn-gn	18, 40, 62	gn-sw / gn-bk	ge-sw / ye-vk
8, 30, 52	ws-ge / wh-ye	ge-bn / ye-bn	19, 41, 63	gr-bl / gr-bu	rs-bl / pk-bu
9, 31, 53	ws-gr / wh-gy	gr-bn / gy-bn	20, 42, 64	gr-rt / gy-rd	rs-rt / pk-rd
10, 32, 54	ws-rs / wh-pk	rs-bn / pk-bn	21, 43, 65	gr-sw / gy-bk	rs-sw / pk-bk
11, 33, 55	ws-bl / wh-bu	bn-bl / bn-bu	22, 44, 66	bl-sw / bu-bk	rt-sw / rd-bk

Grundsätzlich ist die erste Farbe die Grundfarbe der Ader. Bei mehrfarbigen Adern setzt sich die Kennzeichnung aus der Grundfarbe und einer bzw. mehreren Ringmarkierungen zusammen. Die Ringmarkierungen sind in kurzen Abständen in Form von abriebfesten Farbringen aufgebracht. Die Zählweise der Adern beginnt von außen nach innen, durch alle Lagen fortlaufend gleichsinnig.

Generally the first colour is the base colour. Multicoloured cores are marked with the base-colour and one respectively more ring-markings. The ring-markers are applied in short intervals in an abrasion-proof form. The method of counting from the cores is beginning from outside to inside through all layers continuously in the same direction.

Internationaler Farbcode (cULus) | International Colourcode (cULus)

Ader-Nr. Core-No.	Farbe der Ader Colour of core	Ader-Nr. Core-No.	Farbe der Ader Colour of core
1	sw / bk	31	gn-rt / gn-rd
2	bn / bn	32	gn-or / gn-og
3	rt / rd	33	gn-bl / gn-bu
4	or / og	34	gn-vio / gn-vt
5	ge / ye	35	gn-gr / gn-gy
6	gn / gn	36	gn-ws / gn-wh
7	bl / bu	37	ge-sw / ye-bk
8	vio / vt	38	ge-bn / ye-bn
9	gr / gy	39	ge-rt / ye-rd
10	ws / wh	40	ge-or / ye-og
11	ws-sw / wh-bk	41	ge-bl / ye-bu
12	ws-bn / wh-bn	42	ge-vio / ye-vt
13	ws-rt / wh-rd	43	ge-gr / ye-gy
14	ws-or / wh-og	44	ge-ws / ye-wh
15	ws-ge / wh-ye	45	gr-sw / gy-bk
16	ws-gn / wh-gn	46	gr-bn / gy-bn
17	ws-bl / wh-bu	47	gr-rt / gy-rd
18	ws-vio / wh-vt	48	gr-or / gy-og
19	ws-gr / wh-gy	49	gr-ge / gy-ye
20	bn-sw / bn-bk	50	gr-gn / gy-gn
21	bn-rt / bn-rd	51	gr-bl / gy-bu
22	bn-or / bn-og	52	gr-vio / gy-vt
23	bn-ge / bn-ye	53	gr-ws / gy-wh
24	bn-gn / bn-gn	54	or-sw / og-bk
25	bn-bl / bn-bu	55	or-bn / og-bn
26	bn-vio / bn-vt	56	or-rt / og-rd
27	bn-gr / bn-gy	57	or-ge / og-ye
28	bn-ws / bn-wh	58	or-gn / og-gn
29	gn-sw / gn-bk	59	or-bl / og-bu
30	gn-bn / gn-bn	60	or-vio / og-vt

kabeltronik Farbcode | kabeltronik colourcode

Paar-Nr. Pair-No.	Farbe der Ader Colour of core
1	ws, bn / wh, bn
2	ws, gn / wh, gn
3	ws, ge / wh, ye
4	ws, gr / wh, gy
5	ws, rs / wh, pk
6	ws, bl / wh, bu
7	ws, rt / wh, rd
8	ws, sw / wh, bk
9	ws, vio / wh, vt
10	ws, ws-bn / wh, wh-bn
11	ws, ws-gn / wh, wh-gn
12	ws, ws-ge / wh, wh-ye
13	ws, ws-gr / wh, wh-gy
14	ws, ws-rs / wh wh-pk
15	ws, ws-bl / wh, wh-bu
16	ws, ws-rt / wh, wh-rd

Ausnahme: bei 10-paarigen Leitungen hat das 10. Paar den Farbcode: weiß/orange.
Exception: in 10-pair lines the colour-code of the pair 10 is wh/og.

Paar-Nr. Pair-No.	Farbe der Ader Colour of core
17	ws, ws-sw / wh, wh-bk
18	ws, bn-gn / wh, bn-gn
19	ws, bn-ge / wh, bn-ye
20	ws, bn-gr / wh, bn-gy
21	ws, bn-rs / wh, bn-pk
22	ws, bn-bl / wh, bn-bu
23	ws, bn-rt / wh, bn-rd
24	ws, bn-sw / wh, bn-bk
25	ws, gn-gr / wh, gn-gy
26	ws, gn-rs / wh, gn-pk
27	ws, gn-bl / wh, gn-bu
28	ws, gn-rt / wh, gn-rd
29	ws, gn-sw / wh, gn-bk
30	ws, ge-gr / wh, ye-gy
31	ws, ge-rs / wh, ye-pk
32	ws, ge-bl / wh, ye-bu

kabeltronik Farbcode kf 2 | kabeltronik colourcode kf 2

Paar-Nr. Pair-No.	Farbe der Ader Colour of core
1	ws, bn / wh, bn
2	ws, gn / wh, gn
3	ws, ge / wh, ye
4	ws, gr / wh, gy
5	ws, rs / wh, pk
6	ws, bl / wh, bu
7	ws, rt / wh, rd
8	ws, sw / wh, bk
9	or, bn / og, bn
10	or, gn / og, gn
11	or, ge / og, ye
12	or, gr / og, gy

Paar-Nr. Pair-No.	Farbe der Ader Colour of core
13	or, rs / og, pk
14	or, bl / og, bu
15	or, rt / og, rd
16	or, sw / og, bk
17	vio, bn / vt, bn
18	vio, gn / vt, gn
19	vio, ge / vt, ye
20	vio, gr / vt, gy
21	vio, rs / vt, pk
22	vio, bl / vt, bu
23	vio, rt / vt, rd
24	vio, sw / vt, bk

Farbcode für Netzkabel VDE 0293 HD 308 | Colour code for Power lines VDE 0293 HD 308

Ausführung mit gn/ge (-J oder G) | Version with gn/ye (-J or G)

Aderzahl	Neu: DIN VDE 0293–308, fest und flexibel
Number of wires	New: DIN VDE 0293–308, fixed and flexible
3	gnye, bu, bn
4	gnye, bn, bk, gy
5	gnye, bu, bn, bk, gy
6+	gnye, Rest sw mit Ziffern / gnye, others bk numbered

Ausführung ohne gn/ge (–0 oder x) | Version without gn/ye (–0 or x)

Aderzahl	Neu: DIN VDE 0293–308, fest und flexibel
Number of wires	New: DIN VDE 0293–308, fixed and flexible
2	bu, bn
3	bn, bk, gy
4	bu, bn, bk, gy
5	bu, bn, bk, gy, bk
6+	bk mit Ziffern / bk numbered

Farbcodierung nach IEC 757 | Colour code acc. to IEC 757

bk	schwarz	black
bn	braun	brown
rd	rot	red
og	orange	orange
ye	gelb	yellow
gn	grün	green
bu	blau	blue
vt	violett	violet
gy	grau	grey
wh	weiß	white
pk	rosa	pink
gd	gold	gold
tq	türkis	turquoise
sr	silber	silver

Werden verschiedene Adern bezeichnet, so sind die Farbcodes jeweils durch ein (+) Zeichen zu verbinden.
Shall different cores will be designated, so the colour-codes are to combine each with a "+".