


Specification



Model Name : AC 1024

Input Voltage	115 / 230 Vac
Input Frequency	47 ~ 63Hz
Max. In-rush Current	Cold start , 60A for 115Vac , 100A for 230Vac
Input Current	15 A Max for 115Vac 7.5 A Max for 230Vac
Output Voltage	29.2Vdc $\pm$ 0.2V (Absorption Charge) 27.4 Vdc $\pm$ 0.2V (Float Charge)
Start Point of Floating	1.5A $\pm$ 0.2A
Max. Charging Current	10A
Ripple / Noise	500mVp-p
FAN Control	Fan on running (Bulk / Absorption Charge) Fan Turn off (Float Charge)
LED Indication	LED1 : RED LED $\rightarrow$ POWER ON LED2 : ORANGE LED $\rightarrow$ BULK CHARGING LED OFF $\rightarrow$ FLOAT CHARGE
Dimensions	8.2 inch (210mm) Length 7.32 inch (186 mm) Width 2.99 inch (76 mm) Height



Case Drawing

Body View



Ideal Power, Acorn House, Tree Beech Enterprise Park, Gunn, Barnstaple, Devon, England EX32 7NZ
 Web. www.idealpower.co.uk email. sales@idealpower.co.uk
 Tel. +44 (0) 845 2603400 Fax. +44 (0) 845 2603401

Front Panel



Rear Panel

