









Schnitt A-A / cross section A-A



Rohrniet / rivet :



Nietmutter mit Klemmteil clamping thread:



Ident-Nr. /	Part No. :	Refer to table on page 2
Polzahl /	No. of contacts :	Refer to table on page 2
Anschlußart /	Terminal Type :	Angled solder
Anschlußlänge /	Terminal Length :	-
Bauart /	Type :	3W3
Anforderungsstufe /	Class :	207=0.8µm (30 µin) Au CONTACT, TIN/LEAD TERMINAL
Aufdruck /	Logo :	ERNI
Zubehör /	Accessory :	Refer to table on page 2
Sonderausführung /	Special :	Refer to table on page 2

Leiterplattenlochbild 134100 /

Board hole pattern 134100

Information:		Tolerances		Scale	2:1
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation	
a		15.05.2001		TMC-P 3W3-LP07-3	
Index		Date		TMC-P 3W3-LP07-3	
		M:00022942.SZN		054981	
				TMCP	

Consider protection memo from DIN 54

ERNI


www.ERNI.com

Ordering Information

D-Sub Connector High Power Solder Right Angle Male

Number of Pins

3W3



Accessory Termination Side: Rivet nut M3

134464

Accessory Termination Side: Rivet nut #4-40

134465