

Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'F512D5-5F15Y'**

Your search criteria matched only one product, shown below

F512D5-5F15Y



- Pass all TIA/EIA-568-B.3 performance requirements
- FOCIS-5 compliant
- Insertion loss per mated pair: 0.50dB typical; 0.75dB max.
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode cable assembly
- Lifetime traceability of test data to a Q.C. number on each cable assembly
- * MTP is a registered trademark of US Conec Ltd.

▪ Part Number	F512D5-5F15Y
▪ RoHS Compliance Status	RoHS directive is not applicable
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS
▪ Part Description	Female MTP* to female MTP* 12-fiber interconnect cable assembly (one female MTP* connector on each end on ribbon interconnect cable) – 50/125µm.
▪ Product Type	MTP* 12 Fiber Interconnect Cable Assemblies
▪ Length (ft.)	15
▪ Length (m)	4.6
▪ Fiber Compatibility	50/125µm
▪ Fiber Cable Size	5mm x 2.5mm
▪ Fiber Cable Type	Jacketed
▪ Fiber Type	Multimode
▪ Cable Color	Orange
▪ Cable Type	Duplex
▪ CE Compliant	No
▪ Connector 1 Type	MTP* Connector
▪ Connector 2 Type	MTP* Connector
▪ End Configurations	MTP* to MTP*
▪ Fiber Count	12
▪ Flammability Rating	Plenum (OFNP)
▪ Pricing Description	MTP*-MTP* Interconnect Cable Assembly 15ft 50µm
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.