

89-piece metric tool set

CM.EL33

• Supplied loose.

ΔΔ : 4,7 kg.



Ref	Qty	Description
39.JE10T	10	Roll set of short combination wrenches 3.2 to 11 mm
113A.6C	1	Adjustable wrench
R.420P	19	"Radio" socket set 3.2 to 14 mm and accessories
A.65x150	4	Insulated screwdrivers for slotted heads 2.5x50 - 3.5x75 - 4x100 - 5.5x150 mm
AP.VE	2	Insulated screwdrivers for Phillips® heads no. 0 - 1
AD.VE	2	Insulated screwdrivers for Pozidriv® heads no. 0 - 1
AN4X35	1	Stubby screwdriver 4 mm
ANP1X35	1	Stubby screwdriver for Phillips® heads no. 1
AMR	1	Multiblade screwdriver 1.5 - 2 - 2.5 mm
HT.3	2	Tuning screwdrivers
AFU.1	1	Screw starter for slotted heads
AFUX.1	1	Screw starter for cross-heads
83SH.JP9	9	Sleeve set of spherical head hex keys 1.5 to 10 mm
181.18G	1	Lockable multigrip pliers
194.17VE	1	1,000 V insulated wire stripper
405.12MT	1	Precision diagonal cutters
406.MT	1	Diagonal cutters
431.MT	1	Short-nose pliers

Ref	Qty	Description
420.MT	1	Shaping pliers
403.MT	1	Precision angled half-round nose pliers
438	1	Straight-nose ring pliers
1230.30	1	Soldering iron 30 W
661626	1	Reel of solder wire
839A.0	1	Desoldering pump
1195	3	Wallet set of soldering accessories
1802A	2	Black and red mini wire-holders
1803A	2	Black and red probes
1804B	2	Black and red connection leads
841.4	1	Electricians scissors
840.1	1	Electricians knife with wire stripper
AS.6L140T2	6	Roll set of needle files
DELA.892.02	1	Locking tape measure 2 m
149.Y	1	Precision tweezers
827.2	1	Magnetic retriever
834.R1	1	Articulated mirror
835A	1	Spring hook
836	1	Pen light
1830.1	1	Extra-soft silk brush

Set CM.EL33 with case BV.21SX

2138.EL33

• Dimensions 530 x 390 x 180 mm.

ΔΔ : 8,9 kg.

