



FEATURES:

- Multi-purpose test clips allow four ways to connect to a device under test
 - U-shaped nose for blade shaped terminals
 - Notched jaw for gripping screw heads, bare wire or terminals
 - Serrated teeth for gripping threaded or wire wrapped terminals
 - Large piercing needle for penetrating larger gauge wires

MATERIALS:

Jaws: Non-rusting Nickel Copper Alloy.

Boot: Vinyl wire 20 AWG PVC

Cable: 2 conductor, 22 AWG, 7 x 30 tc, 4.6" outside diameter

Y Mold: PVC

Bantam: Miniature phone plug 3 conductor, sleeve no connection

RATINGS:

Operating Voltage: Hand-held 30 VAC/60 VDC

Hands free operation in a controlled voltage environment: 300 VRMS

Current: 5 Amperes

ORDERING INFORMATION: Model 6487-48-*

* =Color; 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue

Standard length is 48" (122cm).

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6487-48-4 6487-48-6