

Wiha Precision Slotted/Phillips Drivers



261 Phillips Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
261 02	000	40	1.6	2.0	.08	120	4.7	.02	10
261 00	00	40	1.6	2.0	.08	120	4.7	.02	10
261 01	00	75	3.0	2.0	.08	155	6.1	.02	10
261 05	0	50	2.0	3.0	.12	145	5.7	.02	10
261 08	0	75	3.0	3.0	.12	170	6.7	.03	10
261 07	0	100	3.9	3.0	.12	195	7.6	.05	10
261 09	0	150	5.9	3.0	.12	245	9.6	.06	10
261 10	1	60	2.4	4.0	.16	170	6.7	.05	10
261 13	1	80	3.1	4.0	.16	190	7.5	.05	10
261 14	1	100	3.9	4.0	.16	210	8.2	.06	10
261 15	1	150	5.9	4.0	.16	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



261 90 Set 7 Pcs. Slotted & Phillips

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.			
	mm	mm	lbs.
261 90	260 15	1.5	40
	260 22	2.0	50
	260 25	2.5	50
	260 32	3.0	60
			
	Size	mm	
	261 00	00	40
	261 05	0	50
	261 10	1	60



261 94 Set 4 Pcs. Phillips

Blade high alloy chrome-vanadium-molybdenum steel.
Hard chrome finished.

Item				
No.		Size	mm	lbs.
261 94	261 02	000	40	.18
	261 00	00	40	
	261 05	0	50	
	261 10	1	60	



261 99 Set 8 Pcs. Slotted/Phillips In Rugged Canvas Pouch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In storage pouch

Item								
No.		mm	mm		Size	mm		lbs.
261 99	260 10	1.0	40	261 02	000	40		.55
	260 20	2.0	40	261 00	00	40		
	260 30	3.0	50	261 05	0	50		
	260 40	4.0	60	261 10	1	60		



261 92 Set 5 Pcs. Slotted & Phillips

Blade high alloy chrome-vanadium-molybdenum steel.

Item				
No.		mm	mm	lbs.
261 92	260 28	2.5	150	.44
	260 34	3.0	150	
	260 42	4.0	150	
				
		Size	mm	
	261 09	0	150	
	261 15	1	150	