




- | | | | |
|-------|-------|----|--------------|
| 1.484 | 37.69 | 14 | 4-644892-4 |
| 1.384 | 35.15 | 13 | 4-644892-3 |
| 1.284 | 32.61 | 12 | 4-644892-2 |
| 1.184 | 30.07 | 11 | 4-644892-1 |
| 1.084 | 27.53 | 10 | 4-644892-0 |
| .984 | 24.99 | 9 | 3-644892-9 |
| .884 | 22.45 | 8 | 3-644892-8 |
| .784 | 19.91 | 7 | 3-644892-7 |
| .684 | 17.37 | 6 | 3-644892-6 |
| .584 | 14.83 | 5 | 3-644892-5 |
| .484 | 12.29 | 4 | 3-644892-4 |
| .384 | 9.75 | 3 | 3-644892-3 |
| .284 | 7.21 | 2 | 3-644892-2 |
| 1.484 | 37.69 | 14 | — 644892-4 — |
| 1.384 | 35.15 | 13 | — 644892-3 — |
| 1.284 | 32.61 | 12 | — 644892-2 — |
| 1.184 | 30.07 | 11 | — 644892-1 — |
| 1.084 | 27.53 | 10 | — 644892-0 — |
| .984 | 24.99 | 9 | — 644892-9 — |
| .884 | 22.45 | 8 | — 644892-8 — |
| .784 | 19.91 | 7 | — 644892-7 — |
| .684 | 17.37 | 6 | — 644892-6 — |
| .584 | 14.83 | 5 | — 644892-5 — |
| .484 | 12.29 | 4 | — 644892-4 — |
| .384 | 9.75 | 3 | — 644892-3 — |
| .284 | 7.21 | 2 | — 644892-2 — |

IN	MM	NO OF POSITIONS	PART NUMBER
L		HEADER ASSEMBLY	

.025	0.64	.100	2.54	.520	13.21
.010	0.25	.092	2.34	.410	10.4
.005	0.13	.063	1.60	.313	7.95
.001	0.03	.040	1.02	.280	7.11
.000350	0.00889	.035	0.89	.176	4.47
.000150	0.00381	.032	0.81	.140	3.56
.000	0.00	.030	0.76	.107	2.72
IN	MM	IN	MM	IN	MM

CONVERSION TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 24/JUNE/2005 CHK D. BOSSI 24/JUNE/2005		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P/LC ± . 1 P/LC ± . 2 P/LC ± . 3 P/LC ± .005 4 P/LC ± . ANGLES ± ± .		NAME CST-100 SHROUDED THREAD ASSEMBLY, FRICTION LOCK, STRAIGHT POST, TIN OR TIN LEAD PLATED	
MATERIAL 		FINISH 		SIZE A1 00779	
		WEIGHT —		DRAWING NO G644892	
CUSTOMER DRAWING				SCALE 10:1	
				SHEET 1 OF 1 REV G1	