



LAPP CY

LAPP CY cables are number coded control and connection cables with tinned copper braid screen. EMC compliant and space saving installation due to small cable diameters suitable for flexible use and fixed installation

LAPP CY cables are suitable for flexible use and fixed installation for medium mechanical use. They are for use in dry, damp and wet rooms. They may only be installed outdoors with UV protection and in observation of the temperature range generally resistant against acids, caustics solutions and certain oils. LAPP CY cables are used as supply and interconnecting cable for controlling machine tools, production lines, control equipment on conveyors, also for use in measuring regulating and computer units. Suitable for free movement without forced guidance and tensile stress

Typical Applications:

Measurement and control technology, office machines and systems for data processing

Technical Data :

Conductor	: Bare copper, fine wire strand in accordance to IEC 60 228 that is VDE 0295, class 5
Core insulation	: PVC compound T11 in accordance to VDE 0207
Identification	: In according to VDE 0293, black cores with white numbers with or without green / yellow ground conductor
Braid	: Tinned copper wire braid
Outer sheath	: Grey PVC compound TM2 in according to VDE 0207 Grey RAL 7001
Nominal voltage	: 300 / 500 V
Test voltage	: 3,000 V ac
Temperature range	: For flexible use -5 up to +70°C maximum conductor temperature Fixed installation -40 up to +80°C maximum conductor temperature
Minimum bending radius	: Fixed installation 12.5 × cable diameter
Flame retardant	: In according to IEC 60 332.1 resp. VDE 0472 part 804
EC directive	: This cable confirms to ECD 73 / 23 / EEC (low voltage directive)

Specification Table

Description	Number Cores × Cross Sectional Area (mm ²)	Outer Diameter (mm)	Weight Kg / Km	Part Number
Cable, CY, 3 Core, 0.5 mm, 100 m	Lapp CY 3G0.5	6.1	59	PPCY3C0.50 100M
Cable, CY, 4 Core, 0.5 mm, 100 m	Lapp CY 4G0.5	6.5	71	PPCY4C0.50 100M
Cable, CY, 5 Core, 0.5 mm, 100 m	Lapp CY 5G0.5	7	86	PPCY5C0.50 100M
Cable, CY, 7 Core, 0.5 mm, 100 m	Lapp CY 7G0.5	7.5	105	PPCY7C0.50 100M
Cable, CY, 3 Core, 0.75 mm, 100 m	Lapp CY 3G0.75	6.5	68.7	PPCY3C0.75 100M
Cable, CY, 4 Core, 0.75 mm, 100 m	Lapp CY 4G0.75	7	85.5	PPCY4C0.75 100M
Cable, CY, 5 Core, 0.75 mm, 100 m	Lapp CY 5G0.75	7.7	102.4	PPCY5C0.75 100M
Cable, CY, 7 Core, 0.75 mm, 100 m	Lapp CY 7G0.75	8.3	127.4	PPCY7C0.75 100M
Cable, CY, 3 Core, 1 mm, 100 m	Lapp CY 3G1	6.8	81.6	PPCY3C1.00 100M
Cable, CY, 4 Core, 1 mm, 100 m	Lapp CY 4G1	7.3	96.9	PPCY4C1.00 100M
Cable, CY, 5 Core, 1 mm, 100 m	Lapp CY 5G1	8.1	122	PPCY5C1.00 100M
Cable, CY, 7 Core, 1 mm, 100 m	Lapp CY 7G1	8.8	146.8	PPCY7C1.00 100M
Cable, CY, 3 Core, 1.5 mm, 100 m	Lapp CY 3G1.5	7.5	100.4	PPCY3C1.50 100M
Cable, CY, 4 Core, 1.5 mm, 100 m	Lapp CY 4G1.5	8.2	129.8	PPCY4C1.50 100M
Cable, CY, 5 Core, 1.5 mm, 100 m	Lapp CY 5G1.5	8.9	152.7	PPCY5C1.50 100M
Cable, CY, 7 Core, 1.5 mm, 100 m	Lapp CY 7G1.5	9.9	196.4	PPCY7C1.50 100M
Cable, CY, 3 Core, 2.5 mm, 100 m	Lapp CY 3G2.5	8.9	147.4	PPCY3C2.50 100M
Cable, CY, 4 Core, 2.5 mm, 100 m	Lapp CY 4G2.5	9.9	189.8	PPCY4C2.50 100M
Cable, CY, 5 Core, 2.5 mm, 100 m	Lapp CY 5G2.5	11	230.9	PPCY5C2.50 100M
Cable, CY, 7 Core, 2.5 mm, 100 m	Lapp CY 7G2.5	11.9	291.5	PPCY7C2.50 100M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.