



A202 Line Splitter

Specifications

Operating Voltage: 130V AC maximum

Operating Amperage: 15A AC maximum

Male Recepticle: Plugs into standard 2 conductor with ground outlets

Female Recepticle: Accepts 2 conductor without ground and 2 conductor with ground cords.

Features

- Enables clamp on meter amperage tests to be performed on devices with power cords without altering the cord.
- Can be used on 2 conductor no ground and 2 conductor with ground cords.
- X1 and X10 turn test areas
- Use the X10 test hole to measure smaller amperage. For example, 0.5A will be amplified to 5A for easier measurement and display on a clamp on meter
- Test holes for measuring voltage using test lead tips.

Dimensions

Size: 6" x 2.1" x 1.0" (152mm x 53mm x 25mm)

Weight: 0.4lbs (181g)

Copyright © 2015 Test Products International, Inc.

Accepts 2 conductor without ground and 2 conductor with ground cords

Test holes for measuring voltage using test lead tips

X1 and X10 turn test areas

Plugs into standard 2 conductor with ground outlets

