

## Protect It! Surge Suppressor

MODEL NUMBER: **161379T**

### Description

Tripp Lite's SurgeBlocker 16-1379T offers economical AC surge suppression for full protection of 220-240V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. SurgeBlocker 16-1379T offers 6 German CEE 7 Schuko output receptacles and 3 meter AC line cord. AC suppression rated at 330 joules shields equipment from surges and line noise. Attractive white suppressor housing. Lifetime warranty.

PLUG/OUTLETS: Input: German CEE 7 Schuko Plug/Output: 6 CEE 7 Receptacles/3m AC line cord

ELECTRICAL: 220-240V AC, 50/60Hz, 10A

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 300V RMS Clamping/330 joules

### Features

- SurgeBlocker 16-1379T offers economical AC surge suppression
- 330 joules AC surge suppression shields equipment from surges and line noise
- 6 German CEE 7 Schuko AC outlets protect computers and peripherals
- 3m AC line cable
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LED confirms surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- Lifetime warranty

## Specifications

OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	10
Outlet quantity / type	6 German CEE7 outlets
INPUT	
Input connection type	CEE7
Input cord length (ft.)	10
Input cord length (m)	3.0
Voltage compatibility (VAC)	220-250

### Highlights

- 6 CEE7 (German) outlets
- 3 m power cord
- 330 joule rating
- Lighted power switch

### Applications

- Ideal for any desktop, network or home computing application requiring AC surge suppression

### Package Includes

- 16-1379T AC surge suppressor
- Instruction manual and warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

#### LEDS ALARMS & SWITCHES

Switches	Two position power switch controls power to all outlets
----------	---

#### SURGE / NOISE SUPPRESSION

AC suppression joule rating	330
Clamping voltage (RMS)	300

#### PHYSICAL

Unit Dimensions (HWD/in)	2.6 x 2.6 x 14
Unit Dimensions (HWD/cm)	6.5 x 6.5 x 35.5

#### CERTIFICATIONS

Approvals	CE, GOST
-----------	----------

#### WARRANTY

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[16-1379T](#)