







Twist-Lock® Devices

30 Ampere, 3Ø Y 120/208, 277/480 and 347/600 Volts AC

4 Pole, 4 Wire Non-Grounding

Insulgrip® Plugs, Flanged Inlets, Connector Bodies and Receptacles**HBL2751****HBL2755****HBL2753****HBL2750****HBL2756****IP20**
SUITABILITY**30A 3ØY**
120/208V AC
NEMA L18-30P
UL Listed
3 HP**30A 3ØY**
277/480V AC
NEMA L19-30P
UL Listed
10 HP**30A 3ØY**
347/600V AC
NEMA L20-30P
UL Listed**Plugs**

Description	Cord Dia.	Catalog Numbers		
Black and white nylon.	.35"-1.15" (9-29)	HBL2751	HBL2761	HBL2771

Accessories on page B-53.

Flanged Inlets

Description	Catalog Numbers		
Nylon casing, back wired.	HBL2755	HBL2765	HBL2775

Accessories on page B-52.

IP20
SUITABILITY**30A 3ØY**
120/208V AC
NEMA L18-30R
UL Listed
3 HP**30A 3ØY**
277/480V AC
NEMA L19-30R
UL Listed
10 HP**30A 3ØY**
347/600V AC
NEMA L20-30R
UL Listed**Connector Bodies**

Description	Cord Dia.	Catalog Numbers		
Black and white nylon.	.35"-1.15" (9-29)	HBL2753	HBL2763	HBL2773

Accessories on page B-53.

Single Flush Receptacles, Back and Side Wired

Description	Catalog Numbers		
Black nylon face.	HBL2750	HBL2760	HBL2770

Accessories on page B-52.

Flanged Receptacles

Description	Catalog Numbers		
Nylon casing, back wired.	HBL2756	HBL2766	HBL2776

Accessories on page B-52.

Note: For technical information on Twist-Lock® Devices see page B-69.