

Ratings:

Current	8A
Voltage	300 V
Wire Size	28-16AWG
Test Voltage / Dirt Level	4.0 kV/3
Rated Torque / Screw Size	0.4Nm /M2

Rated Cross Section:



Single Wire (solid)	1.5mm ²
Stranded Wire (flexible)	1.0mm ²
Stranded Wire with Ferrules	1.0mm ²

Dimensions:

Spacing	3.81mm
Stripped Length	7.0mm

Materials:

Insulating Material	PA
Flammability	UL94V-0
Temperature	-30°C/+105°C
Block	CuZn
Contact	CuSn
Color	Green



ON - SHORE TECHNOLOGY, INC.

Part Number

EDZ1700/[*][*]

* - NUMBER OF POSITIONS

Units

mm

Drawing

Reviewed

Approved

Date

2/15/99

Sheet 1 of 1

Rev. A