


JACK-PTFE INSULATED-CLOSED ENTRY

09-9011-1-XX XX

JACK FOR .040 PIN

BASIC PART NO. FINISH COLOR



ACCEPTS .040 PIN-CLOSED ENTRY BOARD THICKNESS .031 TO .094


PART NO.	BODY (BRASS)	SPRING (BERYLLIUM COPPER)
09-9011-1-03	Gold	Gold
04	Electro Tin	Electro Tin
06	Electro Tin	Gold
063	Bright Tin-Lead	Gold
088	Bright Tin-Lead	Bright Tin-Lead

RECOMMENDED MOUNTING HOLE .136 DIA.(SEE PAGE 139)

09-9060-1-XX XX

JACK FOR .080 PIN

BASIC PART NO. FINISH COLOR



ACCEPTS .080 PIN-CLOSED ENTRY

PART NO.	BODY (BRASS)	SPRING (BERYLLIUM COPPER)
09-9060-1-03	Gold	Gold
04	Electro Tin	Electro Tin
06	Electro Tin	Gold
063	Bright Tin-Lead	Gold
088	Bright Tin-Lead	Bright Tin-Lead


RECOMMENDED MOUNTING HOLE .203(SEE PAGE 139)

PANEL JACKS AND FEED THRU TERMINAL

09-9012-1-XX XX

JACK FOR .040 PIN


BASIC PART NO. FINISH COLOR



ACCEPTS .040 PIN-CLOSED ENTRY BOARD THICKNESS .031 TO .094

PART NO.	BODY (BRASS)	SPRING (BERYLLIUM COPPER)
09-9012-1-03	Gold	Gold
04	Electro Tin	Electro Tin
06	Electro Tin	Gold
063	Bright Tin-Lead	Gold
088	Bright Tin-Lead	Bright Tin-Lead

RECOMMENDED MOUNTING HOLE .172 DIA.(SEE PAGE 139)





09-9110-1-044XX

09-9111-1-044XX

09-9112-1-044XX

BASIC PART NO. FINISH COLOR




PART NO.	INSULATION	METAL SLEEVE	TERMINAL BODY
09-9110-1-044XX	SEE COLOR (NYLON)	NICKEL (BRASS)	BRIGHT TIN (PHOSPHOR BRONZE)
09-9111-1-044XX	SEE COLOR (NYLON)	NICKEL (BRASS)	BRIGHT TIN (PHOSPHOR BRONZE)
09-9112-1-044XX	SEE COLOR (NYLON)	NICKEL (BRASS)	BRIGHT TIN (BRASS)

SUPPLIED UNASSEMBLED NICKEL BRASS MOUNTING HEX NUT NICKEL PLATED PHOSPHOR BRONZE INTERNAL TOOTH LOCKWASHER

09-9092-1-0319

JACK FOR .050 PIN

BASIC PART NO. FINISH COLOR



ACCEPTS .050 PIN-CLOSED ENTRY BOARD THICKNESS .031 TO .094


PART NO.	BODY (BRASS)	SPRING (BERYLLIUM COPPER)
09-9092-1-03	Gold	Gold

RECOMMENDED MOUNTING HOLE .172 DIA.(SEE PAGE 139)

09-9084-1-03 XX

JACK FOR .080 PIN

BASIC PART NO. FINISH COLOR



ACCEPTS .080 PIN

PART NO.	BODY (BRASS)	SPRING (BERYLLIUM COPPER)
09-9084-1-03	Gold	Gold


RECOMMENDED MOUNTING HOLE .172 DIA.(SEE PAGE 139)

09-9150-1-044XX

HEX HEAD TIP JACK

POLYCARBONATE

RATED FOR 10 AMPS
CONTINUOUS DUTY




ACCEPTS STANDARD .080 TIP PLUG MOUNTS IN 1/4 HOLE IN PANELS UP TO 1/4 THICK.

09-9151-1-044XX

HEX HEAD TIP JACK

POLYCARBONATE

RATED FOR 10 AMPS
CONTINUOUS DUTY



ACCEPTS STANDARD .080 TIP PLUG MOUNTS IN 1/4 HOLE IN PANELS UP TO 1/4 THICK.

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

CONCORD