




8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REV

DATE

BY

APPROVED

AD

00

DESCRIPTION

DATE

BY

APPROVED

SEE SHEET 1

-

-

-

800 SERIES MACHINED PREMIUM
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	HIGH RETENTION		.895/.905	1.000	3.200	2	864-AG34D-LF	5-6437538-4
	HIGH RETENTION		.595/.605	.700	2.400	2	848-AG34D-LF	9-1437538-5
	W/RAILS						840-AR11D-LF	8-1437538-6
	.180 PC LEAD		.595/.605	.700	2.000	2	840-AG43D-LF	8-1437538-4
	HIGH RETENTION						840-AG34D-LF	8-1437538-3
	HIGH RETENTION						832-AG38D-LF	9-6437533-4
	HIGH RETENTION		.595/.605	.700	1.600	2	832-AG34D-LF	2-6437538-5
OBSOLETE	W/RAILS						828-AR12D-LF	6-6437538-9
OBSOLETE	W/RAILS		.595/.605	.700	1.400	1	828-AR11D-LF	1-6437538-6
	.180 PC LEAD						828-AG43D-LF	6437538-4
OBSOLETE	HIGH RETENTION						828-AG34D-LF	1-6437538-3
OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D-LF	5-6437538-1
OBSOLETE	W/RAILS		.595/.605	.700	1.200	1	824-AR11D-LF	9-6437537-9
	.180 PC LEAD		.295/.305	.400	1.200	1	824-AG47D-LF	9-6437537-7
OBSOLETE	.180 PC LEAD		.395/.405	.500	1.200	1	824-AG446D-LF	9-6437537-6
	HIGH RETENTION		.595/.605	.700	1.200	1	824-AG34D-LF	9-6437537-5
	HIGH RETENTION						824-AG338D-LF	9-6437537-4
	HIGH RETENTION		.295/.305	.400	1.200	1	824-AG334D-LF	9-6437537-3
	.180 PC LEAD		.295/.305	.400	1.000	1	820-AG43D-LF	7-6437537-3
	HIGH RETENTION						820-AG34D-LF	7-6437537-2
OBSOLETE	.180 PC LEAD W/RAILS		.295/.305	.400	.900	1	818-AR44D-LF	4-6437539-9
OBSOLETE	W/RAILS						818-AR11D-LF	6-6437537-2
OBSOLETE	W/RAILS						816-AR11D-LF	5-6437537-4
	HIGH RETENTION		.295/.305	.400	.800	1	816-AG34D-LF	5-6437537-1
OBSOLETE	W/RAILS						814-AR11D-LF	3-6437537-5
	.180 PC LEAD		.295/.305	.400	.700	1	814-AG43D-LF	3-6437537-2
	HIGH RETENTION						814-AG34D-LF	3-6437537-1
OBSOLETE	W/RAILS		.295/.305	.400	.400	3	808-AR11D-LF	1-6437537-9
	.180 PC LEAD						808-AG43D-LF	6437537-5
	HIGH RETENTION						808-AG34D-LF	6437537-4
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES MACHINED PREMIUM
CONTACT PART NUMBER TABLE

OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D	0-1437538-1
OBSOLETE	W/RAILS		.595/.605	.700	1.200	1	824-AR11D	9-1437537-9
	-		.395/.405	.500	1.200	1	824-AG66D	9-1437537-8
	.180 PC LEAD		.295/.305	.400	1.200	1	824-AG47D	9-1437537-7
	.180 PC LEAD		.595/.605	.700	1.200	1	824-AG45D	6-1437538-6
	.180 PC LEAD		.395/.405	.500	1.200	1	824-AG446D	9-1437537-6
	HIGH RETENTION		.595/.605	.700	1.200	1	824-AG34D	9-1437537-5
	HIGH RETENTION					1	824-AG33D	8-1437539-2
	HIGH RETENTION					1	824-AG338D	9-1437537-4
	HIGH RETENTION					1	824-AG334D	9-1437537-3
	-		.295/.305	.400	1.200	1	824-AG32D	9-1437537-2
	-					1	824-AG31D	8-1437537-9
	-					1	824-AG30D	8-1437537-7
	-		.395/.405	.500	1.200	1	824-AG14D	8-1437537-6
	-					1	824-AG12D	8-1437537-5
	-		.595/.605	.700	1.200	1	824-AG11D	8-1437537-2
	-					1	824-AG10D	8-1437537-1
	-		.295/.305	.400	1.100	1	822-AG11D	7-1437537-8
	-						822-AG10D	7-1437537-7
	W/RAILS						820-AR11D	7-1437537-6
	.180 PC LEAD						820-AG45D	7-1437537-5
	.180 PC LEAD						820-AG44D	7-1437537-4
	.180 PC LEAD		.295/.305	.400	1.000	1	820-AG43D	7-1437537-3
	HIGH RETENTION						820-AG34D	7-1437537-2
	-						820-AG12D	6-1437537-9
	-						820-AG11D	6-1437537-6
	-						820-AG10D	6-1437537-4
	.180 PC LEAD W/RAILS						818-AR44D	4-1437539-9
	W/RAILS						818-AR11D	6-1437537-2
	.180 PC LEAD		.295/.305	.400	.900	1	818-AG44D	6-1437537-1
	HIGH RETENTION S/B 5-1437537-7						818-AG34D	5-1437538-8
	-						818-AG12D	6-1437537-0
	-						818-AG11D	5-1437537-7
	-						818-AG10D	5-1437537-6
	W/RAILS						816-AR11D	5-1437537-4
	.180 PC LEAD		.295/.305	.400	.800	1	816-AG45D	5-1437537-3
	.180 PC LEAD						816-AG44D	5-1437537-2
	HIGH RETENTION						816-AG34D	5-1437537-1
	HIGH RETENTION						816-AG33D	5-1437537-0
OBSOLETE	-						816-AG12D	4-1437537-6
	-						816-AG11D	4-1437537-0
	-						816-AG10D	3-1437537-7
	.180 PC LEAD, W/RAILS S/B 3-1437537-3						814-AR44D	5-1437533-2
	W/RAILS						814-AR11D	3-1437537-5
	.180 PC LEAD		.295/.305	.400	.700	1	814-AG45D	3-1437537-4
	.180 PC LEAD						814-AG44D	3-1437537-3
	.180 PC LEAD						814-AG43D	3-1437537-2
	HIGH RETENTION						814-AG34D	3-1437537-1
	-						814-AG12D	2-1437537-9
	-						814-AG11D	2-1437537-4
	-						814-AG10D	2-1437537-1
OBSOLETE	W/RAILS						808-AR11D	1-1437537-9
	.180 PC LEAD		.295/.305	.400	.400	3	808-AG45D	1-1437537-8
	.180 PC LEAD						808-AG44D	1-1437537-7
	.180 PC LEAD						808-AG43D	1-1437537-5
	HIGH RETENTION						808-AG34D	1-1437537-4
	-						808-AG12D	1-1437537-2
	-						808-AG11D	0-1437537-8
	-						808-AG10D	0-1437537-5
	S/B 6-1437529-8		.295/.305	.400	.300	-	806-AG11D	2-1437533-5
	SUPERSEDED BY 6-1437529-5						806-AG10D	2-1437533-3
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R BROWN 06MAY04

CHK K WRIGHT 06MAY04

APVD K WRIGHT 06MAY04

NAME

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

WEIGHT -

SIZE A1

CAGE CODE 00779

DRAWING NO. 1437539-2

RESTRICTED TO -

CUSTOMER DRAWING

SCALE 1:1

SHEET 2 OF 4

REV A3

AMP 4805 REV 31MAR2000

800 SERIES MACHINED PREMIUM
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	HIGH RETENTION		.895/.905	1.000	3.200	2	864-AG34D	5-1437538-4
	-						864-AG12D	5-1437538-2
	-						864-AG11D	4-1437538-8
	-						864-AG10D	3-1437540-1
	W/RAILS						848-AR11D	4-1437538-6
OBSOLETE	HIGH RETENTION		.595/.605	.700	2.400	2	848-AG34D	4-1437538-5
	-						848-AG12D	4-1437538-4
	-						848-AG11D	4-1437538-1
	-						848-AG10D	3-1437538-9
OBSOLETE	-		.595/.605	.700	2.100	2	842-AG12D	3-1437538-8
OBSOLETE	-						842-AG11D	3-1437538-7
	W/RAILS						840-AR11D	3-1437538-6
	.180 PC LEAD						840-AG44D	3-1437538-5
	.180 PC LEAD		.595/.605	.700	2.000	2	840-AG43D	3-1437538-4
	HIGH RETENTION						840-AG34D	3-1437538-3
	-						840-AG12D	3-1437538-2
	-						840-AG11D	3-1437538-0
	-		.595/.605	.700	1.800	2	840-AG10D	2-1437538-9
	-						836-AG11D	2-1437538-7
	S/B 2-1437528-4						832-AR12D	9-1437533-7
	HIGH RETENTION		.595/.605	.700	1.600	2	832-AG38D	9-1437533-4
	HIGH RETENTION						832-AG34D	2-1437538-5
	-						832-AG12D	2-1437538-4
	-						832-AG11D	2-1437538-2
	-						832-AG10D	2-1437538-1
OBSOLETE	W/RAILS						828-AR12D	6-1437538-9
OBSOLETE	W/RAILS		.595/.605	.700	1.400	1	828-AR11D	1-1437538-6
	.180 PC LEAD						828-AG44D	1-1437538-5
	.180 PC LEAD						828-AG43D	1-1437538-4
	HIGH RETENTION						828-AG34D	1-1437538-3
	-						828-AG12D	1-1437538-0
	-						828-AG11D	0-1437538-4
	-						828-AG10D	0-1437538-3
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R BROWN 06MAY04

CHK K WRIGHT 06MAY04

APVD K WRIGHT 06MAY04

NAME

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

WEIGHT -

SIZE A1

CAGE CODE 00779

DRAWING NO. 1437539-2

RESTRICTED TO -

CUSTOMER DRAWING

SCALE 1:1

SHEET 2 OF 4

REV A3

AMP 4805 REV 31MAR2000

800 SERIES MACHINED PREMIUM
CONTACT PART NUMBER TABLE

OBSOLETE	HIGH RETENTION		.895/.905	1.000	3.200	2	864-AG34D	5-1437538-4
	-						864-AG12D	5-1437538-2
	-						864-AG11D	4-1437538-8
	-						864-AG10D	3-1437540-1
	W/RAILS						848-AR11D	4-1437538-6
OBSOLETE	HIGH RETENTION		.595/.605	.700	2.400	2	848-AG34D	4-1437538-5
	-						848-AG12D	4-1437538-4
	-						848-AG11D	4-1437538-1
	-						848-AG10D	3-1437538-9
OBSOLETE	-		.595/.605	.700	2.100	2	842-AG12D	3-1437538-8
OBSOLETE	-						842-AG11D	3-1437538-7
	W/RAILS						840-AR11D	3-1437538-6
	.180 PC LEAD						840-AG44D	3-1437538-5
	.180 PC LEAD		.595/.605	.700	2.000	2	840-AG43D	3-1437538-4
	HIGH RETENTION						840-AG34D	3-1437538-3
	-						840-AG12D	3-1437538-2
	-						840-AG	

800 SERIES STAMPED ECONOMY
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	W/RAILS		.595/.605	.700	2.400	2	848-AR11D-ES-LF	8-1437540-0
OBSOLETE	W/RAILS						840-AR12D-ES-LF	6-6447099-8
OBSOLETE	W/RAILS						840-AR11D-ESL-LF	7-1437540-2
OBSOLETE	W/RAILS		.595/.605	.700	2.000	2	840-AR11D-ES-LF	7-1437540-1
	.180 PC LEAD						840-AG44D-ESL-LF	7-1437540-0
OBSOLETE	W/RAILS						832-AR11D-ESL-LF	0-6437540-9
OBSOLETE	W/RAILS						832-AR11D-ES-LF	0-6437540-8
	.180 PC LEAD		.595/.605	.700	1.600	2	832-AG44D-ES-LF	0-6437540-7
	.180 PC LEAD						832-AG43D-ES-LF	0-6437540-6
OBSOLETE	.180 PC LEAD W/RAILS						828-AR44D-ESL-LF	9-6437539-8
OBSOLETE	W/RAILS		.595/.605	.700	1.400	1	828-AR12D-ES-LF	6-6447099-7
OBSOLETE	W/RAILS						828-AR11D-ES-LF	9-6437539-6
	.180 PC LEAD						828-AG44D-ES-LF	9-6437539-5
OBSOLETE	.180 PC LEAD W/RAILS		.295/.305	.400	1.200	1	824-AR47D-ESL-LF	8-6437533-3
OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D-ES-LF	8-6437539-7
OBSOLETE	W/RAILS		.595/.605	.700	1.200	1	824-AR12D-ES-LF	6-6447099-6
	.180 PC LEAD		.595/.605	.700	1.200	1	824-AG44D-ESL-LF	8-6437539-3
	.180 PC LEAD		.295/.305	.400	1.100	1	822-AG44D-ES-LF	6-6437539-5
OBSOLETE	W/RAILS		.295/.305	.400	1.000	1	820-AR11D-ESL-LF	5-6437539-8
OBSOLETE	W/RAILS						820-AR11D-ES-LF	5-6437539-7
OBSOLETE	W/RAILS						816-AR11D-ESL-LF	3-6437539-5
OBSOLETE	W/RAILS		.295/.305	.400	.800	1	816-AR11D-ES-LF	3-6437539-4
	.180 PC LEAD						816-AG44D-ESL-LF	3-6437539-2
OBSOLETE	W/RAILS		.295/.305	.400	.700	1	814-AR11D-ES-LF	2-6437539-2
OBSOLETE	W/RAILS						808-AR11D-ES-LF	1-6437539-0
	.180 PC LEAD		.295/.305	.400	.400	1	808-AG43D-ES-LF	6437537-6
COMMENTS		PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES STAMPED ECONOMY
CONTACT PART NUMBER TABLE

17	OBSOLETE	.180 PC LEAD W/RAILS	9	.295/.305	.400	1.200	1	824-AR47D-ESL	8-1437533-3				
	SUPERSEDED	.180 PC LEAD W/RAILS S/B 8-1437539-3	9	.595/.605	.700	1.200	1	824-AR44D-ESL	8-1437533-2				
17	OBSOLETE	W/RAILS	9	.295/.305	.400	1.200	1	824-AR31D-ESL	3-1437540-9				
		W/RAILS	6					824-AR31D-ES	8-1437539-7				
	W/RAILS	7	824-AR12D-ES	6-1447099-6									
	OBSOLETE	W/RAILS	9	.595/.605	.700	1.200	1	824-AR11D-ESL	8-1437539-6				
OBSOLETE	W/RAILS	6	824-AR11D-ES					8-1437539-5					
17	OBSOLETE	-	9	.395/.405	.500	1.200	1	824-AG66D-ESL	8-1437539-4				
		11	5					824-AG65D-ES	0-1571180-1				
17	OBSOLETE	.180 PC LEAD	9	.595/.605	.700	1.200	1	824-AG44D-ESL	8-1437539-3				
		-	7					824-AG32D-ES	8-1437539-1				
		-	9					824-AG31D-ESL	7-1437539-7				
		-	6					824-AG31D-ES	7-1437539-6				
		-	8					824-AG30D-ESL	7-1437539-4				
		-	5					824-AG30D-ES	7-1437539-3				
		-	7					824-AG12D-ES	7-1437539-2				
		-	9					824-AG11D-ESL	7-1437539-0				
	OBSOLETE	-	6	.595/.605	.700	1.200	1	824-AG11D-ES	6-1437539-9				
		-	5					824-AG10D-ES	6-1437539-7				
		.180 PC LEAD	6					822-AG44D-ES	6-1437539-5				
		-	7					822-AG12D-ES	6-1437539-4				
		-	9					822-AG11D-ESL	6-1437539-3				
		-	6					822-AG11D-ES	6-1437539-2				
		-	5					822-AG10D-ES	6-1437539-0				
		17	OBSOLETE					-	5	.295/.305	.400	1.100	1
SUPERSEDED	.180 PC LEAD W/RAILS S/B 7-1437537-4	9	820-AR44D-ESL	7-1437533-1									
17	OBSOLETE	W/RAILS	9	820-AR11D-ESL	5-1437539-8								
		W/RAILS	6	820-AR11D-ES	5-1437539-7								
OBSOLETE	.180 PC LEAD S/B 7-1437537-4	9	820-AG44D-ES	7-1437533-0									
	-	7	820-AG12D-ES	5-1437539-6									
	-	9	820-AG11D-ESL	5-1437539-3									
	-	6	820-AG11D-ES	5-1437539-2									
	W/RAILS	5	820-AG10D-ES	5-1437539-0									
	.180 PC LEAD W/RAILS S/B 4-1437539-9	9	818-AR44D-ESL	6-1437533-4									
	W/RAILS	9	818-AR11D-ESL	4-1437539-8									
	W/RAILS	6	818-AR11D-ES	4-1437539-7									
Y 1571552-5	.180 PC LEAD S/B 6-1437537-1	9	.295/.305	.400	.900	1	818-AG44D-ESL	6-1437533-3					
	-	7					818-AG12D-ES	4-1437539-6					
	-	9					818-AG11D-ESL	4-1437539-4					
	-	6					818-AG11D-ES	4-1437539-3					
	17	OBSOLETE					-	5	818-AG10D-ES	4-1437539-1			
	OBSOLETE	W/RAILS					9	816-AR11D-ESL	3-1437539-5				
		W/RAILS					6	816-AR11D-ES	3-1437539-4				
	OBSOLETE	.180 PC LEAD					5	.295/.305	.400	.800	1	816-AG45D-ES	3-1437539-3
		.180 PC LEAD					9					816-AG44D-ESL	3-1437539-2
		-					7					816-AG12D-ES	3-1437539-1
		-					9					816-AG11D-ESL	2-1437539-9
		-					6					816-AG11D-ES	2-1437539-8
-		5	816-AG10D-ES	2-1437539-6									
.180 PC LEAD, W/RAILS S/B 3-1437537-3		9	814-AR44D-ESL	5-1437533-3									
W/RAILS		9	814-AR11D-ESL	2-1437539-3									
17	OBSOLETE	W/RAILS	6	.295/.305	.400	.700	1	814-AR11D-ES	2-1437539-2				
		.180 PC LEAD	5					814-AG45D-ES	2-1437539-1				
SUPERSEDED	.180 PC LEAD S/B 3-1437537-3	9	.295/.305	.400	.700	1	814-AG44D-ESL	4-1437540-5					
	-	7					814-AG12D-ES	2-1437539-0					
	-	9					814-AG11D-ESL	1-1437539-7					
	-	6					814-AG11D-ES	1-1437539-6					
	-	5					814-AG10D-ES	1-1437539-4					
	.180 PC W/RAILS, S/B 1437539-9	9					808-AR44D-ESL	3-1437533-1					
	W/RAILS	9					808-AR11D-ESL	1-1437539-1					
	W/RAILS	6					808-AR11D-ES	1-1437539-0					
	OBSOLETE	.180 PC LEAD					9	.295/.305	.400	.400	1	808-AG44D-ESL	0-1437539-9
		.180 PC LEAD					7					808-AG43D-ES	1-1437537-6
		-					7					808-AG12D-ES	0-1437539-8
		-					9					808-AG11D-ESL	0-1437539-6
-		6	808-AG11D-ES	0-1437539-5									
-		5	808-AG10D-ES	0-1437539-2									
S/B 7-1437529-1		7	806-AG12D-ES	2-1437533-8									
S/B 1437535-8		9	806-AG11D-ESL	8-1437536-5									
OBSOLETE	S/B 1437535-7	6	.295/.305	.400	.300	1	806-AG11D-ES	2-1437533-7					
	COMMENTS	PLATING					C	B	A	FIG	AUGAT PART NO.	TE PART NO.	

800 SERIES STAMPED ECONOMY CONTACT PART NUMBER TABLE									
	OBSOLETE	—		.895/.905	1.000	3.200	2	864-AG12D-ES	5-1437538-3
		—						864-AG11D-ESL	5-1437538-0
		—						864-AG11D-ES	4-1437538-9
	OBSOLETE	—		.595/.605	.700	2.400	2	864-AG10D-ES	3-1437540-2
		W/RAILS						848-AR11D-ESL	6-1437540-2
		W/RAILS						848-AR11D-ES	3-1437540-0
		—						848-AG12D-ES	2-1437540-8
		—						848-AG11D-ESL	4-1437538-2
		—						848-AG11D-ES	2-1437540-6
	OBSOLETE	—		.595/.605	.700	2.100	2	848-AG10D-ES	2-1437540-5
		—						842-AG11D-ESL	2-1437540-4
		—						842-AG11D-ES	2-1437540-3
		.180 PC LEAD W/RAILS S/B 2-1437540-0		.595/.605	.700	2.000	2	840-AR44D-ESL	0-1437534-7
	OBSOLETE	W/RAILS						840-AR12D-ES	6-1447099-8
		W/RAILS						840-AR11D-ESL	2-1437540-2
		W/RAILS						840-AR11D-ES	2-1437540-1
		.180 PC LEAD						840-AG44D-ESL	2-1437540-0
		—						840-AG12D-ES	1-1437540-9
		—						840-AG11D-ESL	1-1437540-7
		—						840-AG11D-ES	1-1437540-6
		—						840-AG10D-ES	1-1437540-4
	OBSOLETE	—						.595/.605	.700
		—		836-AG11D-ESL	1-1437540-1				
		—		836-AG11D-ES	1-1437540-0				
		W/RAILS		.595/.605	.700	1.600	2	832-AR11D-ESL	0-1437540-9
		W/RAILS						832-AR11D-ES	0-1437540-8
		.180 PC LEAD S/B 1437540-1						832-AG45D-ESL	6-1437538-0
		.180 PC LEAD S/B 1437540-7						832-AG44D-ESL	9-1437533-5
		.180 PC LEAD						832-AG44D-ES	0-1437540-7
		.180 PC LEAD						832-AG43D-ES	0-1437540-6
		—						832-AG12D-ES	0-1437540-5
		—						832-AG11D-ESL	0-1437540-3
		—						832-AG11D-ES	0-1437540-2
		—						832-AG10D-ES	0-1437540-1
	OBSOLETE	.180 PC LEAD W/RAILS		.595/.605	.700	1.400	1	828-AR44D-ESL	9-1437539-8
		W/RAILS						828-AR12D-ES	6-1447099-7
		W/RAILS						828-AR11D-ESL	9-1437539-7
		W/RAILS						828-AR11D-ES	9-1437539-6
	OBSOLETE	.180 PC LEAD						828-AG44D-ES	9-1437539-5
		—						828-AG12D-ES	9-1437539-4
		—						828-AG11D-ESL	9-1437539-2
		—						828-AG11D-ES	9-1437539-1
		—						828-AG10D-ES	8-1437539-9
		COMMENTS	PLATING					C	B

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOCAD

DIST00

REV

LTR

DESCRIPTION

DATE

DWN

APVD

—

SEE SHEET 1

—

—

—

1000 SERIES MACHINED PREMIUM CONTACT, LOW INSERTION FORCE PART NUMBER TABLE

S/B 4-1437538-8		.895/.905	1.000	3.200	2	1064-AG11D	2-1437529-4
S/B 3-1437540-1		.895/.905	1.000	3.200	2	1064-AG10D	2-1437529-3
S/B 3-1437538-0		.595/.605	.700	2.000	2	1040-AG11D	2-1437529-2
S/B 2-1437538-2		.595/.605	.700	1.600	2	1032-AG11D	2-1437529-1
S/B 1437538-4		.595/.605	.700	1.400	1	1028-AG11D	1-1437529-9
S/B 8-1437537-9		.295/.305	.400	1.200	1	1024-AG31D	1-1437529-8
S/B 8-1437537-2		.595/.605	.700	1.200	1	1024-AG11D	1-1437529-6
S/B 8-1437537-1		.595/.605	.700	1.200	1	1024-AG10D	1-1437529-5
S/B 6-1437537-6		.295/.305	.400	1.000	1	1020-AG11D	1-1437529-4
S/B 6-1437537-4		.295/.305	.400	.900	1	1020-AG10D	1-1437529-3
S/B 5-1437537-7		.295/.305	.400	.900	1	1018-AG11D	1-1437529-2
S/B 5-1437537-6		.295/.305	.400	.900	1	1018-AG10D	1-1437529-1
S/B 4-1437537-0		.295/.305	.400	.800	1	1016-AG11D	1-1437529-0
S/B 3-1437537-7		.295/.305	.400	.800	1	1016-AG10D	0-1437529-9
S/B 2-1437537-4		.295/.305	.400	.700	1	1014-AG11D	0-1437529-7
S/B 2-1437537-1		.295/.305	.400	.700	1	1014-AG10D	0-1437529-6
S/B 1437537-8		.295/.305	.400	.400	3	1008-AG11D	0-1437529-5
S/B 1437537-5		.295/.305	.400	.400	3	1008-AG10D	0-1437529-4
COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

1800 SERIES MACHINED PREMIUM CONTACT, LOW GOLD PART NUMBER TABLE

S/B 5-1437538-0		.895/.905	1.000	3.200	2	1864-AG111D	5-1437529-1
S/B 6-1437540-2 W/RAILS		.595/.605	.700	2.400	2	1848-AR111D	5-1437529-0
S/B 4-1437538-2		.595/.605	.700	2.400	2	1848-AG111D	4-1437529-9
S/B 2-1437540-4		.595/.605	.700	2.100	2	1842-AG111D	4-1437529-8
S/B 2-1437540-2 W/RAILS		.595/.605	.700	2.000	2	1840-AR111D	4-1437529-7
S/B 1-1437540-7		.595/.605	.700	2.000	2	1840-AG111D	4-1437529-6
S/B 1437540-3		.595/.605	.700	1.600	2	1832-AG111D	4-1437529-5
S/B 9-1437539-7 W/RAILS		.595/.605	.700	1.400	1	1828-AR111D	4-1437529-4
S/B 9-1437539-2		.595/.605	.700	1.400	1	1828-AG111D	4-1437529-3
S/B 3-1437540-9 W/RAILS		.295/.305	.400	1.200	1	1824-AR131D	4-1437529-2
S/B 8-1437539-6 W/RAILS		.595/.605	.700	1.200	1	1824-AR111D	4-1437529-1
S/B 8-1437539-4		.395/.405	.500	1.200	1	1824-AG141D	4-1437529-0
S/B 7-1437539-7		.295/.305	.400	1.200	1	1824-AG131D	3-1437529-9
S/B 7-1437539-0		.595/.605	.700	1.200	1	1824-AG111D	3-1437529-8
S/B 6-1437539-3		.395/.405	.500	1.100	1	1822-AG111D	3-1437529-7
S/B 5-1437539-8 W/RAILS		.295/.305	.400	1.000	1	1820-AR111D	3-1437529-6
S/B 5-1437539-3		.295/.305	.400	1.000	1	1820-AG111D	3-1437529-5
S/B 4-1437539-8 W/RAILS		.295/.305	.400	.900	1	1818-AR111D	3-1437529-4
S/B 4-1437539-4		.295/.305	.400	.900	1	1818-AG111D	3-1437529-3
S/B 3-1437539-5 W/RAILS		.295/.305	.400	.800	1	1816-AR111D	3-1437529-2
S/B 2-1437539-9		.295/.305	.400	.800	1	1816-AG111D	3-1437529-1
S/B 2-1437539-3 W/RAILS		.295/.305	.400	.700	1	1814-AR111D	3-1437529-0
S/B 1-1437539-7		.295/.305	.400	.700	1	1814-AG111D	2-1437529-9
S/B 1-1437539-1 W/RAILS		.295/.305	.400	.400	3	1808-AR111D	2-1437529-6
S/B 1437539-6		.295/.305	.400	.400	3	1808-AG111D	2-1437529-5
S/B 1437535-8		.295/.305	.400	.300		1806-AG111D	0-1437535-2
COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

AMP 4805 REV 31MAR2000

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± .005

4 PLC ± —

ANGLES ± —

FINISH —

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R BROWN 06MAY04

CHK K WRIGHT 06MAY04

APVD K WRIGHT 06MAY04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT —

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

CUSTOMER DRAWING

SCALE 1:1

SHEET 4 OF 4

REV A3

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

DIP SOCKET, 800 SERIES

00779

1437539-2