




Have a Question?  
Chat with a Product  
Information Specialist

What can we help you find?



## 1393738-5 Product Details

[Share](#) [Print](#) [Email](#)



1393738-5

### Cable Clamps



Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Backshell/Cable Clamp
- Cable Clamp Type = Two-Piece RFI/EMI Shield
- 37.5° Cable Exit Angle
- Cable Insulation Diameter = 10.00 - 14.90 mm
- 50 Positions

[View all Features](#)

TE Internal Number: 1393738-5



Active

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

### Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [D-Sub Housing shielded \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- [mounting guideline for d-Sub housings \(PDF, English\)](#)

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Schematic](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Backshell/Cable Clamp
- Cable Clamp Type = Two-Piece RFI/EMI Shield
- Shell Size = 5
- Screws and Retainer Clips = Without
- Grommets = Without
- Slide Latch = Without
- Thread Size = 4-40
- Color = Gray

#### Configuration Features:

- Number of Positions = 50

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Packaging Features:

- [Packaging Method](#) = Tray

#### Other:

- Brand = TE Connectivity
- Comment = Knurled screws, cable bushing (grommet) and contact tube must be ordered separately.

#### Electrical Characteristics:

- [Shielded](#) = Yes

#### Dimensions:

- [Cable Insulation Diameter \(mm \[in\]\)](#) = 10.00 - 14.90 [0.394 - 0.587]

#### Body Features:

- [Cable Exit Angle](#) = 37.5°
- [Cable Clamp Material](#) = Thermoplastic with Shielding Plates
- [Shield Plating](#) = Bright Nickel over Copper

### Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

### Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

