


JKL PART NUMBER	-A- LENGTH	LCD HIGH OUTPUT WHITE RGB COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms) TYP.	OPERATING LAMP VOLTAGE VL (Vrms) TYP.	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF2698-20B	98±2.0	5,400°k x = .336 y = .353	690 @ 0°C	275	5 ± 1	30,000 TYP.	35,000 AVG.
BF26188-20B	188±3.0		1115 @ 0°C	405			
BF26214-20B	214±2.0		1150 @ 0°C	460			
BF26285-20B	285±1.5		1525 @ 0°C	610			
BF26318-20B	318±1.5		1710 @ 0°C	685			
BF26360-20B	360±1.5		1940 @ 0°C	775			

NOTES:

* RATED LIFE IS DEFINED AS THE POINT WHICH INTENSITY BECOMES 50% OF THE INITIAL RATING.

RATING AT 25°C UNLESS OTHERWISE SPECIFIED.

			METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- REF.	JKL COMPONENTS CORPORATION							
					TITLE MINIATURE COLD CATHODE FLUORESCENT LAMP							
D	WIRE LENGTH TOLERANCE CHANGE	3/25/08	DRAWN BY L. WENGSTROM	APPV'D BY L.R.	DATE 3/25/08	SIZE	FSCM NO.	DRAWING NO.				
C	BF26285-20B LENGTH TOLERANCE CHANGE	2/3/06				A	55335	BF 26-20B				
B	ADD PART BF2698-20B	2/1/04										
A	ELECTRICAL CHNG. & ADD BF26318 & BF26360	10/20/04										
RELEASED TO CAD MULTI LIST		8/14/03				SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET		
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			NONE	8/14/03	3/25/08	D	1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF26360-20B](#) [BF2698-20B](#)