



Product: [179DT](#) 

Serial Digital Coax, Ultra-miniature, RG179 Type, 28.5 AWG Solid BC, Foil + TC Braid, CMR

Product Description

Low Loss Serial Digital Coax, Riser-CMR, Ultra-miniature, RG-179/U, 28.5 AWG solid bare copper conductor, foam HDPE core, Duofoil, + 95% tinned copper braid, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Broadcast Mobil Trucks, Digital Video, Precision Video, Telecommunications
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
28.5	Solid	BC - Bare Copper	0.012 in	1

Conductor Count:	1
------------------	---

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.056 in

Table Notes:	Gas Injected
--------------	--------------

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Alum / Poly / Alum	Duofoil®	100%
Braid	2	Tinned Copper (TC)		95%

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.1 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Outer Conductor DCR
70.5 Ohm/1000ft	8 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
17.4 pF/ft

Inductance

Nominal Inductance
0.106 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB
4500 - 6000 MHz	15 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	1.18 dB/100ft
5 MHz	1.85 dB/100ft
6 MHz	1.99 dB/100ft
7 MHz	2.15 dB/100ft
10 MHz	2.39 dB/100ft
12 MHz	2.5 dB/100ft
67.5 MHz	5.3 dB/100ft
71.5 MHz	5.5 dB/100ft
88.5 MHz	6 dB/100ft
100 MHz	6.4 dB/100ft
135 MHz	7.2 dB/100ft
143 MHz	7.5 dB/100ft
180 MHz	8.3 dB/100ft
270 MHz	10.2 dB/100ft
360 MHz	11.8 dB/100ft
540 MHz	14.6 dB/100ft
720 MHz	17 dB/100ft
750 MHz	17.4 dB/100ft
1000 MHz	20.2 dB/100ft
1500 MHz	24.8 dB/100ft
2000 MHz	28.9 dB/100ft
2250 MHz	30.9 dB/100ft
3000 MHz	35.9 dB/100ft
4500 MHz	45 dB/100ft
6000 MHz	58 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.29 ns/ft	79.0%

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-30°C To +75°C

Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	8 lbs/1000ft
Max. Pull Tension:	14 lbs
Min Bend Radius/Minor Axis:	1 in

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
CPR Euroclass:	Eca
RG Type:	179/U Type

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Riser
----------------------	----------------

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
179DT 010500	Black	Reel	500 ft	612825358558
179DT 0101000	Black	Reel	1,000 ft	612825358534
179DT 0108200	Black	Reel	8,200 ft	612825440390
179DT 0061000	Blue, Light	Reel	1,000 ft	612825358541
179DT 0011000	Brown	Reel	1,000 ft	612825357032
179DT 0081000	Gray	Reel	1,000 ft	612825356981
179DT N3U1000	Green, Mil	Reel	1,000 ft	612825357049
179DT 0031000	Orange	Reel	1,000 ft	612825357018
179DT 0021000	Red	Reel	1,000 ft	612825357025
179DT 0071000	Violet	Reel	1,000 ft	612825356998
179DT 0091000	White	Reel	1,000 ft	612825356974
179DT 0041000	Yellow	Reel	1,000 ft	612825357001

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.261 Revision Date: 04-28-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.