



Slip joint pliers, 8224/8225C

ISO: 8976


DIN: 8976

Finish: Nickel and Chrome plated, anti-corrosion treated.

Material: Chrome-Vanadium. Parallel, specially hardened jaws. With Ergo-handles in two-material combination. Thermoplastic surface on tough polypropylene which gives a superior grip.

Shape: with both flat and pipe grip jaws. Self locking jaws grip tightly at three points.

Slip joint plier with outstanding jaw opening and depth. Speedy one hand setting by pressing a button on the upper handle. Can be adjusted with parallel jaws in 11 different positions. Ergonomic design for maximum gripping comfort.



			A mm	B mm	C mm	D E F mmmmmm	
8224CIP	0103607	5	250	40	51	8.0 6 8.0 45 350	
8225CIP	0103614	5	315	52	48	9.5 7 9.5 55 550	